

MBRB10100CT

Schottky Barrier Rectifier

Reverse Voltage 100 Volts Forward Current 10 Amperes

Features


- Plastic package has underwriters Laboratory
 Flammability Classification 94V-0
- Dual rectifier construction, positive center tap
- Metal of silicon rectifier, majority carrier conduction
- Low forward voltage, high efficiency
- Guarding for over voltage protection



Package: TO-263

Mechanical Data

- Case: Epoxy, Molded
- Weight: 1.4grams(approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 sec
- •Shipped 50 units per plastic tube or tape reel packing 800/reel



Maximum Ratings & Electrical Characteristics

(TA=25°C unless otherwise noted)

PARAMETER		TEST CONDITIONS		SYMBOL	MBRB10100CT	UNIT
Maximum repetitive peak reverse voltage				VRRM	100	V
Working peak reverse voltage				VRWM	100	٧
Maximum DC blocking voltage				VDC	100	V
Maximum average forward rectified current at				Ir(AV)	10	Α
T _c =105°C total device per diode					5	
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load per diode				Ifsм	120	А
Peak repetitive reverse current per leg at tp=2.0us ,1KHz		IRRM		IRRM	1.0	Α
Voltage rate of change(rated V _R)				Dv/dt	10000	V/us
Operating junction temperature range				TJ	—55 to+150	°C
Storage temperature range				Tstg	—55 to+150	°C
Maximum instantaneous forward voltage per leg		IF=5A IF=5A	Tc=25℃ Tc=125℃	VF	0.85 0.75	V
Maximum reverse current per leg at working peak Reverse voltage			TJ=25°C TJ=100°C	lR	200 15	uA mA
Thermal Characteristics T _A =25℃ unless otherwise noted						
Symbol	Parameter	TYP. (TO-263)				Unit
Rejc	Thermal Resistance, Junction to Case per Leg	2.0				°C /W
RөJA	Thermal Resistance, Junction to Ambient per Leg	62.5			°C /W	

Note: Pulse test:300us pulse width, duty cycle=2%




MBRB10100CT


Schottky Barrier Rectifier


Reverse Voltage 100 Volts Forward Current 10 Amperes


Ratings and Characteristics Curves


(T_A = 25°C unless otherwise noted)

















Schottky Barrier Rectifier Reverse Voltage 100 Volts Forward Current 10 Amperes


Package Outline Dimensions

Unit: millimeters TO-263











MBRB10100CT

Schottky Barrier Rectifier

Reverse Voltage 100 Volts Forward Current 10 Amperes

Disclaimers

These materials are intended as a reference to assist our customers in the selection of the Suzhou Goo-Ark product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Suzhou Good-Ark Electronics Co., Ltd.or a third party.

Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.

All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Suzhou Good-Ark Electronics Co., Ltd. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Suzhou Good-Ark Electronics Co., Ltd. or an authorized Suzhou Good-Ark Electronics Co., Ltd. for the latest product information before purchasing a product listed herein. The information described here may contain technical inaccuracies or typographical errors. Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors. Please also pay attention to information published by Suzhou Good-Ark Electronics Co., Ltd. by various means, including our website home page. (http://www.goodark.com)

When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, Please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.

The prior written approval of Suzhou Good-Ark Electronics Co., Ltd. is necessary to reprint or reproduce in whole or in part these materials.

Please contact Suzhou Good-Ark Electronics Co., Ltd. or an authorized distributor for further details on these materials or the products contained herein.