




# CEP60N10/CEB60N10

## N-Channel Enhancement Mode Field Effect Transistor

### FEATURES

- 100V, 57A,  $R_{DS(ON)} = 24m\Omega$  @ $V_{GS} = 10V$ .
- Super high dense cell design for extremely low  $R_{DS(ON)}$ .
- High power and current handling capability.
- Lead free product is acquired.
- TO-220 & TO-263 package.



### ABSOLUTE MAXIMUM RATINGS $T_C = 25^\circ C$ unless otherwise noted

Parameter	Symbol	Limit	Units
Drain-Source Voltage	$V_{DS}$	100	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Drain Current-Continuous	$I_D$	57	A
Drain Current-Pulsed <sup>a</sup>	$I_{DM}$	228	A
Maximum Power Dissipation @ $T_C = 25^\circ C$ - Derate above $25^\circ C$	$P_D$	200 1.3	W W/ $^\circ C$
Single Pulsed Avalanche Energy <sup>d</sup>	$E_{AS}$	560	mJ
Single Pulsed Avalanche Current <sup>d</sup>	$I_{AS}$	40	A
Operating and Store Temperature Range	$T_J, T_{stg}$	-55 to 175	$^\circ C$

### Thermal Characteristics

Parameter	Symbol	Limit	Units
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	0.75	$^\circ C/W$
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	62.5	$^\circ C/W$

This is preliminary information on a new product in development now .  
Details are subject to change without notice .

Rev 4. 2008.Oct.  
<http://www.cet-mos.com>



# CEP60N10/CEB60N10

## Electrical Characteristics $T_C = 25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
<b>Off Characteristics</b>						
Drain-Source Breakdown Voltage	$\text{BV}_{\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$	100			V
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{DS}} = 80\text{V}, V_{\text{GS}} = 0\text{V}$		1		$\mu\text{A}$
Gate Body Leakage Current, Forward	$I_{\text{GSSF}}$	$V_{\text{GS}} = 20\text{V}, V_{\text{DS}} = 0\text{V}$		100		nA
Gate Body Leakage Current, Reverse	$I_{\text{GSSR}}$	$V_{\text{GS}} = -20\text{V}, V_{\text{DS}} = 0\text{V}$		-100		nA
<b>On Characteristics<sup>b</sup></b>						
Gate Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{GS}} = V_{\text{DS}}, I_D = 250\mu\text{A}$	2		4	V
Static Drain-Source On-Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = 10\text{V}, I_D = 30\text{A}$		20	24	$\text{m}\Omega$
<b>Dynamic Characteristics<sup>c</sup></b>						
Input Capacitance	$C_{\text{iss}}$	$V_{\text{DS}} = 25\text{V}, V_{\text{GS}} = 0\text{V}, f = 1.0 \text{ MHz}$		2810		pF
Output Capacitance	$C_{\text{oss}}$			440		pF
Reverse Transfer Capacitance	$C_{\text{rss}}$			38		pF
<b>Switching Characteristics<sup>c</sup></b>						
Turn-On Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{DD}} = 50\text{V}, I_D = 30\text{A}, V_{\text{GS}} = 10\text{V}, R_{\text{GEN}} = 2.5\Omega$		26	52	ns
Turn-On Rise Time	$t_r$			5	10	ns
Turn-Off Delay Time	$t_{\text{d}(\text{off})}$			52	104	ns
Turn-Off Fall Time	$t_f$			8	16	ns
Total Gate Charge	$Q_g$	$V_{\text{DS}} = 80\text{V}, I_D = 30\text{A}, V_{\text{GS}} = 10\text{V}$		64	76	nC
Gate-Source Charge	$Q_{\text{gs}}$			15		nC
Gate-Drain Charge	$Q_{\text{gd}}$			24		nC
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
Drain-Source Diode Forward Current	$I_S$				57	A
Drain-Source Diode Forward Voltage <sup>b</sup>	$V_{\text{SD}}$	$V_{\text{GS}} = 0\text{V}, I_S = 57\text{A}$			1.3	V
<b>Notes :</b>						
a.Repetitive Rating : Pulse width limited by maximum junction temperature.						
b.Pulse Test : Pulse Width $\leq 300\mu\text{s}$ , Duty Cycle $\leq 2\%$ .						
c.Guaranteed by design, not subject to production testing. d.L = 700 $\mu\text{H}$ , I <sub>AS</sub> = 40A, V <sub>DD</sub> = 25V, R <sub>G</sub> = 25 $\Omega$ , Starting T <sub>J</sub> = 25 $^\circ\text{C}$						



# CEP60N10/CEB60N10




Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Capacitance




Figure 4. On-Resistance Variation with Temperature



Figure 5. Gate Threshold Variation with Temperature




Figure 6. Body Diode Forward Voltage Variation with Source Current



# CEP60N10/CEB60N10




Figure 7. Gate Charge




Figure 8. Maximum Safe Operating Area




Figure 9. Switching Test Circuit



Figure 10. Switching Waveforms




Figure 11. Normalized Thermal Transient Impedance Curve