

## Metallized Polypropylene Film Capacitor

Type: ECQUA [Class X2]

In accordance with UL/CSA and European safety regulation class X2 Equipped with a safety mechanism

# E N.B.


#### **Features**

- High humidity resistance
  - (THB test : 85 °C/85 %/240 V.AC/1000 h (C  $\leq$  1.0  $\mu$ F)
- High safety (safety function installed)
- Compact
- Flame-retardant plastic case and non-combustible resin
- RoHS directive compliant

#### **Recommended applications**

• Interference suppressors

#### **Explanation of part number**



#### **Applicable standard**

\* It is certified as type ECQUA in the following approval.

Ар	proval	Class	Certification organization		
UL	UL60384-14	Class X2	1.11		
CSA	CAN/CSA E60384-14	Class X2			
Europe	EN60384-14	Class X2	VDF		
International	IEC60384-14	Class X2	] VDE		

<sup>\*</sup> When applying this capacitor to European and American safety standards, please use type designation and rating such as ECQUA, 0.1 μF.

<sup>\*</sup> Approval number (File No.) of safety regulations are subject to revision without notice. Ask factory for a copy of the latest file No.

Specifications						
Category temperature range	−40 °C to +110 °C					
Rated voltage	275 V.AC					
Rated capacitance	0.10 μF to 4.7 μF					
Capacitance tolerance	±10 % (K), ±20 % (M)					
Dissipation factor (tan $\delta$ )	$C \le 1.0 \mu\text{F}$ : tan $\delta \le 0.1 \%$ ( $20 ^{\circ}\text{C}$ , 1 kHz )					
	C > 1.0 $\mu$ F : tan $\delta$ ≤ 0.2 % ( 20 °C, 1 kHz )					
Withstand voltage	Between terminals: 633 V.AC, 1183 V.DC, 60 s					
	Between terminals to enclosure : 2050 V.AC, 60 s					
	$C ≤ 0.33 \mu\text{F} : IR ≥ 15000 \text{M}\Omega$ (20 °C, 100 V.DC, 60 s)					
Insulation resistance (IR)	C > 0.33 $\mu$ F : IR ≥ 5000 M $\Omega \cdot \mu$ F (20 °C, 100 V.DC, 60 s)					
	$C ≤ 0.47 \mu\text{F} : IR ≥ 2000 \text{M}\Omega$ (20 °C, 500 V.DC, 60 s)					
Maximum AC voltage *	310 V.AC					

<sup>\*</sup> Use of this capacitor is limited to AC voltage (50 Hz or 60 Hz sine wave).

This maximum AC voltae is specified in only ECQUA type, not specified in other types.


Please refer to individual product specification, and contact us for further questions regarding design life.

<sup>\*</sup> A faint corona discharge may occur inside of the capacitor element at rated voltage, however there is no influence on the reliability of the capacitor. (Suitable for series to the mains usage - for more details, please contact your Panasonic contact person.)

<sup>\*</sup> Maximum AC voltage including line voltage fluctuation is 310 V.AC.

<sup>310</sup> V.AC is not nominal continuous applied voltage, but only indicates maximum value including in the voltage of the power supply. Basic nominal voltage is considered as 240 VAC.





### Rating · Dimensions · Quantity

Capacitance tolerance : ±10 %(K), ±20 %(M)

	Part No.	Cap.	Dimensions (mm)				Min. order Q'ty				
	rait NO.	(µF)	L	Т	Н	F	<i>φ</i> d	Р	Q	Straight	Cut lead
	ECQUAAF104□( )	0.10	17.5	5.0	12.0	15.0	0.6	0±0.8	1.3	1000	1000
	ECQUAAF154□( )	0.15	17.5	6.0	13.0	15.0	0.6	0±0.8	1.3		
	ECQUAAF224□( )	0.22	17.5	7.5	14.0	15.0	0.6	0±0.8	1.3		
	ECQUAAF334□( )	0.33	17.5	9.0	16.0	15.0	0.6	0±0.8	1.3		800
	ECQUAAF474□( )	0.47	26.0	8.5	15.0	22.5	0.8	0±0.8	1.8		
	ECQUAAF684□( )	0.68	26.0	10.0	17.0	22.5	0.8	0±0.8	1.8	500	500
	ECQUAAF105□( )	1.0	26.0	12.0	19.0	22.5	0.8	0±0.8	1.8	300	300
	ECQUAAF155□( )	1.5	31.0	12.0	22.0	27.5	0.8	0±0.8	1.8	200	200
	ECQUAAF225□( )	2.2	31.0	14.5	24.5	27.5	0.8	0±0.8	1.8		
NEW	ECQUAAF335□( )	3.3	31.0	19.0	29.0	27.5	0.8	0±0.8	1.8	150	150
NEW	ECQUAAF475□( )	4.7	31.0	23.0	33.0	27.5	0.8	0±0.8	1.8	100	100

<sup>\* 

:</sup> Capacitance tolerance code

<sup>():</sup> Suffix for lead form