


**Vishay Semiconductors** 

# Schottky Rectifier, 2 x 15 A



PRODUCT SUMMARY						
Package	TO-247AC					
I <sub>F(AV)</sub>	2 x 15 A					
V <sub>R</sub>	60 V					
V <sub>F</sub> at I <sub>F</sub>	0.56 V					
I <sub>RM</sub> max.	100 mA at 125 °C					
T <sub>J</sub> max.	150 °C					
Diode variation	Common cathode					
E <sub>AS</sub>	13 mJ					

### FEATURES

- 150 °C T<sub>J</sub> operation
- Very low forward voltage drop
- High frequency operation
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance





- Guard ring for enhanced ruggedness and long term reliability
- Compliant to RoHS Directive 2002/95/EC
- Designed and qualified according to JEDEC-JESD47
- Halogen-free according to IEC 61249-2-21 definition (-N3 only)

### DESCRIPTION

The VS-STPS30L60CW... center tap Schottky rectifier has been optimized for very low forward voltage drop, with moderate leakage. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS									
SYMBOL	CHARACTERISTICS	VALUES	UNITS						
I <sub>F(AV)</sub>	Rectangular waveform	30	A						
V <sub>RRM</sub>		60	V						
I <sub>FSM</sub>	t <sub>p</sub> = 5 μs sine	1020	A						
V <sub>F</sub>	15 Apk, $T_J = 125 \ ^{\circ}C$ (per leg)	0.56	V						
TJ		- 55 to 150	°C						

VOLTAGE RATINGS								
PARAMETER	SYMBOL	VS-STPS30L60CWPbF	VS-STPS30L60CW-N3	UNITS				
Maximum DC reverse voltage	V <sub>R</sub>	60	60	V				
Maximum working peak reverse voltage	V <sub>RWM</sub>	00	00	v				

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	SYMBOL	TEST COND	ITIONS	VALUES	UNITS		
Maximum average forward current See fig. 5	I <sub>F(AV)</sub>	50 % duty cycle at $T_C = 112 \text{ °C}$	30				
Maximum peak one cycle non-repetitive surge current per leg		5 $\mu s$ sine or 3 $\mu s$ rect. pulse	Following any rated load condition and with rated	1020	А		
See fig. 7	IFSM	10 ms sine or 6 ms rect. pulse	V <sub>RRM</sub> applied	265			
Non-repetitive avalanche energy per leg	E <sub>AS</sub>	T <sub>J</sub> = 25 °C, I <sub>AS</sub> = 1.50 A, L = 11.	13	mJ			
Repetitive avalanche current per leg	I <sub>AR</sub>	Current decaying linearly to zero Frequency limited by T <sub>J</sub> maximum	1.50	А			

Revision: 30-Aug-11

1



www.vishay.com

## Vishay Semiconductors

ELECTRICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CO	NDITIONS	VALUES	UNITS		
		15 A	T <sub>.1</sub> = 25 °C	0.60			
Maximum forward voltage drop per leg	V <sub>FM</sub> <sup>(1)</sup>	30 A	1j=25 0	0.80	v		
See fig. 1	VFM (")	15 A	T.I = 125 °C	0.56			
		30 A	1j=125 0	0.70			
•• • • • •	I <sub>RM</sub> <sup>(1)</sup>	$T_J = 25 \ ^\circ C$		0.48			
Maximum reverse leakage current per leg See fig. 2		T 105 %O	$V_R = Rated V_R$	50 (typical)	mA		
600 lig. 2		T <sub>J</sub> = 125 °C		100			
Maximum junction capacitance per leg	CT	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		720	pF		
Typical series inductance per leg	L <sub>S</sub>	Measured lead to lead 5 n	7.5	nH			
Maximum voltage rate of change	dV/dt	Rated V <sub>R</sub>	10 000	V/µs			


#### Note


 $^{(1)}$  Pulse width < 300  $\mu s,$  duty cycle < 2 %


THERMAL - MECHANICAL SPECIFICATIONS								
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS			
Maximum junction and storage temperature range		T <sub>J</sub> , T <sub>Stg</sub>		- 55 to 150	°C			
Maximum thermal resistance, junction to case per leg		Р	DC operation See fig. 4					
Maximum thermal resistance, junction to case per package		R <sub>thJC</sub>	DC operation	1.10	°C/W			
Typical thermal resistance, case to heatsink		R <sub>thCS</sub>	Mounting surface, smooth and greased	0.24				
Approvimate weight				6	g			
Approximate weight				0.21	oz.			
Mounting torque	minimum		Non-lubricated threads	6 (5)	kgf ⋅ cm			
Mounting torque —	maximum		Non-Iupricated threads	12 (10)	(lbf · in)			
Marking device			Case style TO-247AC (JEDEC)	STPS30	L60CW			




**Vishay Semiconductors** 













Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)








Revision: 30-Aug-11 3 Document Number: 94329 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



**Vishay Semiconductors** 










Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)





Fig. 8 - Unclamped Inductive Test Circuit



**Vishay Semiconductors** 

### **ORDERING INFORMATION TABLE**



ORDERING INFORMATION (Example)								
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION					
VS-STPS30L60CWPbF	25	500	Antistatic plastic tube					
VS-STPS30L60CW-N3	25	500	Antistatic plastic tube					

LINKS TO RELATED DOCUMENTS						
Dimensions www.vishay.com/doc?95223						
Part marking information	TO-247AC PbF	www.vishay.com/doc?95226				
	TO-247AC -N3	www.vishay.com/doc?95007				


Revision: 30-Aug-11 Document Number: 94329 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



**Vishay Semiconductors** 

**TO-247AC** 

### **DIMENSIONS** in millimeters and inches



SYMBOL	MILLIMETERS		INC	HES NOTES		INCHES		NOTES	SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STMBOL	MIN.	MAX.	MIN.	MAX.	NOTES	NOTES	STINDOL	MIN.	MAX.	MIN.	MAX.	NOTES		
А	4.65	5.31	0.183	0.209			D2	0.51	1.30	0.020	0.051			
A1	2.21	2.59	0.087	0.102			E	15.29	15.87	0.602	0.625	3		
A2	1.50	2.49	0.059	0.098			E1	13.72	-	0.540	-			
b	0.99	1.40	0.039	0.055			е	5.46	BSC	0.215	BSC			
b1	0.99	1.35	0.039	0.053			ØК	2.	54	0.0	)10			
b2	1.65	2.39	0.065	0.094			L	14.20	16.10	0.559	0.634			
b3	1.65	2.34	0.065	0.092			L1	3.71	4.29	0.146	0.169			
b4	2.59	3.43	0.102	0.135			ØΡ	3.56	3.66	0.14	0.144			
b5	2.59	3.38	0.102	0.133			Ø P1	-	6.98	-	0.275			
С	0.38	0.89	0.015	0.035			Q	5.31	5.69	0.209	0.224			
c1	0.38	0.84	0.015	0.033			R	4.52	5.49	0.178	0.216			
D	19.71	20.70	0.776	0.815	3		S	5.51	BSC	0.217	BSC			
D1	13.08	-	0.515	-	4									

#### Notes

<sup>(1)</sup> Dimensioning and tolerancing per ASME Y14.5M-1994

(2) Contour of slot optional

(3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body

(4) Thermal pad contour optional with dimensions D1 and E1

<sup>(5)</sup> Lead finish uncontrolled in L1

<sup>(6)</sup> Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")

<sup>(7)</sup> Outline conforms to JEDEC<sup>®</sup> outline TO-247 with exception of dimension c

Revision: 20-Apr-17

1



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.