
## **Spec Sheet**

# SMD Power Inductors (NR series)

## NR6045T6R3M



#### Features

- Item Summary 6.3uH±20%, 2.8A, 6.0x6.0x4.5mm
- Lifecycle Stage
  - Mass Production
- Standard packaging quantity (minimum)
  Taping Embossed 1500pcs


#### ■ Products characteristics table

Inductance	6.3 uH ± 20 %
Case Size (mm)	6.0x6.0
Rated Current (max)	2.8 A
Saturation Current (max)	3.8 A
Temperature Rise Current (max)	2.8 A
DC Resistance (max)	49.4 mΩ
DC Resistance (typ)	38 mΩ
LQ Measuring Frequency	100 kHz
Self Resonant Frequency (min)	15 MHz
Operating Temp. Range	-25 to +120 ℃ (Including-self-generated heat)
Temperature characteristic (Inductance change)	± 20 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

#### External Dimensions

Dimension L	6.0 ±0.2 mm
Dimension W	6.0 ±0.2 mm
Dimension H	Max 4.5 mm
Dimension e	1.35 ±0.2 mm
Dimension f	4.0 ±0.2 mm
Dimension Δ1	Typ 2.3 mm

### Recommended Land Patterns



2017.01.02

## SMD Power Inductors (NR series)

## NR6045T6R3M



Dimension unit : mm unit: inch Length: 6.0 + / - 0.2(0.236 + / - 0.008)Width: 6.0 +/- 0.2 (0.236 +/- 0.008) max. ) Height: 4.5 max. (0.177

Inductance: 6.3 (test freq at 0.1MHz) иΗ DC Resistance: 0.038 / 0.0494 ohm (typ/max)

Saturation Current: 3,800 mA (max) 2,800 mA ( max ) Temp. rise Current:

> Saturation current typical: 30% reduction from initial L value. Temp rise Current typical: Temperature will rise by 40 deg C

