



DMN3067LW

N-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

V _{(BR)DSS}	R _{DS(ON)}	I _D T _A = +25°C
30V	67mΩ @ V _{GS} = 4.5V	2.6A
	70mΩ @ V _{GS} = 4.0V	2.5A
	98mΩ @ V _{GS} = 2.5V	2.2A

Description

This new generation MOSFET has been designed to minimize the on-state resistance (RDS(ON)) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

Applications

- Switching
- **Power Management Functions**








Top View


Features and Benefits

- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Small Surface Mount Package
- **ESD Protected Gate**
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: SOT323
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish annealed over Alloy 42 leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208
- Terminal Connections: See Diagram
- Weight: 0.006 grams (approximate)





Top View Pin Configuration

Equivalent Circuit


Ordering Information (Note 4)

Part Number	Case	Packaging
DMN3067LW-7	SOT323	3000/Tape & Reel
DMN3067LW-13	SOT323	10000/Tape & Reel

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + CI) and <1000ppm antimony compounds.</p>
 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



N30 = Product Type Marking Code

YM = Date Code Marking for SAT (Shanghai Assembly/ Test site) YM = Date Code Marking for CAT (Chengdu Assembly/ Test site) Y or \overline{Y} = Year (ex: A = 2013)

M = Month (ex: 9 = September)

Date Code Key

Year	201	1	2012		2013	20	14	2015		2016	:	2017
Code	Υ		Z		Α	[3	С		D		E
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Units
Drain-Source Voltage	V_{DSS}	30	V
Gate-Source Voltage	V_{GSS}	±12	V
Continuous Drain Current (Note 6) V _{GS} = 4.5V	I _D	2.6 2.1	А
Pulsed Drain Current (10µs pulse, duty cycle = 1%)	I _{DM}	10	А

Thermal Characteristics

Characteristic		Symbol	Value	Units	
Total Power Dissipation	(Note 5)	D	0.5	W	
Total Fower Dissipation	(Note 6)	P_{D}	1.1		
Thermal Resistance, Junction to Ambient	(Note 5)	В	241	°C/W	
Thermal Resistance, Junction to Ambient	(Note 6)	$R_{ heta JA}$	130		
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C	


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)						
Drain-Source Breakdown Voltage	BV _{DSS}	30	_	_	V	V _{GS} = 0V, I _D = 250μA
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1	μA	$V_{DS} = 30V, V_{GS} = 0V$
Gate-Body Leakage	I _{GSS}	_	_	±10	μA	$V_{GS} = \pm 12V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)				-		
Gate Threshold Voltage	V _{GS(th)}	0.5	_	1.5	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$
			48	67		V _{GS} = 4.5V, I _D = 2.5A
Static Drain-Source On-Resistance	R _{DS} (ON)	_	50	70	-	$V_{GS} = 4.0V, I_D = 2.5A$
		_	70	98		$V_{GS} = 2.5V, I_D = 2.5A$
Diode Forward Voltage	V _{SD}		_	1.2	V	V _{GS} = 0V, I _S = 0.6A
DYNAMIC CHARACTERISTICS (Note 8)						
Input Capacitance	C _{iss}		447	_		
Output Capacitance	Coss		54	_	pF	$V_{DS} = 10V, V_{GS} = 0V, f = 1.0MHz$
Reverse Transfer Capacitance	C _{rss}	_	41	_		
Gate Resistance	R _G	_	23	_	Ω	V_{DS} = 0V, V_{GS} = 0V, f = 1.0MHz
Total Gate Charge	Qg	_	4.6	_		V 45V V 45V
Gate-Source Charge	Q _{gs}	_	1.0	_	nC	$V_{GS} = 4.5V, V_{DS} = 15V,$ $I_{D} = 2.5A$
Gate-Drain Charge	Q_{gd}	_	1.0	_		ID = 2.5A
Turn-On Delay Time	t _{D(on)}	_	3.8	_		
Turn-On Rise Time	t _r	_	5.2	_	nS	V _{DD} = 15V, I _D = 1.25A, V _{GEN} = 4.5V,
Turn-Off Delay Time	t _{D(off)}	_	15	_	1110	$R_{GEN} = 10\Omega$
Turn-Off Fall Time	t _f		6.1			


Notes:

- 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.6. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper pad layout
- 7 .Short duration pulse test used to minimize self-heating effect.
 8. Guaranteed by design. Not subject to production testing.










Drain Current and Temperature

10 V_{DS} = 5.0V 9 8 DRAIN CURRENT (A) 6 5 T_A = 85°C د<u>-</u>3 T_A = 25°C 2 = -55°C 1 0 0 0.5 1.5 2 2.5 3 V_{GS}, GATE-SOURCE VOLTAGE (V) Figure 2 Typical Transfer Characteristics









Figure 6 On-Resistance Variation with Temperature













Figure 8 Gate Threshold Variation vs. Ambient Temperature



100
R_{DS(0n)}
Limited

10
P_W = 10s
P_W = 10ms
P_W = 100ms


0.01
T_A = +25°C
V_{GS} = 4.5V
Single Pulse
DUT on 1 * MRP Board

0.001
V_{DS}, DRAIN-SOURCE VOLTAGE (V)
Figure 12 SOA, Safe Operation Area



Package Outline Dimensions


Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for latest version.



SOT323							
Dim	Min	Max	Тур				
Α	0.25	0.40	0.30				
В	1.15	1.35	1.30				
С	2.00	2.20	2.10				
D	1	-	0.65				
G	1.20	1.40	1.30				
Н	1.80	2.20	2.15				
J	0.0	0.10	0.05				
K	0.90	1.00	0.95				
L	0.25	0.40	0.30				
M	0.10	0.18	0.11				
α	0°	8°	-				
All	All Dimensions in mm						

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.



Dimensions	Value (in mm)				
Z	2.8				
Х	0.7				
Υ	0.9				
С	1.9				
E	1.0				



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2014, Diodes Incorporated

www.diodes.com