

Product Specification

GENERAL DESCRIPTION

OB2358L combines a dedicated current mode PWM controller with a high voltage power MOSFET. It is optimized for high performance, low standby power, and cost effective off-line flyback converter applications in sub 27W range.

OB2358L offers complete protection coverage with automatic self-recovery feature including Cycle-by-Cycle current limiting (OCP), over load protection (OLP), over temperature protection (OTP), over voltage protection and VDD under voltage lockout (UVLO). Excellent EMI performance is achieved with On-Bright proprietary frequency shuffling technique together with soft switching control at the totem pole gate drive output.

The tone energy at below 20KHZ is minimized in the design and audio noise is eliminated during operation.

OB2358L is offered in DIP8 package.

APPLICATIONS


Offline AC/DC flyback converter for

- AC/DC adapter
- PDA power supplies
- Digital Cameras and Camcorder Adapter
- VCR, SVR, STB, DVD&DVCD Player SMPS
- Set-Top Box Power
- Auxiliary Power Supply for PC and Server
- Open-frame SMPS

FEATURES

- Power on Soft Start Reducing MOSFET Vds Stress
- Frequency shuffling for EMI
- Extended Burst Mode Control For Improved Efficiency and Minimum Standby Power Design
- Audio Noise Free Operation
- Fixed 50KHZ Switching Frequency
- Internal Synchronized Slope Compensation
- Low VDD Startup Current and Low Operating Current
- Leading Edge Blanking on Current Sense Input
- Good Protection Coverage With Auto Self-Recovery
 - VDD Under Voltage Lockout with Hysteresis (UVLO)
 - Over Temperature Protection (OTP)
 - On-Bright Proprietary Line Input Compensated
 Cycle-by-Cycle Over-current Threshold Setting For Constant Output Power Limiting Over Universal Input Voltage Range.
 - Overload Protection (OLP).
 - Over voltage Protection(OVP)

TYPICAL APPLICATION



Output Power Table

	Output I ower Table							
	Product	230VAC±15%	85-265VAC					
		Open Frame ¹	Open Frame ¹					
	OB2358L	27W	16W					


Notes: 1. Maximum practical continuous power in an open frame design with sufficient drain pattern as a heat sink, at 50 °C ambient. Higher output power is possible with extra added heat sink or air circulation to reduce thermal resistance.



GENERAL INFORMATION

Pin Configuration

The OB2358L is offered in DIP8 package as shown below.



Ordering Information

Part Number	Description
OB2358LAP	DIP8, Pb-free

Package Dissipation Rating


Package	RθJA (℃/W)
DIP8	75

Note: Drain Pin Connected to 100mm2 PCB copper clad.

Absolute Maximum Ratings

Parameter	Value			
Drain Voltage (off state)	-0.3V to BVdss			
VDD Voltage	-0.3V to 30 V			
VDD-G Input Voltage	-0.3V to 30 V			
FB Input Voltage	-0.3 to 7V			
Sense Input Voltage	-0.3 to 7V			
Maximum Operating Junction Temperature T _J	150℃			
Min/Max Storage Temperature T _{stg}	-55 to 150℃			
Lead Temperature (Soldering, 10secs)	260℃			
Notes Characas havened these lies	tll			

Note: Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute maximum-rated conditions for extended periods may affect device reliability.



Marking Information



Y: Year Code

WW: Week Code(01-52)

ZZZ:Lot Code

A:DIP8 Package

P:Pb-free Package

L: Version


S:Internal Code(Optional)



TERMINAL ASSIGNMENTS

Pin Name	I/O	Description
GND	Р	Ground
FB	I	Feedback input pin. The PWM duty cycle is determined by voltage level into this pin and the current-sense signal at Pin 4.
VDD-G	Р	Internal Gate Driver Power Supply
SENSE	I	Current sense input
VDD	Р	IC DC power supply Input
Drain	0	HV MOSFET Drain Pin. The Drain pin is connected to the primary lead of the transformer

BLOCK DIAGRAM





ELECTRICAL CHARACTERISTICS

 $(T_A = 25^{\circ}C, VDD=16V, unless otherwise noted)$

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
Supply Voltage (VI						
Istartup	VDD Start up	VDD=11V,Measure		5	20	uA
istartup	Current	Leakage current into VDD		3	20	uA
I_VDD_Operation	Operation	V _{FR} =3V		1.6		mA
	Current	ALB OA		1.0		1107
UVLO(ON)	VDD Under					
	Voltage Lockout		5.8	6.8	7.8	V
	Enter				X /-	
UVLO(OFF)	VDD Under		44.5	40.5	40.5	.,
	Voltage Lockout		11.5	12.5	13.5	V
	Exit (Recovery)	CS=0V,FB=3V				
OVP(ON)	Over voltage	Ramp up VDD until gate	22.0	23.5	25.0	V
OVP(ON)	protection voltage	clock is off	22.0	23.5	25.0	V
Feedback Input Se	ction(FR Pin)	CIOCK IS OII				
•	V _{FB} Open Loop					
V _{FB} _Open	Voltage	• (4.6	4.9	5.2	V
	FB pin short	Short FB pin to GND and				_
I _{FB} _Short	circuit current	measure current	•	1.15		mA
	Zero Duty Cycle					
V _{TH} _0D	FB Threshold			8.0		V
	Voltage	\ (/ ₁ `				
	Power Limiting					
V_{TH} PL	FB Threshold			3.7		V
	Voltage					
T _D _PL	Power limiting			50		mSec
'D_' L	Debounce Time					
Z _{FB} _IN	Input Impedance			4		Kohm
Current Sense Inp	ut(Sense Pin)		ı	,		1
Soft start time				4		ms
T_blanking	Leading edge			270		ns
	blanking time					
Z _{SENSE} _IN	Input Impedance			40		Kohm
T 00	Over Current	From Over Current Occurs		00		
T _D OC	Detection and	till the Gatedrive output		80		nSec
	Control Delay	start to turn off				
	Internal Current Limiting	ED-2 21/				
V _{TH} _OC	Threshold	FB=3.3V	0.72	0.77	0.82	V
	Voltage					
Oscillator	Vollage					
Oscillatol	Normal					
Fosc	Oscillation		45	50	55	KHZ
· USC	Frequency					1312
)	Frequency			1		
△f_Temp	Temperature			5		%
	Stability					"
A 6 1 (B =	Frequency			<u> </u>		%
$\triangle f_VDD$	Voltage Stability			5		"
D	Maximum duty	FB=3.3V, CS =0V	50	00	70	0/
D_max	cycle	,	56	66	76	%





F_Burst	Burst Mode Base Frequency			22		KHZ
Mosfet Section						
BVdss	MOSFET Drain- Source Breakdown Voltage		600			V
Rdson	Static, Id=1.0A			4.4	5.5	Ω
Frequency Shuffling					/^ ^	
Δf_OSC	Frequency Modulation range /Base frequency		-4		4	%
Over temperature protection						
Over temperature pr	rotection trip point			150		$^{\circ}\mathbb{C}$





CHARACTERIZATION PLOTS


(The characteristic graphs are normalized at Ta=25°C)



















OPERATION DESCRIPTION

The OB2358L is a low power off-line SMPS Switcher optimized for off-line flyback converter applications in sub 27W power range. The 'Extended burst mode' control greatly reduces the standby power consumption and helps the design easily to meet the international power conservation requirements.

Startup Current and Start up Control

Startup current of OB2358L is designed to be very low so that VDD could be charged up above UVLO threshold level and device starts up quickly. A large value startup resistor can therefore be used to minimize the power loss yet achieve a reliable startup in application. For AC/DC adapter with universal input range design, a 2 $M\Omega,\,1/8$ W startup resistor could be used together with a VDD capacitor to provide a fast startup and yet low power dissipation design solution.

Operating Current

The Operating current of OB2358L is low at 2mA. Good efficiency is achieved with OB2358L low operating current together with the 'Extended burst mode' control features.

Soft Start

OB2358L features an internal 4ms soft start to soften the electrical stress occurring in the power supply during startup. It is activated during the power on sequence. As soon as VDD reaches UVLO(OFF), the peak current is gradually increased from nearly zero to the maximum level of 0.77V. Every restart up is followed by a soft start.

Frequency shuffling for EMI improvement

The frequency Shuffling (switching frequency modulation) is implemented in OB2358L. The oscillation frequency is modulated so that the tone energy is spread out. The spread spectrum minimizes the conduction band EMI and therefore eases the system design.

Extended Burst Mode Operation

At light load or zero load condition, most of the power dissipation in a switching mode power supply is from switching loss on the MOSFET, the core loss of the transformer and the loss on the snubber circuit. The magnitude of power loss is in proportion to the switching frequency. Lower switching frequency leads to the reduction on the power loss and thus conserves the energy.

The switching frequency is internally adjusted at no load or light load condition. The switch frequency reduces at light/no load condition to improve the conversion efficiency. At light load or no load condition, the FB input drops below burst mode threshold level and device enters Burst Mode control. The Gate drive output switches only when VDD voltage drops below a preset level and FB input is active to output an on state. Otherwise the gate drive remains at off state to minimize the switching loss and reduces the standby power consumption to the greatest extend.

The switching frequency control also eliminates the audio noise at any loading conditions.

Oscillator Operation

The switching frequency of OB2358L is internally fixed at 50KHZ. No external frequency setting components are required for PCB design simplification.

• Current Sensing and Leading Edge Blanking Cycle-by-Cycle current limiting is offered in OB2358L current mode PWM control. The switch current is detected by a sense resistor into the sense pin. An internal leading edge blanking circuit chops off the sensed voltage spike at initial internal power MOSFET on state due to snubber diode reverse recovery and surge gate current of internal power MOSFET so that the external RC filtering on sense input is no longer needed. The current limiting comparator is disabled and cannot turn off the internal power MOSFET during the blanking period. The PWM duty cycle is determined by the current sense input voltage and the FB input voltage.

Internal Synchronized Slope Compensation

Built-in slope compensation circuit adds voltage ramp onto the current sense input voltage for PWM generation. This greatly improves the close loop stability at CCM and prevents the subharmonic oscillation and thus reduces the output ripple voltage.

Drive

The internal power MOSFET in OB2358L is driven by a dedicated gate driver for power switch control. Too weak the gate drive strength results in higher conduction and switch loss of MOSFET while too strong gate drive results the compromise of EMI. A good tradeoff is achieved through the built-in totem pole gate design with right output strength and dead time control. The low idle loss and good



EMI system design is easier to achieve with this dedicated control scheme.

In addition to the gate drive control scheme mentioned, the gate drive strength can also be adjusted externally by a resistor connected between VDD and VDDG, the falling edge of the Drain output can be well controlled. It provides great flexibility for system EMI design.

Protection Controls

Good power supply system reliability is achieved with its rich protection features including Cycle-by-Cycle current limiting (OCP), Over Load Protection (OLP), over voltage protection and Under Voltage Lockout on VDD (UVLO).

With On-Bright Proprietary technology, the OCP is line voltage compensated to achieve constant


output power limit over the universal input voltage range.


At overload condition when FB input voltage exceeds power limit threshold value for more than TD_PL, control circuit reacts to shut down the switcher. Switcher restarts when VDD voltage drops below UVLO limit. Similarly, control circuit shutdowns the power MOSFET when an Over Temperature condition is detected.


VDD is supplied by transformer auxiliary winding output. When VDD voltage exceeds the internal OVP threshold voltage (23.5V) due to abnormal conditions, The power MOSFET is shut down until VDD drops below 6.8V (UVLO limit), and device enters power on restart-up sequence thereafter.

PACKAGE MECHANICAL DATA

8-Pin Plastic DIP







Cumbal	Dimensions In Millimeters		Dimensions In Inches		
Symbol	Min	Max	Min	Max	
Α	3.710	5.334	0.146	0.210	
A1	0.381		0.015		
A2	2.921	4.953	0.115	0.195	
В	0.350	0.650	0.014	0.026	
B1	1.524 (BSC)		0.06 (BSC)		
С	0.200	0.360	0.008	0.014	
D	9.000	10.160	0.354	0.400	
E	6.096	7.112	0.240	0.280	
E1	7.320	8.255	0.288	0.325	
е	2.540 (BSC)		0.1 (BSC)	
L	2.921	3.810	0.115	0.150	
E2	7.620	10.920	0.300	0.430	



IMPORTANT NOTICE

RIGHT TO MAKE CHANGES

On-Bright Electronics Corp. reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

WARRANTY INFORMATION

On-Bright Electronics Corp. warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with its standard warranty. Testing and other quality control techniques are used to the extent it deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed. On-Bright Electronics Corp. assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using On-Bright's components, data sheet and application notes. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

LIFE SUPPORT

On-Bright Electronics Corp.'s products are not designed to be used as components in devices intended to support or sustain human life. On-bright Electronics Corp. will not be held liable for any damages or claims resulting from the use of its products in medical applications.

MILITARY

On-Bright Electronics Corp.'s products are not designed for use in military applications. On-Bright Electronics Corp. will not be held liable for any damages or claims resulting from the use of its products in military applications.