500 WATT ULTRA LOW CAPACITANCE TVS ARRAY



DESCRIPTION

The PSOTxxLC series are ultra low capacitance transient voltage suppressor (TVS) arrays, designed for power or data line applications that provide protection against ESD, tertiary lightning and switching transients. This series offers low clamping voltage for the protection of sensitive components.

The PSOTxxLC series has a peak pulse power of 500 Watts for an $8/20\mu s$ waveshape and is available in a SOT-23 package configuration. This series meets the IEC 61000-4-2, 61000-4-4 and IEC 61000-4-5 requirements.

FEATURES

- Compatible with IEC 61000-4-2 (ESD): Air 15kV, Contact 8kV
- Compatible with IEC 61000-4-4 (EFT): 40A, 5/50ns
- Compatible with IEC 61000-4-5 (Surge): 12A, 8/20µs Level 1(Line-Ground) & Level 2(Line-Line)
- 500 Watts Peak Pulse Power per Line(tp = 8/20μs)
- Low Clamping Voltage
- Ultra Low Capacitance
- Available in Multiple Voltages Ranging from 3V to 36V
- RoHS Compliant
- REACH Compliant


MECHANICAL CHARACTERISTICS

- Molded JEDEC SOT-23 Package
- Approximate Weight: 8 milligrams
- Lead-Free Pure-Tin Plating (Annealed)
- Solder Reflow Temperature:
 - Pure-Tin Sn, 100: 260-270°C
- Flammability Rating UL 94V-0
- 8mm Tape and Reel per EIA Standard 481

APPLICATIONS

- Ethernet 10/100 Base T
- Cellular Phones
- FireWire
- Audio/Video Inputs
- Portable Electronics

PIN CONFIGURATION



TYPICAL DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified								
PARAMETER	SYMBOL	VALUE	UNITS					
Peak Pulse Power (tp = 8/20μs) - See Figure 1	P _{pp}	500	Watts					
Operating Temperature	T,	-55 to 150	°C					
Storage Temperature	Т _{stg}	-55 to 150	°C					


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified								
PART NUMBER (Note 1)	DEVICE MARKING	RATED STAND-OFF VOLTAGE V _{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE (Note 2) @ 1mA V _(BR) VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ I _p = 1A V _c VOLTS	MAXIMUM CLAMPING VOLTAGE (Fig. 2) @ I _p = 5A V _c VOLTS	MAXIMUM LEAKAGE CURRENT @V _{wm} Ι _D μΑ	TYPICAL CAPACITANCE @0V, 1MHz C pF	
PSOT03LC	03L	3.3	4.0	7.0	9.0	125	5	
PSOT05LC	05L	5.0	6.0	9.8	11.0	20	5	
PSOT08LC	08L	8.0	8.5	13.4	15.0	10	5	
PSOT12LC	12L	12.0	13.3	19.0	23.0	1	5	
PSOT15LC	15L	15.0	16.7	24.0	28.0	1	5	
PSOT24LC	24L	24.0	26.7	43.0	46.0	1	5	
PSOT36LC	36L	36.0	40.0	51.0	68.0	1	5	
NOTES								


05066


1. Positive potential is applied from pin 1 to 2; pin 2 is ground.

2. Do not test or surge from pin 2 to 1. PIV typically greater than 100V for rectifier diode.

TYPICAL DEVICE CHARACTERISTICS








TYPICAL DEVICE CHARACTERISTICS

PROFEK DEVICES



SPICE MODEL

FIGURE 1 SPICE MODEL FOR



ABD - Avalanche Breakdown Diode (TVS) LCRD - Low Capacitance Rectifier Diode Lg - Lead Inductance

TABLE 1 - SPICE PARAMETERS							
PARAMETER	UNIT	ABD(TVS)	LCRD				
BV	V	See Table 2	200				
IBV	μΑ	1	0.01				
C _{jo}	pF	See Table 2	5				
I _s	А	See Table 2	1E-14				
Vj	V	0.6	0.6				
м	-	0.33	0.33				
N	-	1	1				
R _s	Ohms	See Table 2	0.31				
TT	S	1E-8	1E-9				
EG	eV	1.11	1.11				

TABLE 2 - ABD SPECIFIC SPICE PARAMETERS								
PART NUMBER	B _v (VOLTS)	C _{io} (pF)	I _s (AMPS)	Rs(OHMS)				
PSOT03LC	4.5	438	1E-11	0.21				
PSOT05LC	6.0	284	1E-11	0.14				
PSOT08LC	8.5	146	1E-11	0.28				
PSOT12LC	13.3	123	1E-13	0.40				
PSOT15LC	16.7	102	1E-13	0.52				
PSOT12LC	26.7	61	1E-13	1.54				

APPLICATION INFORMATION




FIGURE 1 - COMMON MODE I/O PORT PROTECTION

Two PSOTxxLC devices used in parallel. Circuit connectivity is as follows:

- I/O Line connected to Device 1, Pin 1.
- I/O Line connected to Device 2, Pin 2.
- Device 1, Pin 2 connected to ground.
- Device 2, Pin 1 connected to ground.
- Device 1 and 2, Pin 3 not connected.




FIGURE 1 - DIFFERENTIAL MODE ETHERNET PROTECTION

Two PSOTxxLC devices used in parallel. Circuit connectivity is as follows:

- I/O Line 1 connected to Device 1, Pin 1.
- I/O Line 1 connected to Device 2, Pin 2.
- I/O Line 2 connected to Device 1, Pin 1.
- I/O Line 2 connected to Device 2, Pin 2.
- Device 1 and 2, Pin 3 not connected.


CIRCUIT BOARD RECOMMENDATIONS


Circuit board layout is critical for electromagnetic compatibility protection. The following guidelines are recommended:


- The protection device should be placed near the input terminals or connectors, the device will divert the transient current immediately before it can be coupled into the nearby traces.
- The path length between the TVS device and the protected line should be minimized.
- All conductive loops including power and ground loops should be minimized.
- The transient current return path to ground should be kept as short as possible to reduce parasitic inductance.
- Ground planes should be used whenever possible. For multilayer PCBs, use dedicated ground planes

SOT-23 PACKAGE INFORMATION

OUTLINE DIMENSIONS							
DIM	MILLIN	IETERS	INCHES				
DIIVI	MIN	MAX	MIN	MAX			
А	2.80	3.04	0.110	0.120			
В	1.20	1.40	0.047	0.055			
С	0.89	1.11	0.035	0.044			
D	0.37	0.50	0.015	0.020			
G	1.78	2.04	0.070	0.081			
н	0.013	0.100	0.001	0.004			
J	0.085	0.177	0.003	0.007			
к	0.45	0.60	0.018	0.024			
L	0.89	1.02	0.035	0.040			
S	2.10	2.50	0.083	0.098			
V	0.45	0.60	0.018	0.024			







NOTES


1. Controlling dimension: inches.

2. Dimensioning and tolerances per ANSI Y14.5M, 1985.


3. Pin 3 is the cathode (Unidirectional Only)

4. Dimensions are exclusive of mold flash and metal burrs.

PAD LAYOUT DIMENSIONS								
DIM	MILLIN	MILLIMETERS		HES				
DIM	MIN	MAX	MIN	MAX				
А	0.71	0.97	0.028	0.038				
В	1.88	2.13	0.074	0.084				
С	0.71	0.97	0.028	0.038				
D	0.81	1.07	0.032	0.042				
NOTES 1. Controlling dimension: inches.								



TAPE AND REEL



User Direction of Feed

SPECIFICATIONS												
REEL DIA.	TAPE WIDTH	A0	В0	ко	D	E	F	W	PO	P2	Р	tmax
178mm (7")	8mm	3.15 ± 0.10	2.77 ± 0.10	1.30 ± 0.10	1.55 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	4.00 ± 0.10	0.228
NOTES 1. Dimensions are in	NOTES 1. Dimensions are in millimeters.											

2. Surface mount product is taped and reeled in accordance with EIA-481.

3. Suffix - T7 = 7" Reel - 3,000 pieces per 8mm tape.

4. Suffix - T13 = 13" Reel - 10,000 pieces per 8mm tape.

5. Marking on Part - marking code (see page 2) and date code.

Package outline, pad layout and tape specifications per document number 06012.R2 8/10.

ORDERING INFORMATION								
BASE PART NUMBER (xx = Voltage)	LEADFREE SUFFIX	TAPE SUFFIX	QTY/REEL	REEL SIZE	TUBE QTY			
PSOTxxLC	-LF	-T7	3,000	7"	n/a			
PSOTxxLC	-LF	-T13	10,000	13"	n/a			
This device is only available in a Lead-Free configuration.								

COMPANY INFORMATION

COMPANY PROFILE

In business more than 20 years, ProTek Devices[™] is a privately-held company located in Tempe, Arizona, that offers a product line of transient voltage suppressors (TVS); avalanche breakdown diodes; steering diode TVS arrays and other surge suppressor component products. These TVS devices protect electronic systems from the effects of lightning, electrostatic discharge (ESD), nuclear electromagnetic pulses (NEMP), inductive switching and EMI / RFI. ProTek Devices also offers high performance interface and linear products that include analog switches; multiplexers; LED drivers; audio control ICs; RF and related high frequency products. The analog devices work in a host of consumer; industrial; automotive and other applications.

CONTACT US

Corporate Headquarters

2929 South Fair Lane Tempe, Arizona 85282 USA

By Telephone

General: 602-431-8101 Sales: & Marketing: 602-414-5109 Customer Service: 602-414-5114 Product Technical Support: 602-414-5107

By Fax

General: 602-431-2288

By E-mail:

Sales: <u>sales@protekdevices.com</u> Customer Service: <u>service@protekdevices.com</u> Technical Support: <u>support@protekdevices.com</u>

ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19 Zervex Singapore - 408538 Tel: +65-67488312 Fax: +65-67488313

Web www.protekdevices.com

COPYRIGHT © ProTek Devices 1998 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice.

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.