

UNISONIC TECHNOLOGIES CO., LTD

1N60 Power MOSFET

1.2A, 600V N-CHANNEL **POWER MOSFET**


DESCRIPTION


The UTC 1N60 is a high voltage MOSFET and is designed to have better characteristics, such as fast switching time, low gate charge, low on-state resistance and have a high rugged avalanche characteristics. This power MOSFET is usually used at high speed switching applications in power supplies, PWM motor controls, high efficient DC to DC converters and bridge circuits.

FEATURES

- * $R_{DS(ON)}$ < 11.50@ V_{GS} = 10V, I_D = 0.6A
- * Ultra Low gate charge (typical 5.0nC)
- * Low reverse transfer capacitance (C_{RSS} = typical 3.0 pF)
- * Fast switching capability
- * Avalanche energy specified
- * Improved dv/dt capability, high ruggedness

SYMBOL






■ ORDERING INFORMATION

Ordering Number		Dookogo	Pin Assignment			Dooking	
Lead Free	Halogen Free	Package	1	2	3	Packing	
-	1N60G-AA3-R	SOT-223	G	D	S	Tape Reel	
1N60L-TA3-T	1N60G-TA3-T	TO-220	G	D	S	Tube	
1N60L-TF2-T	1N60G-TF2-T	TO-220F2	G	D	S	Tube	
1N60L-TF3-T	1N60G-TF3-T	TO-220F	G	D	S	Tube	
1N60L-TM3-T	1N60G-TM3-T	TO-251	G	D	S	Tube	
1N60L-TMS-T	1N60G-TMS-T	TO-251S	G	D	S	Tube	
1N60L-TMS2-T	1N60G-TMS2-T	TO-251S2	G	D	S	Tube	
1N60L-TMS4-T	1N60G-TMS4-T	TO-251S4	G	D	S	Tube	
1N60L-TN3-R	1N60G-TN3-R	TO-252	G	D	S	Tape Reel	
1N60L-TND-R	1N60G-TND-R	TO-252D	G	D	S	Tape Reel	
1N60L-T60-K	1N60G-T60-K	TO-126	G	D	S	Bulk	
1N60L-T92-B	1N60G-T92-B	TO-92	G	D	S	Tape Box	
1N60L-T92-K	1N60G-T92-K	TO-92	G	D	S	Bulk	

Note: Pin Assignment: G: Gate D: Drain S: Source




- (1) B: Tape Box, K: Bulk, T: Tube, R: Tape Reel
- (2) AA3: SOT-223, T92: TO-92, TA3: TO-220,

TF2: TO-220F2, TF3: TO-220F, TM3: TO-251, TMS: TO-251S, TMS2: TO-251S2,

TMS4: TO-251S4, TN3: TO-252, TND: TO-252D, T60: TO-126

(3) L: Lead Free, G: Halogen Free and Lead Free

MARKING



■ **ABSOLUTE MAXIMUM RATINGS** (T_C = 25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Drain-Source Voltage		V_{DSS}	600	V
Gate-Source Voltage		V_{GSS}	±30	V
Avalanche Current (Note 2)		I _{AR}	1.2	Α
Continuous Drain Current		I _D	1.2	Α
Pulsed Drain Current (Note 2)		I _{DM}	4.8	Α
Avalanche Energy	Single Pulsed (Note 3)	E _{AS}	50	mJ
	Repetitive (Note 2)	E _{AR}	4.0	mJ
Peak Diode Recovery dv/dt (Note 4)		dv/dt	4.5	V/ns
	SOT-223		8	
Power Dissipation	TO-251/TO-252			
	TO-252D/TO-251S		28	
	TO-251S2/ TO-251S4			
	TO-220	P _D	40	W
	TO-220F		21	
	TO-220F2		23	
	$TO-92(T_A=25^{\circ}C)$		1	
	TO-126		12.5	
Junction Temperature		TJ	+150	°C
Operating Temperature		T _{OPR}	-55 ~ +150	°C
Storage Temperature		T _{STG}	-55 ~ +150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

- 2. Repetitive Rating: Pulse width limited by maximum junction temperature
- 3. L = 60mH, I_{AS} = 1A, V_{DD} = 50V, R_G = 25 Ω , Starting T_J = 25 $^{\circ}$ C
- 4. $I_{SD} \le 1.2A$, $di/dt \le 200A/\mu s$, $V_{DD} \le BV_{DSS}$, Starting $T_J = 25^{\circ}C$

■ THERMAL DATA

PARAMETER		SYMBOL	RATINGS	UNIT		
Junction to Ambient	SOT-223		150			
	TO-251/TO-252	θја				
	TO-252D/TO-251S		110			
	TO-251S2/ TO-251S4			°C/W		
	TO-220/TO-220F		62.5	C/VV		
	TO-220F2		62.5			
	TO-92		140	1		
	TO-126		132			
	SOT-223		14			
	TO-251/TO-252					
Junction to Case	TO-252D/TO-251S		4.53			
	TO-251S2/ TO-251S4					
	TO-220	θ _{Јс}	3.13	°C/W		
	TO-220F		5.95			
	TO-220F2		5.43			
	TO-92		80			
	TO-126		10			

■ **ELECTRICAL CHARACTERISTICS** (T_C=25°C, unless otherwise specified.)


PARAMETER	SYMBOI	TEST	TEST CONDITIONS		TYP	MAX	UNIT
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D	V _{GS} =0V, I _D =250μA				V
Drain-Source Leakage Current	I _{DSS}	V _{DS} =600V,	V _{DS} =600V, V _{GS} =0V			10	μΑ
Forward Lockson Current	rd ,	V _{GS} =30V, V	V _{DS} =0V			100	nA
Gate-Source Leakage Current Rever	se I _{GSS}	V _{GS} =-30V,	V _{GS} =-30V, V _{DS} =0V			-100	nA
Breakdown Voltage Temperature Coeffic	cient △BV _{DSS} /△	$T_J I_D = 250 \mu A$	I _D =250μA		0.4		V/°C
ON CHARACTERISTICS							
Gate Threshold Voltage	$V_{GS(TH)}$	V _{DS} =V _{GS} , I _I	$V_{DS}=V_{GS}$, $I_D=250\mu A$			4.0	V
Static Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I	V _{GS} =10V, I _D =0.6A			11.5	Ω
DYNAMIC CHARACTERISTICS							
Input Capacitance	C _{ISS}		V _{DS} =25V, V _{GS} =0V, f=1MHz		120	150	pF
Output Capacitance	Coss	V _{DS} =25V, \			20	25	pF
Reverse Transfer Capacitance	C _{RSS}				3.0	4.0	pF
SWITCHING CHARACTERISTICS							
Turn-On Delay Time	t _{D(ON)}		V_{DD} =300V, I_{D} =1.2A, R_{G} =50 Ω (Note 2,3)		5	20	ns
Turn-On Rise Time	t _R	V _{DD} =300V,			25	60	ns
Turn-Off Delay Time	t _{D(OFF)}	(Note 2,3)			7	25	ns
Turn-Off Fall Time	t _F				25	60	ns
Total Gate Charge	Q_G		V _{DS} =480V, V _{GS} =10V, I _D =1.2A (Note 2,3)		5.0	6.0	nC
Gate-Source Charge	Q_GS				1.0		nC
Gate-Drain Charge	Q_GD	(14016-2,3)			2.6		nC
SOURCE-DRAIN DIODE RATINGS AN	D CHARACTER	STICS					
Drain-Source Diode Forward Voltage	V_{SD}	V_{GS} =0 V , I_{S}	=1.2A			1.4	V
Maximum Continuous Drain-Source Dioc	de ,					1.2	Α
Forward Current	Is					1.2	A
Maximum Pulsed Drain-Source Diode	I _{SM}					4.8	Α
Forward Current	ISM					4.0	^
Reverse Recovery Time	t _{rr}	V_{GS} =0V, I_{S}	V _{GS} =0V, I _S =1.2A		160		ns
Reverse Recovery Charge	Q_{RR}	dI _F /dt=100	dI _F /dt=100A/μs (Note 1) 0.		0.3		μC

Notes: 1. Repetitive Rating: Pulse width limited by maximum junction temperature


^{2.} Pulse Test: Pulse Width ≤300µs, Duty Cycle≤2%

^{3.} Essentially Independent of Operating Temperature

■ TEST CIRCUITS AND WAVEFORMS





Peak Diode Recovery dv/dt Test Circuit



Peak Diode Recovery dv/dt Waveforms


■ TEST CIRCUITS AND WAVEFORMS (Cont.)






Switching Test Circuit


Switching Waveforms






Gate Charge Test Circuit

Gate Charge Waveform








Unclamped Inductive Switching Test Circuit


Unclamped Inductive Switching Waveforms

■ TYPICAL CHARACTERISTICS









UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.