

600mA LDO Linear Regulator with Shutdown


❖ GENERAL DESCRIPTION

The AX6607 is a low dropout, positive linear regulator with very low quiescent. It can supply 600mA output current. The BP pin with a 10nF bypass capacitor can help reduce the output noise level. The characteristics of low dropout voltage and less quiescent current make it good for some critical current application, for example, some battery powered devices. The typical guiescent current is approximately 50µA. In the shutdown mode, the maximum supply current is less than 2µA. The AX6607 regulator is able to operate with output capacitors as small as 1µF for stability. The AX6607 series are offering several fixed output voltage types including 1.2V, 1.5V, 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 3.0V, 3.3V and adjustable version. Built-in current-limit and thermal-shutdown functions prevent any fault condition from IC damage.


❖ FEATURES

- Input voltage range : 2.6V~5.5V
- Adjustable and 1.2/1.5/1.8/2.5/2.6/2.7/2.8/3.0/3.3V fixed output voltages
- VOUT adjust range from V_{FB} to 5.0V
- Guaranteed 600mA output current
- Very Low quiescent current at 50µA (typ.)
- Needs Only 1µF capacitor for Stability
- Maximum supply current in shutdown mode <2µA
- Current limit and thermal shutdown protection
- Short circuit current fold-back
- Available in the SOT-23-5L and TDFN-6L Pb-Free Packages

❖ BLOCK DIAGRAM



Fixed Version




Adjustable Version




❖ PIN ASSIGNMENT

The packages of AX6607 are SOT-23-5L and TDFN-6L; the pin assignment is given by: (Top View)




Adjustable Version: Pin 4 is FB Fixed Version: Pin 4 is BP



Name	Description
VIN	Voltage input. The input capacitor in the range of $1\mu\text{F}$ to $10\mu\text{F}$ is sufficient.
GND	Ground
EN	Enable pin (Active High)
BP	Reference Noise Bypass (The Bypass capacitor ≥ 1nF)
VOUT	Output Voltage, The AX6607 is stable with an output capacitor 1µF for greater.
FB/NC	For adjustable output voltage version only, the pin connects two resistances to decide output voltage. When use fixed output voltage version, this pin is NC pin.

❖ ORDER/MARKING INFORMATION



2/11



Appendix

Part Number	Identification Code	Part Number	Identification Code
AX6607-ADJ	FA	AX6607-2.6V	Fj
AX6607-1.2V	Fh	AX6607-2.7V	Fp
AX6607-1.5V	Fi	AX6607-2.8V	Fn
AX6607-1.8V	Fk	AX6607-3.0V	Fr
AX6607-2.5V	Fm	AX6607-3.3V	Fs

❖ ABSOLUTE MAXIMUM RATINGS (at T_A=25 °C)

Characteristics	,	Symbol	Rating	Unit	
V _{IN} Pin Voltage			GND - 0.3 to 7	V	
Output Voltage		V _{OUT}	GND - 0.3 to 7	٧	
Enable Voltage		V _{EN}	GND - 0.3 to 7	V	
Feedback Voltage		V_{FB}	GND - 0.3 to 7	V	
Power Dissipation	SOT-23-5L	PD	400	- mW	
Power Dissipation	TDFN-6L	רם	830		
Storage Temperature Range		T _{ST}	-40 to +150	°C	
Operating Temperature Range		T _{OP}	-40 to +85	°C	
Junction Temperature		TJ	-40 to +125	°C	
Thermal Resistance from	SOT-23-5L	0	180	°C/W	
Junction to case	TDFN-6L	θ _{JC}	25		
Thermal Resistance from	SOT-23-5L	0	250	°C/W	
Junction to ambient	TDFN-6L	θ_{JA}	120	-0/00	

Note: θ_{JA} is measured with the PCB copper area of approximately 1 in²(Multi-layer). That need connect to GND (exposed pad) pin.



❖ ELECTRICAL CHARACTERISTICS (V_{IN}=5V, T_A=25 °C, unless otherwise noted)

Characteristics	Symbol	Condit	ions	Min	Тур	Max	Units
Input Voltage	V _{IN}	I _{OUT} =30mA (Note1)		2.6	-	5.5	V
Quiescent Current	ΙQ	I _{OUT} =0mA		-	50	80	μA
Shutdown Current	I _{SD}	V _{IN} =3.6V, I _{OUT} =0ı	mA, V _{EN} =0V	-	-	1	μA
Output Voltage Accuracy	۸۱/۰۰۰	V_{IN} = V_{OUT} +0.1V to 5.5V V_{OUT} \geq 2.5V, I_{OUT} =1mA		-2	1	+2	%
(Fixed Version Only)	ΔV _{OUT}	V_{IN} =2.6V to 5.5V 2.5V > $V_{OUT} \ge 1.2V$, I_{OUT} =1mA		-3	-	+3	70
Feedback Voltage	V_{FB}	V _{IN} =2.6V to 5.5V,	I _{OUT} =1mA	0.784	8.0	0.816	V
FB Input Leakage Current	I _{FB}	V _{FB} =0.8V		-100	-	100	nΑ
		I _{OUT} =600mA, 1.2V≦V _{OUT} <1.5V		-	1400	1500	mV
Dropout Voltage	\/	I_{OUT} =600mA, 1.5V \leq V _{OUT} \leq 2.1V		-	1100	1200	
(Note2)	V _{DROP}	I_{OUT} =600mA, 2.1V $<$ V $_{OUT}$ \leq 2.8V		-	500	600	
		I_{OUT} =600mA, 2.8V $<$ V _{OUT} \le 3.3V		-	300	500	
Current Limit	I _{LIMIT}			700	-	-	mA
Short Circuit Current	I _{Short}	Output Voltage < 0.375*V _{OUT}		-	300	1	mA
Line Regulation	ΔV_{LINE}	V_{IN} =2.6V to 5.5V,	I _{OUT} =1mA	-	0.2	0.5	%
Load Regulation (Note 3)	ΔV_{LOAD}	I _{OUT} =10m~0.6A		-	0.5	1	%
D: 1 D : 1:	PSRR	$C_{IN}=1\mu F$,	F=120Hz	-	65	-	
Ripple Rejection		С _{оит} =1µF, І _{оит} =10mA	F=1KHz	-	55	- dl	dB
Enable Input Threshold	V_{ENH}			1.5	-	-	V
Enable input mirotiola	V _{ENL}			-	-	0.4	V
Enable Pin Current	I _{ENH}	V _{EN} =V _{IN} V _{IN} =3.6V, V _{EN} =0V		-	0.003	0.1	μA
Lilable i ili Gallent	I _{ENL}			-	0.35	1	
Temperature Shutdown	Ts			-	140	-	°C
Temperature Shutdown Hysterisis	T _{SH}			-	30	-	°C


Note1. Minimum V_{IN} voltage is defined by output adds a dropout voltage.

Note2. The dropout voltage is defined as V_{IN}-V_{OUT}, which is measured when V_{OUT} drop about 100mV.


Note3. Regulation is measured at constant junction temperature by using pulsed testing with a low ON time.

*** APPLICATION CIRCUIT**

(1) Fixed Output Voltage Version



(2) Adjustable Output Voltage Version



$$V_{OUT}=V_{FB}*(1+R1/R2)$$

 $V_{FB}=0.8V$
R2 Range=50K~300K



FUNCTION DESCRIPTIONS

A minimum of 1µF capacitor must be connected from V_{OUT} to ground to insure stability. Typically a large storage capacitor is connected from V_{IN} to ground to ensure that the input voltage does not sag below the minimum dropout voltage during the load transient response. This pin must always be dropout voltage higher than V_{OUT} in order for the device to regulate properly.

❖ APPLICATION INFORMATION

Like any low-dropout regulator, the AX6607 requires input and output decoupling capacitors. The device is specifically designed for portable applications requiring minimum board space and smallest components. These capacitors must be correctly selected for good performance. Please note that linear regulators with a low dropout voltage have high internal loop gains which require care in guarding against oscillation caused by insufficient decoupling capacitance.

Capacitor Selection

Normally, use a 1µF capacitor on the input and a 1µF capacitor on the output of the AX6607. Larger input capacitor values and lower ESR (X5R, X7R) provide better supply-noise rejection and transient response. A higher-value output capacitor (2.2µF) may be necessary if large, fast transients are anticipated and the device is located several inches from the power source.

Input-Output (Dropout) Voltage

A regulator's minimum input-to-output voltage differential (dropout voltage) determines the lowest usable supply voltage. In battery-powered systems, this determines the useful end-of-life battery voltage. Because the device uses a PMOS, its dropout voltage is a function of drain-to source on-resistance, R_{DS (ON)}, multiplied by the load current:

$$V_{DROPOUT} = V_{IN} - V_{OUT} = R_{DS(ON)} \times I_{OUT}$$

Current Limit and Thermal Shutdown Protection

In order to prevent overloading or thermal condition from damaging the device, AX6607 regulator has internal thermal and current limiting functions designed to protect the device. It will rapidly shut off PMOS pass element during overloading or over temperature condition.



Thermal Considerations

The AX6607 series can deliver a current of up to 600mA over the full operating junction temperature range. However, the maximum output current must be dated at higher ambient temperature to ensure the junction temperature does not exceed 125°C. With all possible conditions, the junction temperature must be within the range specified under operating conditions. Power dissipation can be calculated based on the output current and the voltage drop across regulator.

$$PD = (V_{IN} - V_{OUT}) I_{OUT}$$

The final operating junction temperature for any set of conditions can be estimated by the following thermal equation:

PD (MAX) =
$$(T_{J (MAX)} - T_A) / \theta_{JA}$$


Where T_{J (MAX)} is the maximum junction temperature of the die (125°C) and T_A is the maximum ambient temperature. The junction to ambient thermal resistance (θ_{JA}) for TDFN-6L package at recommended minimum footprint is 120°C/W.


PCB Layout

An input capacitance of $\approx 1 \mu F$ is required between the AX6607 input pin and ground (the amount of the capacitance may be increased without limit), this capacitor must be located a distance of not more than 1cm from the input and return to a clean analog ground. Input capacitor can filter out the input voltage spike caused by the surge current due to the inductive effect of the package pin and the printed circuit board's routing wire. Otherwise, the actual voltage at the VIN pin may exceed the absolute maximum rating. The output capacitor also must be located a distance of not more than 1cm from output to a clean analog ground. Because it can filter out the output spike caused by the surge current due to the inductive effect of the package pin and the printed circuit board's routing wire.





*** TYPICAL CHARACTERISTICS**

















*** PACKAGE OUTLINES**

TDFN-6L (2*2 0.75mm)










Symbol	Dimensions in Millimeters			Dimensions in Inches			
	Min.	Nom.	Max.	Min.	Nom.	Max.	
А	0.70	0.75	0.80	0.028	0.030	0.031	
A1	0.00	0.02	0.05	0.000	0.001	0.002	
A3	0.203 REF.			0.008 REF.			
b	0.20	0.28	0.35	0.009	0.011	0.013	
D	1.95	2.00	2.05	0.077	0.079	0.081	
D2	1.35	1.50	1.65	0.055	0.059	0.063	
Е	1.95	2.00	2.05	0.077	0.079	0.081	
E2	0.75	0.90	1.05	0.031	0.035	0.039	
е	0.65 BSC.			0.026 BSC.			
Ĺ	0.20	0.30	0.40	0.008	0.012	0.016	

SOT-23-5L (2)





Cumbal	Dime	ensions in Millin	Dimensions in Inches			
Symbol	Min.	Nom.	Max.	Min.	Nom.	Max.
А	-	-	1.45	-	-	0.057
A1	0.00	0.08	0.15	0	0.003	0.006
A2	0.90	1.10	1.30	0.035	0.043	0.051
b	0.30	0.40	0.50	0.012	0.016	0.020
С	0.08	0.15	0.22	0.003	0.006	0.009
D	2.70	2.90	3.10	0.106	0.114	0.122
E1	1.40	1.60	1.80	0.055	0.063	0.071
E	2.60	2.80	3.00	0.102	0.110	0.118
L	0.30	0.45	0.60	0.012	0.018	0.024
L1	0.50	0.60	0.70	0.020	0.024	0.028
e1		1.9 BSC			0.075 BSC	
е	0.95 BSC				0.037 BSC	
θ	0°	4 º	80	00	40	80
θ 1	5∘	10°	15°	5°	10°	15∘
θ2	5∘	10°	15∘	5°	10°	15∘

JEDEC outline: MO-178 AA