
LH1510AAB, LH1510AABTR, LH1510AT

Vishay Semiconductors

1 Form A Solid-State Relay



DESCRIPTION

The LH1510 is an SPST normally open switch (1 form A) that can replace electromechanical relays in many applications. The relay is constructed using a GaAlAs LED for actuation control and an integrated monolithic die for the switch output. The die, fabricated in a high-voltage dielectrically isolated technology, is comprised of a photodiode array, switch control circuity, and MOSFET switches. In addition, the relay employs current-limiting circuity enabling it to pass lightning surge testing as per ANSI/TIA-968-B and other regulatory voltage surge requirements when overvoltage protection is provided. The LH1510 is the only relay in the family that provides current limiting for unidirectional DC applications.

FEATURES

- Isolation test voltage 5300 V_{RMS}
- · Current limit protection built in
- High reliability monolithic output die
- Low power consumption
- · Clean bounce free switching
- · High surge capability
- Surface mountable
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC



- · General telecom switching
- Instrumentation
- Industrial controls

AGENCY APPROVALS

UL1577: file no. E52744 system code H, double protection

CSA: certification no. 093751 BSI: certification no. 7979/7980

DIN EN: 60747-5-2 (VDE 0884)/60747-5-5 (pending),

available with option 1

FIMKO: 25419

ORDERING INFORMATION			
L H 1 5 1 0 # PART NUMBER ELECTR. VARIATION	# # T R PACKAGE TAPE AND REEL 7.62 mm		
PACKAGE	UL, CSA, BSI, FIMKO		
SMD-6, tubes	LH1510AAB		
SMD-6, tape and reel	LH1510AABTR		
DIP-6, tubes	LH1510AT		

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
INPUT				
LED continuous forward current		I _F	50	mA
LED reverse voltage	I _R ≤ 10 μA	V _R	8	V
OUTPUT				
DC or peak AC load voltage	I _L ≤ 50 μA	V_L	200	V
Continuous DC load current - bidirectional operation		IL	200	mA
Continuous DC load current - unidirectional operation		ال	350	mA
Peak load current (single shot)	t = 100 ms	I _P	(1)	



LH1510AAB, LH1510AABTR, LH1510AT

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
SSR					
Ambient temperature range		T _{amb}	- 40 to + 85	°C	
Storage temperature range		T _{stg}	- 40 to + 150	°C	
Pin soldering temperature (2)	t = 10 s max.	T _{sld}	260	°C	
Input to output isolation voltage		V _{ISO}	5300	V_{RMS}	
Output power dissipation (continuous)		P _{diss}	550	mW	

Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
 implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
 maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to current limit performance application note 58 for a discussion on relay operation during transient currents.
- (2) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT						
LED forward current, switch turn-on	$I_L = 100 \text{ mA}, t = 10 \text{ ms}$	I _{Fon}		0.95	2	mA
LED forward current, switch turn-off	$V_{L} = \pm 150 \text{ V}$	I _{Foff}	0.2	0.85		mA
LED forward voltage	I _F = 10 mA	V_{F}	1.15	1.27	1.45	V
OUTPUT						
ON-resistance AC/DC: pin 4 (±) to 6 (±)	$I_F = 5 \text{ mA}, I_L = 50 \text{ mA}$	R _{ON}	6	11.27	15	Ω
ON-resistance DC: pin 4, 6 (+) to 5 (±)	I _F = 5 mA, I _L = 100 mA	R _{ON}	1.5	3.15	3.75	Ω
Off-resistance	$I_F = 0 \text{ mA}, V_L = \pm 100 \text{ V}$	R _{OFF}	0.5	80		GΩ
Current limit AC/DC: pin 4 (±) to 6 (±)	$I_F = 5 \text{ mA}, V_L = \pm 5 \text{ V}, t = 5 \text{ ms}$	I _{LMT}	300	368	450	mA
Current limit DC: pin 4, 6 (+) to 5 (±)	$I_F = 5 \text{ mA}, V_L = \pm 4 \text{ V}, t = 5 \text{ ms}$	I _{LMT}	600	736	920	mA
Off state lookage ourrent	$I_F = 0 \text{ mA}, V_L = \pm 100 \text{ V}$	Io		2.36	200	nA
Off-state leakage current	$I_F = 0 \text{ mA}, V_L = \pm 200 \text{ V}$	Io		79.2	1	μΑ
Output conscitones nin 4 to 6	$I_F = 0 \text{ mA}, V_L = 1 \text{ V}$	Co		27.75		pF
Output capacitance pin 4 to 6	$I_F = 0 \text{ mA}, V_L = 50 \text{ V}$	Co		10.82		pF
Switch offset	I _F = 5 mA	V _{OS}		0.17		μV
TRANSFER						
Capacitance (input to output)	V _{ISO} = 1 V	C _{IO}		0.72		pF

Note

• Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

SWITCHING CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Turn-on time	$I_F = 5 \text{ mA}, I_L = 50 \text{ mA}$	t _{on}		0.5	2	ms
Turn-off time	$I_F = 5 \text{ mA}, I_L = 50 \text{ mA}$	t _{off}		0.7	2	ms



PARAMETER		TEST CONDITION	SYMBOL	VALUE	UNIT
Climatic classification		IEC 68 part 1		40/85/21	
Pollution degree		DIN VDE 0109		2	
Tracking resistance (comparative tracking index	()	Insulation group IIIa	СТІ	175	
Highest allowable overvolta	age	Transient overvoltage	V _{IOTM}	8000	V _{peak}
Max. working insulation vol	tage	Recurring peak voltage	V _{IORM}	890	V _{peak}
Insulation resistance at 25 °C			R _{IS}	≥ 10 ¹²	Ω
Insulation resistance at T _S		V _{IO} = 500 V	R _{IS}	≥ 10 ⁹	Ω
Insulation resistance at 100 °C			R _{IS}	≥ 10 ¹¹	Ω
Partial discharge test voltage	ge	Methode a, V _{pd} = V _{IORM} x 1.875	V_{pd}	1669	V _{peak}
Safety limiting values -	Case temperature		T _{SI}	175	°C
maximum values allowed	Input current		I _{SI}	300	mA
in the event of a failure	Output power		P _{SO}	700	mW
Minimum external air gap (clearance)		Measured from input terminals to output terminals, shortest distance through air		≥ 7	mm
Minimum external tracking (creepage)		Measured from input terminals to output terminals, shortest distance path along body		≥ 7	mm

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Recommended Operating Conditions




Fig. 2 - LED Voltage vs. Temperature




Fig. 3 - LED Forward Current vs. LED Forward Voltage




Fig. 4 - LED Reverse Current vs. LED Reverse Voltage




Fig. 5 - LED Current vs. Load Voltage




Fig. 6 - LED Current for Switch Turn-on vs. Temperature




Fig. 7 - LED Dropout Voltage vs. Temperature




Fig. 8 - DC Load Current vs. Load Voltage




Fig. 9 - DC Current Limit vs. Temperature




Fig. 10 - Current Limit vs. Temperature




Fig. 11 - Load Current vs. Load Voltage




Fig. 12 - On-Resistance vs. Temperature




Fig. 13 - Variation in On-Resistance vs. LED Current




Fig. 14 - Switch Terminal Capacitance vs. Applied Voltage




Fig. 15 - Insertion Loss vs. Frequency




Fig. 16 - Leakage Current vs. Applied Voltage




Fig. 17 - Output Isolation




Fig. 18 - Switch Breakdown Voltage vs. Load Current




Fig. 19 - Switch Breakdown Voltage vs. Temperature




Fig. 20 - Switch Offset Voltage vs. Temperature




Fig. 21 - Switch Offset Voltage vs. LED Current




Fig. 22 - Turn-on Time vs. Temperature




Fig. 23 - Turn-off Time vs. Temperature




Fig. 25 - Turn-off Time vs. LED Current





Fig. 24 - Turn-on Time vs. LED Current


i178001

PACKAGE DIMENSIONS in millimeters



LH1510AAB, LH1510AABTR, LH1510AT

Vishay Semiconductors



PACKAGE MARKING



Note

• Tape and reel suffix (TR) is not part of the package marking.






Footprint and Schematic Information for LH1510AAB, LH1510AABTR, LH1510AT

The footprint and schematic symbols for the following parts can be accessed using the associated links. They are available in Eagle, Altium, KiCad, OrCAD / Allegro, Pulsonix, and PADS.

Note that the 3D models for these parts can be found on the Vishay product page.

PART NUMBER	FOOTPRINT / SCHEMATIC	
LH1510AAB	www.snapeda.com/parts/LH1510AAB/Vishay/view-part	
LH1510AABTR	www.snapeda.com/parts/LH1510AABTR/Vishay/view-part	
LH1510AT	www.snapeda.com/parts/LH1510AT/Vishay/view-part	

For technical issues and product support, please contact optocoupleranswers@vishay.com.





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.