


Vishay Semiconductors

Small Signal Switching Diode, Dual in Series



MECHANICAL DATA


Case: SOT-23

Weight: approx. 8.8 mg
Packaging codes/options:

18/10K per 13" reel (8 mm tape), 10K/box 08/3K per 7" reel (8 mm tape), 15K/box

FEATURES

- Fast switching speed
- High conductance





- Connected in series
- AEC-Q101 qualified
- Base P/N-E3 RoHS-compliant, commercial grade
- Base P/N-HE3 RoHS-compliant, AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

PARTS TABLE					
PART	ORDERING CODE	INTERNAL CONSTRUCTION	TYPE MARKING	REMARKS	
BAV99	BAV99-E3-08 or BAV99-E3-18	Dual diodes serial	JE	Tape and reel	
	BAV99-HE3-08 or BAV99-HE3-18	Dual diodes serial	JE		

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Non repetitive peak reverse voltage		V_{RM}	100		
Repetitive peak reverse voltage = working peak reverse voltage = DC blocking voltage		$V_{RRM} = V_{RWM} = V_{R}$	70	V	
Peak forward surge current	t _p = 1 s		1	Α	
reak lorward surge current	t _p = 1 μs	IFSM	4.5	7	
Average forward current	Half wave rectification with resistive load and f ≥ 50 MHz, on ceramic substrate 10 mm x 8 mm x 0.7 mm	I _{F(AV)}	150	mA	
Forward current	On ceramic substrate 10 mm x 8 mm x 0.7 mm	l _F 250			
Power dissipation	On ceramic substrate 10 mm x 8 mm x 0.7 mm	P _{tot}	300	mW	

THERMAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Junction ambient	On ceramic substrate 10 mm x 8 mm x 0.7 mm	R _{thJA}	430	K/W		
Junction and storage temperature range		$T_j = T_{stg}$	- 55 to + 150	°C		
Operating temperature range		T _{op}	- 55 to + 150	°C		



Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
	I _F = 1 mA	V _F			0.715	V
Forward voltage	I _F = 10 mA				0.855	V
Forward voltage	I _F = 50 mA				1	V
	I _F = 150 mA				1.25	V
	V _R = 70 V	I _R			2500	nA
Reverse current	V _R = 70 V, Tj = 150 °C				50	μA
	V _R = 25 V, Tj = 150 °C				30	μA
Diode capacitance	V _R = 0, f = 1 MHz	C _D			1.5	pF
Reverse recovery time	I_F = 10 mA to i_R = 1 mA, V_R = 6 V, R_L = 100 Ω	t _{rr}			6	ns

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Forward Voltage






Fig. 2 - Peak forward current $f_{FM} = f(t_p)$

LAYOUT FOR RthJA TEST


Thickness: Fiberglass 1.5 mm (0.059 inches) Copper leads 0.3 mm (0.012 inches)









PACKAGE DIMENSIONS in millimeters (inches): SOT-23






Document no.: 6.541-5014.01-4 Rev. 8 - Date: 23.Sept.2009 17418



Foot print recommendation:





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.