


Description

The enhancement mode MOS is extremely high density cell and low on-resistance.

MOSFET Product Summary		
$V_{DS}(V)$	$R_{DS(on)}(\Omega)$	$I_D(A)$
-12	0.045 @ $V_{GS}=-4.5V$	-4.3



Absolute maximum rating@25°C

Rating		Symbol	Value	Units
Drain-Source Voltage		V_{DS}	-12	V
Gate-Source Voltage		V_{GS}	± 8.0	V
Drain Current	Continuous $T_A=25^\circ C$	I_D	-4.3	A
	Pulsed $T_A=70^\circ C$	I_D	-3.4	A
Pulsed Drain Current		I_{DM}	-34	A
Total Power Dissipation	$T_A=25^\circ C$	P_D	1.3	W
	$T_A=125^\circ C$	P_D	0.8	W
Linear Derating Factor			0.01	W/°C
Single Pulse Avalanche Energy		E_{AS}	33	mJ
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to +150	°C


Thermal resistance

Parameter	Symbol	Typ.	Max.	Units
Maximum Junction-to-Ambient	$R_{\theta JA}$	75	100	°C/W

Electrical characteristics per line@25°C (unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Drain-Source Breakdown Voltage	BV_{DSS}	$I_D = -250\mu A, V_{GS} = 0V$	-12	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = -12V, V_{GS} = 0V$	-	-	-1.0	μA
Gate-to-Source Forward Leakage	I_{GSS}	$V_{GS} = -8.0V$	-	-	-100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\mu A$	-0.45	-0.7	-1.0	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS} = -4.5V, I_D = -4.3A$	-	-	0.045	Ω
		$V_{GS} = -2.5V, I_D = -2.5A$	-	-	0.060	Ω
		$V_{GS} = -1.8V, I_D = -2.0A$	-	-	0.100	Ω
Forward Trans conductance	g_{FS}	$V_{DS} = -10V, I_D = -4.3A$	8.6	-	-	S
Total Gate Charge	Q_g	$I_D = -4.3A, V_{DS} = -10V, V_{GS} = -5.0V$	-	7.8	-	nC
Gate-to-Source Charge	Q_{gs}		-	1.4	-	
Gate-to-Drain(Miller) Charge	Q_{gd}		-	1.6	-	
Input Capacitance	C_{ISS}	$V_{GS} = 0V, V_{DS} = -10V, f = 1MHz$	-	750	-	pF
Output Capacitance	C_{DSS}		-	230	-	pF
Reverse Transfer Capacitance	C_{RSS}		-	160	-	pF
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -6.0V, I_D = -1.0A, R_D = 6.0\Omega, R_G = 89\Omega$	-	11	-	ns
Rise Time	t_r		-	32	-	
Turn-Off Delay Time	$t_{d(off)}$		-	250	-	
Fall Time	t_f		-	210	-	

Source-Drain Rating and Characteristics

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode 	-	-	-1.6	A
Diode Forward Voltage	V_{SD}	$T_J = 25^\circ C, I_S = -1.3A, V_{GS} = 0V$	-	-	-1.2	V
Reverse Recovery Time	t_{rr}	$T_J = 25^\circ C, I_F = -1.3A, di/dt = -100A/\mu s$	-	22	33	ns
Reverse Recovery Charge	Q_{rr}		-	8.0	12	nC

Typical Characteristics




Fig 1. Typical output characteristics




Fig 2. Typical output characteristics




Fig 3. Typical transfer characteristics




Fig 4. Normalized On-Resistance vs, Temperature




Fig 5. Typical Capacitance vs. Drain-to-Source voltage




Fig 6. Typical Gate Charge vs. Gate-to-Source voltage




Fig 7. Typical Source-Drain Diode Forward Voltage




Fig 8. Maximum Safe Operating Area




Fig 9. Maximum Drain Current vs. Case Temperature




Fig 10. Maximum Avalanche Energy vs. Drain Current




Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient




Fig 12. Typical On-Resistance vs. Gate Voltage




Fig 13. Typical On-Resistance vs. Drain Current






Fig14. Typical Threshold Voltage vs. Junction Temperature

Product dimension(SOT-23)



Dim	Millimeters		Inches	
	MIN	MAX	MIN	MAX
A	2.80	3.00	0.1102	0.1197
B	1.20	1.40	0.0472	0.0551
C	2.10	2.50	0.0830	0.0984
D	0.89	1.02	0.0350	0.0401
E	0.45	0.60	0.0177	0.0236
F	1.78	2.04	0.0701	0.0807
G	0.085	0.177	0.0034	0.0070
H	0.45	0.60	0.0180	0.0236
J	0.37	0.50	0.0150	0.0200
K	0.89	1.11	0.0350	0.0440
L	0.013	0.100	0.0005	0.0040
θ	0°	10°	0°	10°


IMPORTANT NOTICE

 and **Prisemi**[®] are registered trademarks of **Prisemi Electronics Co., Ltd (Prisemi)** ,Prisemi reserves the right to make changes without further notice to any products herein. Prisemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Prisemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. “Typical” parameters which may be provided in Prisemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including “Typicals” must be validated for each customer application by customer’s technical experts. Prisemi does not convey any license under its patent rights nor the rights of others. The products listed in this document are designed to be used with ordinary electronic equipment or devices, Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Website: <http://www.prisemi.com>

For additional information, please contact your local Sales Representative.

©Copyright 2009, Prisemi Electronics

 **Prisemi**[®] is a registered trademark of Prisemi Electronics.

All rights are reserved.