# UNISONIC TECHNOLOGIES CO., LTD


MBR30100C


# 30A SCHOTTKY BARRIER RECTIFIER

#### **■ FEATURES**

- \* 30 amps total (15 amps per diode leg)
- \* Guard ring for transient protection
- \* Low forward voltage drop
- \* High surge capability
- \* Low power loss/High efficiency

#### ■ SYMBOL







#### **■ ORDERING INFORMATION**

Ordering Number		Dookogo	Pin Assignment			Dooking	
Lead Free	Halogen Free	Package	1	2	3	Packing	
MBR30100CL-TA3-T	MBR30100CG-TA3-T	TO-220	Α	K	Α	Tube	
MBR30100CL-TF3-T	MBR30100CG-TF3-T	TO-220F	Α	K	Α	Tube	
MBR30100CL-TF1-T	MBR30100CG-TF1-T	TO-220F1	Α	K	Α	Tube	
MBR30100CL-T3P-T	MBR30100CG-T3P-T	TO-3P	Α	K	Α	Tube	
MBR30100CL-T47-T	MBR30100CG-T47-T	TO-247	Α	K	Α	Tube	
MBR1060CL-TQ2-T	MBR1060CG-TQ2-T	TO-263	Α	K	Α	Tube	
MBR1060CL-TQ2-R	MBR1060CG-TQ2-R	TO-263	Α	K	Α	Tape Reel	

Note: Pin Assignment: A: Anode K: Cathode



### ■ MARKING



<u>www.unisonic.com.tw</u> 1 of 3

MBR30100C

# ■ **ABSOLUTE MAXIMUM RATINGS** (T<sub>A</sub>=25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Maximum Repetitive Peak Reverse Voltage		$V_{RRM}$	100	V
Maximum non-repetitive Peak Reverse Voltage		$V_{RM}$	100	V
Maximum DC Blocking Voltage		$V_R$	100	V
Average Forward Rectified Output Current	Per Leg		15	Α
	Total	I <sub>O</sub>	30	Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half-Sine-Wave		I <sub>FSM</sub>	275	А
Junction Capacitance (Note 3)		CJ	300	pF
Operating Temperature		T <sub>J</sub>	-65 ~ <b>+</b> 150	°C
Storage Temperature		$T_{STG}$	-65 ~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

#### **■ THERMAL DATA**

PARAMETER		SYMBOL	RATINGS	UNIT	
Junction to Ambient	TO-220/TO-220F TO-220F1/TO-263	•	62.5	°C/W	
	TO-3P	$\theta_{JA}$	29		
	TO-247		35		
Junction to Case	TO-220/TO-263		2		
	TO-220F/TO-220F1	0	5	°C/W	
	TO-3P	$\theta_{ extsf{JC}}$	1.5		
	TO-247		1.45		

# **■ ELECTRICAL CHARACTERISTICS**


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Instantaneous Forward Voltage Drop (Note 2)	V <sub>F</sub>	I <sub>F</sub> =15A, T <sub>C</sub> =25°C			0.85	V
		I <sub>F</sub> =15A, T <sub>C</sub> =125°C			0.75	٧
		I <sub>F</sub> =30A, T <sub>C</sub> =25°C			1.10	V
		I <sub>F</sub> =30A, T <sub>C</sub> =125°C			1.05	٧
Instantaneous Reverse Current (Note 2)	l <sub>D</sub>	Rated DC Voltage, T <sub>C</sub> =25°C			100	μΑ
		Rated DC Voltage, T <sub>C</sub> =125°C			20	mA


Notes: 1. 2.0µs Pulse Width, f = 1.0 KHz


- 2. Pulse Test: Pulse Width ≤ 300µs, Duty Cycle ≤ 2.0%
- 3. Applied  $V_R$  = 4.0V and f = 1.0 MHz

MBR30100C

#### ■ TYPICAL CHARACTERISTICS







UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.