# Surface Mount Fuses

# Ceramic Fuse > 438 Series


# 438 Series - 0603 Fast-Acting Fuse











# **Agency Approvals**

AGENCY	AGENCY FILE NUMBER	AMPERE RANGE
<b>71</b> 2	E10480	0.250A – 6A
<b>⊕</b> ;	29862	0.250A – 6A

#### **Electrical Characteristics for Series**

% of Ampere Rating	Ampere Rating	Opening Time at 25°C
100%	0.250A – 6A	4 Hours, Minimum
250%	0.250A – 6A	5 Seconds, Maximum

### **Description**

The 438 Series is a 100% Lead-free, RoHS compliant and Halogen-free fuse series designed specifically to provide over-current protection to circuits that operate under high working ambient temperature up to 150°C.

The general design ensures excellent temperature stability and performance reliability.

The high I<sup>2</sup>t values which is typical in the Littelfuse Ceramic Fuse family ensure high inrush current withstand capability.

#### **Features**

- Operating Temperature from -55°C to +150°C
- 100% Lead-free, RoHS compliant and Halogen-
- Suitable for both leaded and lead-free reflow / wave soldering

### **Applications**

- Handheld Electronics
- LCD Displays
- Battery Packs
- · Hard Disk Drives
- SD Memory Cards

### **Additional Information**









# Electrical Specifications by Item

Ampere	٨	Max.		Nominal	Nominal	Nominal Voltage	Nominal Power	Agency A	Approvals
Rating (A)	Amp Code	Voltage Rating (V)	Interrupting Rating	Resistance (Ohms) <sup>2</sup>	Melting I <sup>2</sup> t (A <sup>2</sup> Sec.) <sup>3</sup>	Drop At Rated Current (V) <sup>4</sup>	Dissipation At Rated Current (W)	<i>71</i> 2	<b>®</b> ;
0.25	.250	63VDC		2.218	0.0017	0.550	0.138	Х	Х
0.375	.375	63VDC		1.247	0.0041	0.488	0.183	X	X
0.5	.500	63VDC		0.829	0.0100	0.486	0.243	X	X
0.75	.750	63VDC	50A @ 63VDC	0.466	0.0281	0.378	0.284	Х	х
1	001.	63VDC	50A @ 32VAC	0.310	0.0593	0.351	0.351	X	Х
1.25	1.25	63VDC		0.200	0.0510	0.365	0.456	Х	Х
1.5	01.5	63VDC		0.174	0.0902	0.368	0.552	X	X
1.75	1.75	63VDC		1.405	0.1440	0.360	0.540	X	Х
2	002.	32		0.051	0.1490	0.107	0.214	Х	Х
2.5	02.5	32		0.0324	0.1977	0.095	0.238	X	х
3	003.	32	50A @ 32VDC/12VAC	0.0255	0.2922	0.093	0.279	X	Х
3.5	03.5	32		0.0205	0.4752	0.082	0.287	X	X
4	004.	32		0.0170	0.6920	0.079	0.316	Х	Х
5	005.	32		0.0115	0.7398	0.074	0.370	Х	Х
6	006.	24	50A @ 24VDC/12VAC	0.0085	1.3838	0.072	0.432	X	X


- 1. AC Interrupting Rating tested at rated voltage with unity power factor. DC Interrupting Rating tested at rated voltage with time constant < 0.8 msec.
- 2. Nominal Resistance measured with < 10% rated current.
- 3. Nominal Melting I2t measured at 1 msec. opening time.
- 4. Nominal Voltage Drop measured at rated current after temperature has stabilized

Devices designed to carry rated current for 4 hours minimum. It is recommended that devices be operated continuously at no more than 80% rated current. See "Temperature Re-rating Curve" for additional re-rating information.

Devices designed to be mounted with marking code facing up.



# **Temperature Re-rating Curve**




#### Note:

1. Re-rating depicted in this curve is in addition to the standard re-rating of 20% for continuous operation.

#### Example:

For continuous operation at 75 degrees celsius, the fuse should be rerated as follows:  $I=(0.80)(0.85)I_{RAT}=(0.68)I_{RAT}$ 


# **Average Time Current Curves**



# **Soldering Parameters**

Reflow Condition		Pb – free assembly
	-Temperature Min (T <sub>s(min)</sub> )	150°C
Pre Heat	-Temperature Max (T <sub>s(max)</sub> )	200°C
	-Time (Min to Max) (t <sub>s</sub> )	60 – 180 seconds
Average F (T <sub>L</sub> ) to pea	Ramp-up Rate (Liquidus Temp ak)	3°C/second max.
T <sub>S(max)</sub> to T	L - Ramp-up Rate	5°C/second max.
Dofland	-Temperature (T <sub>L</sub> ) (Liquidus)	217°C
Reflow	-Temperature (t <sub>L</sub> )	60 – 150 seconds
PeakTemp	perature (T <sub>P</sub> )	260+0/-5 °C
Time within 5°C of actual peak Temperature (t <sub>p</sub> )		10 – 30 seconds
Ramp-down Rate		6°C/second max.
Time 25°C	to peakTemperature (T <sub>P</sub> )	8 minutes max.
Do not ex	ceed	260°C

Wave Soldering	260°C, 10 seconds max.
----------------	------------------------






### **Product Characteristics**

Materials	Body: Advanced Ceramic Terminations: Ag / Ni / Sn (100% Lead-free) Element Cover Coating: Lead-free Glass	
Moisture Sensitivity Level	IPC/JEDEC J-STD-020, Level 1	
Solderability	IPC/EIC/JEDEC J-STD-002, Condition B	
Humidity	MIL-STD-202, Method 103, Conditions D	
Resistance to Solder Heat	MIL-STD-202, Method 210, Condition B	

Moisture Resistance	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B-3
Mechanical Shock	MIL-STD-202, Method 213, Condition A
Vibration	MIL-STD-202, Method 201
Vibration, High Frequency	MIL-STD-202, Method 204, Condition D
Dissolution of Metallization	IPC/EIC/JEDEC J-STD-002, Condition D
Terminal Strength	IEC 60127-4

#### **Dimensions**




# Part Marking System

Amp Code	Marking Code
.250	D
.375	E
.500	F
.750	G
001.	Н
1.25	J
01.5	К
1.75	L

Marking Code	Amp Code
N	002.
0	02.5
Р	003.
R	03.5
S	004.
Т	005.
U	006.

## **Part Numbering System**



# **Packaging**

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
8mm Tape and Reel	EIA-481, IEC 60286, Part 3	3000	WR

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <a href="https://www.littelfuse.com/disclaimer-electronics">www.littelfuse.com/disclaimer-electronics</a>.