

## Schottky Barrier Rectifiers

Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. The proprietary barrier technology allows for reliable operation up to 175°C junction temperature. Typical application are in switching Mode Power Supplies such as adaptors, DC/DC converters, free-wheeling and polarity protection diodes.

### Features.


- \* Low Forward Voltage.
- \* Low Switching noise.
- \* High Current Capacity
- \* Guarantee Reverse Avalanche.
- \* Guard-Ring for Stress Protection.
- \* Low Power Loss & High efficiency.
- \* 175°C Operating Junction Temperature
- \* Low Stored Charge Majority Carrier Conduction.
- \* Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O




\* In compliance with EU RoHS 2002/95/EC directives

### SCHOTTKY BARRIER RECTIFIERS

**20 AMPERES  
150 VOLTS**



**TO-220AB**



DIM	MILLIMETERS	
	MIN	MAX
A	14.68	15.32
B	9.78	10.42
C	5.02	6.52
D	13.06	14.62
E	3.57	4.07
F	2.42	2.66
G	1.12	1.36
H	0.72	0.96
I	4.22	4.98
J	1.14	1.38
K	2.20	2.98
L	0.33	0.55
M	2.48	2.98
O	3.70	3.90

### MAXIMUM RATINGS


Characteristic	Symbol	MBR20150CT	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	$V_{RRM}$ $V_{RWM}$ $V_R$	150	V
RMS Reverse Voltage	$V_{R(RMS)}$	105	V
Average Rectifier Forward Current (per diode) Total Device (Rated $V_R$ ), $T_C=125^\circ\text{C}$	$I_{F(AV)}$	10 20	A
Peak Repetitive Forward Current (Rate $V_R$ , Square Wave, 20kHz)	$I_{FM}$	20	A
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfwave, single phase, 60Hz)	$I_{FSM}$	150	A
Operating and Storage Junction Temperature Range	$T_J, T_{stg}$	-65 to +175	$^\circ\text{C}$

### THERMAL RESISTANCES

Typical Thermal Resistance junction to case	$R_{\theta jc}$	3.6	$^\circ\text{C}/\text{w}$
---	-----------------	-----	---------------------------

### ELECTRIAL CHARACTERISTICS

Characteristic	Symbol	MBR20150CT	Unit
Maximum Instantaneous Forward Voltage ( $I_F=10$ Amp $T_C=25^\circ\text{C}$ ) ( $I_F=10$ Amp $T_C=125^\circ\text{C}$ )	$V_F$	0.95 0.85	V
Maximum Instantaneous Reverse Current (Rated DC Voltage, $T_C=25^\circ\text{C}$ ) (Rated DC Voltage, $T_C=125^\circ\text{C}$ )	$I_R$	0.01 10	mA



# MBR20150CT

FIG-1 FORWARD CURRENT DERATING CURVE




FIG-2 TYPICAL FORWARD CHARACTERISTICS




FIG-3 TYPICAL REVERSE CHARACTERISTICS




FIG-4 TYPICAL JUNCTION CAPACITANCE




FIG-5 PEAK FORWARD SURGE CURRENT

