







60V N-CHANNEL ENHANCEMENT MODE VERTICAL DMOSFET


Features


- BV_{DSS} > 60V
- $R_{DS(on)} \le 5\Omega$ @ $V_{GS} = 10V$
- I_D = 270mA Maximum Continuous Drain Current
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability


Mechanical Data

- Case: E-Line (TO-92 Compatible)
- Case Material: Molded Plastic, "Green" Molding Compound UL Flammability Rating 94V-0
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.159 grams (Approximate)









Flat Face View


Device Symbol

Ordering Information (Note 4)

Product	Marking	Package	Leads	Quantity
VN10LP	VN10LP	E-Line	Straight	4,000 Loose in a Box
VN10LPSTZ	VN10LP	E-Line	Joggled	2,000 Taped per Ammo Box

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and
- <1000ppm antimony compounds.</p>
 4. For packaging details, go to our website at http"//www.diodes.com/products/packages.html.

Marking Information



VN10LP = Product Type Marking Code



VN10LP

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	60	V
Gate-Source Voltage	V_{GSS}	±20	V
Continuous Drain Current	I _D	270	mA
Pulsed Drain Current	I _{DM}	3	Α

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Value	Unit	
Power Dissipation	(Note 5)	P _D	625	mW	
Thermal Resistance, Junction to Ambient	(Note 5)	R _{0JA}	200	°C/W	
Thermal Resistance, Junction to Leads	(Note 6)	R _{0JL}	71	°C/W	
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C		

Notes:

- 5. For a through-hole device mounted on the minimum recommended pad layout with 12mm lead length from the bottom of package to the single-sided FR4 PCB; device is measured under still air conditions whilst operating in a steady-state.
- 6. Thermal resistance from junction to solder-point at the seating plane (2.5mm from the bottom of package along the drain lead).

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage	BV _{DSS}	60	_	_	V	$I_D = 250 \mu A, V_{GS} = 0 V$	
Zero Gate Voltage Drain Current		_	_	10	μΑ	$V_{DS} = 60V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS							
On state Drain Current (Note 7)	I _{D(on)}	750	_	_	mA	V _{DS} =15 V, V _{GS} =10V	
Gate Threshold Voltage	$V_{GS(th)}$	0.8	_	2.5	V	$I_D = 1 \text{mA}, V_{DS} = V_{GS}$	
Static Drain-Source On-Resistance (Note 7)	7) —	_	5.0	()	$V_{GS} = 10V, I_D = 500mA$	
Static Drain-Source On-Resistance (Note 1)	R _{DS} (ON)			7.5		$V_{GS} = 5V, I_D = 200mA$	
Forward Transconductance (Notes 7 & 9)	g _{fs}	100	_	_	mS	V _{DS} = 15V, I _D = 500mA	
DYNAMIC CHARACTERISTICS (Note 9)							
Input Capacitance	C _{iss}	_	_	60		.,	
Output Capacitance	Coss	_	_	25	pF	$V_{DS} = 25V$, $V_{GS} = 0V$ f = 1.0MHz	
Reverse Transfer Capacitance	C _{rss}	_		5			
Turn-On Time (Note 8)	t _(on)	_	_	10	V 45V 1 200 A		
Turn-Off Time (Note 8)	t _(off)	_		10	ns	$V_{DD} = 15V, I_D = 600mA$	


Notes:

- 7. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.
- 8. Switching characteristics are independent of operating junction temperature. Switching times are measured with 50ohm source impedance and <5ns rise time on a pulse generator.</p>
 9. For design aid only, not subject to production testing.




VN10LP


Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)




Saturation Characteristics



Voltage Saturation Characteristics




Vgs-Gate Source Voltage (Volts)




Vgs-Gate Source Voltage (Volts)

Transfer Characteristics



Normalised RDS(on) and VGS(th) vs Temperature

On-resistance vs gate-source voltage



ID(on) - Drain Current (Amps)


Transconductance v drain current





Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.



E-Line					
Dim	Min	Max	Тур		
Α	2.16	2.41	-		
b	0.41	0.495	_		
b1	0.41	0.495	-		
D	4.37	4.77	_		
Е	3.61	4.01	-		
е	-	-	1.27		
e2	_	_	2.54		
F	_	2.50	_		
L	13.00	13.97	_		
L1	2.50	3.50	_		
All Dimensions in mm					





VN10LP

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2014, Diodes Incorporated

www.diodes.com