# UTC UNISONIC TECHNOLOGIES CO., LTD


# BC817

# **NPN SILICON TRANSISTOR**

# **NPN GENERAL PURPOSE AMPLIFIER**

#### **DESCRIPTION**


The UTC BC817 is designed for general purpose medium power amplifiers and switches requiring collector currents to 1.2A.



#### ORDERING INFORMATION

Ordering Number	Package	Pin Assignment			Dealing	
Ordering Number		1	2	3	Packing	
BC817G-xx-AE3-R	SOT-23	E	В	С	Tape Reel	
BC817G-xx-AL3-R	SOT-323	E	В	С	Tape Reel	

Note: Pin Assignment: C: Collector B: Base E: Emitter



### **MARKING**

BC817-16	BC817-25	BC817-40		
E-B-				
6AG	6BG	6CG		

www.unisonic.com.tw 1 of 4

## ■ **ABSOLUTE MAXIMUM RATINGS** (T<sub>A</sub>=25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT
Collector-Base Voltage		$V_{\sf CES}$	50	٧
Collector-Emitter Voltage		$V_{\sf CEO}$	45	٧
Emitter-Base Voltage		$V_{EBO}$	5.0	٧
Callacter Current Centinuous	Continuous	Ic	1.5	Α
Collector Current -Continuous	Peak	I <sub>CM</sub>	1.7	Α
Callactor Dissination	SOT-23	P <sub>C</sub>	310	mW
Collector Dissipation	SOT-323		200	mW
Junction Temperature		$T_J$	+150	°C
Storage Temperature		$T_{STG}$	-65 ~ +150	°C

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.


# ■ **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub>=25°C, unless otherwise specified)


SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT		
OFF CHARACTERISTICS							
$BV_CEO$	I <sub>C</sub> =10mA, I <sub>B</sub> =0	45			V		
BV <sub>CES</sub>	$I_{C}=100\mu A, I_{E}=0$	50			V		
$BV_{EBO}$	$I_E=10\mu A, I_C=0$	5			V		
I <sub>CBO</sub>	V <sub>CB</sub> =20V			100	nA		
	V <sub>CB</sub> =20V,T <sub>A</sub> =150°C			5	μΑ		
I <sub>CEO</sub>	V <sub>CE</sub> =45V			100	nA		
I <sub>EBO</sub>	V <sub>EB</sub> =5V			100	nA		
ON CHARACTERISTICS							
h <sub>FE1</sub>	I <sub>C</sub> =100mA, V <sub>CE</sub> =1.0V	See Classification		tion			
h <sub>FE2</sub>	I <sub>C</sub> =500mA, V <sub>CE</sub> =1.0V	40					
$V_{CE(SAT)}$	I <sub>C</sub> =500mA, I <sub>B</sub> =50mA			0.7	V		
$V_{BE(SAT)}$	I <sub>C</sub> =500mA, I <sub>B</sub> =50mA			1.2	٧		
$V_{BE(ON)}$	I <sub>C</sub> =500mA, V <sub>CE</sub> =1.0V			1.2	V		
	BVCEO BVCES BVEBO ICBO ICEO IEBO  hFE1 hFE2 VCE(SAT) VBE(SAT)	BV <sub>CEO</sub>	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$		


# ■ CLASSIFICATION OF h<sub>FE1</sub>


RANK	16	25	40
RANGE	100-250	160-400	250-600


#### **■ TYPICAL CHARACTERISTICS**



















Collector-Base Capacitance vs.

## **■ TYPICAL CHARACTERISTICS(Cont.)**





UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.