TOSHIBA photocoupler GaAlAs IRed & Photo IC

TLP2631


Isolated Line Receiver
Simplex / Multiplex Data Transmission
Computer-Peripheral Interface
Microprocessor System Interface
Digital Isolation for A / D, D / A Conversion

The TOSHIBA TLP2631 dual photocoupler consists of a pair of GaAlAs light emitting diode and integrated high gain, high speed photodetector. This unit is 8-lead DIP.

The output of the detector circuit is an open collector, Schottky clamped transistor.

A Faraday shield integrated on the photodetector chip reduces the effects of capacitive coupling between the input LED emitter and the high gain stages of the detector. This provides an effective common mode transient immunity of $1000~V/\mu s$.

- Input current threshold: $I_F = 5 \text{ mA (max)}$
- Switching speed: 10MBd (typ.)
- Common mode transient immunity: ±1000 V/µs (min)
- Guaranteed performance over temperature: 0 to 70°C
- Isolation voltage: 2500 V_{rms} (min)
- UL recognized: UL1577, file no. E67349
- cUL approved :CSA Component Acceptance Service No. 5A, File No.E67349




Weight: 0.54 g (typ.)

Truth Table (positive logic)


Input	Output
Н	Ţ//
L	Н

Schematic



A 0.01 to $0.1\mu F$ bypass capacitor must be connected between pins 8 and 5(see Note 1).

Pin Configuration (top view)



Start of commercial production 1986-03

Absolute Maximum Ratings (no derating required up to 70°C)

	Characteristic	Symbol	Rating	Unit	
	Forward current (each channel)	lF	20	mA	
	Pulse forward current (each channel)*	IFP	30	mA	
LED	Reverse voltage (each channel)	VR	5	V	
٦	Input power dissipation(each channel)	PD	25	mW	
	Input power dissipation derating (Ta ≥ 70°C) (each channel)	ΔPD/°C	-0.45	mW/°C	
Detector	Output current (each channel)	lo	16	mA	
	Output voltage (each channel)	Vo	−0.5 to 7	v	
	Supply voltage (1 minute maximum)	Vcc	7	Vy	
	Output collector power dissipation (each channel)	Po	40	mW	
	Output power dissipation derating (Ta ≥ 70°C) (each channel)	ΔΡΟ/°C	-0.75	mW/°C	
Stora	Storage temperature range		-55 to 125	°C <	
Opera	ating temperature range	Topr	-40 to 85	°C	
Lead	soldering temperature (10s)**	Tsol	260	6	
	ion voltage 1 minute, R.H.≤ 60%, Ta=25°C (Note 3)	BVs	2500	Vrms	

Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

- * t ≤ 1 msec duration.
- ** 2mm below seating plane.

Recommended Operating Conditions

Characteristic	Symbol	Min	Тур.	Max	Unit
Input current, low level, each channel	IFL	0	_	250	μΑ
Input current, high level, each channel	I _{FH}	6.3*	_	20	mA
Supply voltage**	Vcc	4.5	5	5.5	V
Fan out (TTL load, each channel)	N	_	_	8	
Operating temperature	T _{opr}	0	_	70	°C

Note: Recommended operating conditions are given as a design guideline to obtain expected performance of the device. Additionally, each item is an independent guideline respectively. In developing designs using this product, please confirm specified characteristics shown in this document.

- * 6.3mA is a guard banded value which allows for at least 20% CTR degradation. Initial input current threshold value is 5.0 mA or less.
- ** This item denotes operating ranges, not meaning of recommended operating conditions.

Electrical Characteristics (Ta = 0 to 70°C unless otherwise noted)

Characteristic	Symbol	Test Condition	Min	Тур. *	Max	Unit
Input forward voltage (each channel)	VF	I _F = 10mA, Ta = 25°C	_	1.65	1.75	V
Input diode temperature coefficient (each channel)	ΔV _F / ΔTa	I _F = 10mA		-2.0	-	mV / °C
Input reverse breakdown voltage (each channel)	BV _R	I _R = 10μA, Ta = 25°C	5	7	_	V
Input capacitance (each channel)	Ст	V _F = 0V, f = 1MHz		45	1	pF
High level output current (each channel)	Іон	V _{CC} = 5.5V, V _O = 5.5V I _F = 250μA	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	1	250	μА
Low level output voltage (each channel)	VoL	V _{CC} = 5.5V, I _F = 5mA I _{OL} (sinking) = 13mA	9_	0.4	0.6	V
High level supply current (both channels)	Іссн	V _{CC} = 5.5V, I _F = 0 mA	_	14	30	mA
Low level supply current (both channels)	ICCL	V _{CC} = 5.5V, I _F = 10mA	\Diamond	24/	38	mA
Isolation voltage	Rs	V _S = 500V, R.H. ≤ 60% (Note 3)	5×10 ¹⁰	1014	/ _	Ω
Capacitance (input-output)	Cs	f = 1MHz (Note 3)	(G/>	0.6	_	pF
Input-input leakage current	11-1	R.H. \leq 60%, t = 5s V _{I-I} = 500V (Note 6)	775	0.005	_	μА
Resistance (input-input)	R _{I-I}	V _{I-I} = 500V (Note 6)		10 ¹¹	_	Ω
Capacitance (input-input)	CI-I	f = 1MHz (Note 6)	_	0.25	_	pF

^{*} All typical values are at $V_{CC} = 5V$, Ta = 25°C.



Switching Characteristics (Ta = 25°C, Vcc = 5V)

Characteristic	Symbol	Test Circuit	Test Condition	Min	Тур.	Max	Unit
Propagation delay time to low output level	t _p HL	1	I _F = 0 \rightarrow 7.5mA, R _L = 350Ω C _L = 15pF (each channel)	_	60	75	ns
Propagation delay time to high output level	t _p LH	1	I _F = 7.5mA \rightarrow 0, R _L = 350Ω C _L = 15pF (each channel)		60	75	ns
Output rise time, output fall time (10 to 90%)	t _r , t _f	1	$I_F = 0 \rightleftarrows 7.5 \text{mA}, R_L = 350\Omega$ $C_L = 15 \text{pF} \text{ (each channel)}$	-((30		ns
Common mode transient immunity at high output level	СМН	2	$I_F = 0$ mA, $R_L = 350\Omega$ $V_{CM} = 400V$, $V_{O}(min.) = 2V$ (each channel, Note 4)	1000	10000	1	V / μs
Common mode transient immunity at low output level	CML	2	$\begin{aligned} &\text{IF} = 7.5\text{mA}, \ &\text{R}_{\text{L}} = 350\Omega \\ &\text{V}_{\text{CM}} = 400\text{V} \\ &\text{V}_{\text{O}}(\text{max.}) = 0.8\text{V} \\ &\text{(each channel, (Note 5))} \end{aligned}$	1000	-10000	/	V / μs

- (Note 1) 2mm below seating plane
- (Note 2) The V_{CC} supply voltage to each TLP2631 isolator must be bypassed by a 0.1μF capacitor or larger. This can be either a ceramic or solid tantalum capacitor with good high frequency characteristic and should be connected as close as possible to the package V_{CC} and GND pins each device.
- (Note 3) Device considered a two-terminal device: Pins 1, 2, 3 and 4 shorted together, and pins 5, 6, 7 and 8 shorted together.
- (Note 4) CMH·the maximum tolerable rate of rise of the common mode voltage to ensure the output will remain in the high state (i.e. Vout > 2.0V).

Measured in volts per microsecond (V / μs).

Volts/ microsecond can be translated to sinusoidal voltages:

$$V/\mu s = \frac{(dVCM)}{dt}Max. = f_{CM}V_{CM}(p.p.)$$

Example:

VCM = 319Vpp when fCM = 1MHz using CML and CMH = $1000V / \mu s$ data sheet specified minimum.


(Note 5) CML·the maximum tolerable rate of fall of the common mode voltage to ensure the output will remain in the low output state (i.e. VOUT < 0.8V).

Measured in volts per microsecond (V / μs).


(Note 6) Measured between pins 1 and 2 shorted together, and pins 3 and 4 shorted together.



Test Circuit 1. tpHL and tpLH




Test Circuit 2. Transient Immunity and Typical Waveforms




$$\text{CM}_{H} = \frac{320(\text{V})}{t_{f}(\mu s)}, \text{CM}_{L} = \frac{320(\text{V})}{t_{f}(\mu s)}$$



^{*} C_L is approximately 15pF which includes probe and stray wiring capacitance.





RESTRICTIONS ON PRODUCT USE

Toshiba Corporation and its subsidiaries and affiliates are collectively referred to as "TOSHIBA". Hardware, software and systems described in this document are collectively referred to as "Product".

- TOSHIBA reserves the right to make changes to the information in this document and related Product without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
 EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH
 MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
 ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without
 limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for
 automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions,
 safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. IF YOU USE
 PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your
 TOSHIBA sales representative.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
 applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any
 infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to
 any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE
 FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY
 WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR
 LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND
 LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO
 SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS
 FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- GaAs (Gallium Arsenide) is used in Product. GaAs is harmful to humans if consumed or absorbed, whether in the form of dust or vapor.
 Handle with care and do not break, cut, crush, grind, dissolve chemically or otherwise expose GaAs in Product.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product.
 Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES
 OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.