


# SL1011A and SL1411A Series









#### **Agency Approvals**

AGENCY

AGENCY FILE NUMBER

*71* 

E128662

# 2 Electrode GDT Graphical Symbol



# **Additional Information**



Datasheet SL1011A



Datasheet SL1411A



Resources SL1011A



Resources SL1411A



Samples SL1011A



Samples SL1411A

# **Description**

The SL1011A and SL1411A series provides high levels of protection against fast rising transients in the 100V/µs to 1kV/µs range usually caused by lightning disturbances.

The SL1011A and SL1411A series offers low capacitance (< 1.5pf) which provides low insertion loss at high frequencies.

SL1011A offers 5kA protection without destruction whereas the SL1411A offer 10kA surge protection without destruction (maximum single surge of 12kA @  $8/20\mu s$ ).

#### **Features**

- Lead-free and RoHS compliant
- Low insertion loss
- Excellent response to fast rising transients
- Ultra low capacitance
- 5kA (SL1011A) or 10kA (SL1411A) surge capability tested with 8/20µs pulse as defined by IEC 61000-4-5 2nd edition

#### **Applications**

- Broadband equipment
- ADSL equipment
- XDSL equipment
- Satellite and CATV equipment
- General telecom equipment

# Gas Discharge Tubes SL1011A and SL1411A Series

# **Electrical Characteristics**

	Device Specifications (at 25°C)				Life Ratings										
Part Number	DC Breakdov in Volts <sup>1,2</sup> (@ 100V/s)			Impulse Breakdown in Volts³ (@100V/µs)	Impulse Breakdown In Volts (@1kV/µs)	Insulation Resistance	Capaci- tance (@1MHz)	Arc Voltage (on state Voltage) @1Amp Min	Surge Life (@100A 10/1000µs)	Nominal Impulse Discharge Current (8/20µs)	Nominal AC Discharge Current (10x1s @50-60Hz)	AC Dischage Current (9 Cycles @ 50Hz)	DC Holdover Voltage <sup>4</sup>	Discharg	mpulse ge Current plication)
	MIN	TYP	MAX	MAX		MIN	MAX	TYP					TYP	@ 8/20μs	@ 10/350μs
SL1011A075	60	60 75	90	500	700	10 <sup>10</sup> Ω (at 50V)	1.5 pF	pF ~20 V	300 shots			SL1011A: 20 A SL1411A:	50 V	SL1411A: 12 kA	1 kA
SL1411A075															
SL1011A090	72	2 90 108	108	500	600										
SL1411A090				000											
SL1011A145	116	145	174	500	650										
SL1011A150	120	150	180	500	650	10 <sup>10</sup> Ω									
SL1411A150		130								SL1011A:					
SL1011A230	184	230	276	550	700					10 shots	SL1011A:				
SL1411A230										(@5kA)	SL1411A: SL				
SL1011A250	200			600	800										
SL1411A250												65 A			
SL1011A260	210		310	600	800	(at 100V)									
SL1011A350	280		420	800	900										
SL1411A350															
SL1011A470	376	376 470	564	564 1000	1100										
SL1411A470	400			4400	4000										
SL1011A500	400	500	600	1100	1200										
SL1011A600	480	600	720	1200	1400										
SL1411A600															

#### Notes:

- 1. At delivery AQL 0.65 level II, DIN ISO 2859
- 2. In ionized mode
- 3. Comparable to the silicon measurement Switching Voltage (Vs)
- 4. Tested according to ITU-T Rec. K.12 < 150 msecs.

# **Product Characteristics**

Materials	<b>Leaded Device:</b> Nickel-plated with Tin- plated wires <b>Core and Surface Mount:</b> Dull Tin-plated		
Product Marking	Littelfuse 'LF' Mark, voltage and date code		


Glow to Arc Transition Current	< 0.5 Amps			
Glow Voltage	~60 Volts			
Storage and Operational Temperature	-40 to +90°C			




#### **Device Dimensions**

#### For SL1011A Series:

#### 'A' Type Axial Lead Devices




#### 'C' Type Core Devices




#### For SL1411A series:


#### 'A' Type Axial Lead Devices



#### 'SM' Type Surface Mount Devices




#### 'C' Type Core Devices






# **Soldering Parameters - Reflow Soldering (Surface Mount Devices)**

Reflow Co	ndition	Pb-free assembly		
	-Temperature Min (T <sub>s(min)</sub> )	150°C		
Pre Heat	-Temperature Max (T <sub>s(max)</sub> )	200°C		
	-Time (Min to Max) (t <sub>s</sub> )	60 – 180 seconds		
Average R (T <sub>L</sub> ) to pea	amp-up Rate (Liquidus Temp k)	3°C/second max.		
T <sub>S(max)</sub> to T <sub>L</sub>	- Ramp-up Rate	5°C/second max.		
- ·	-Temperature (T <sub>L</sub> ) (Liquidus)	217°C		
Reflow	-Temperature (t <sub>L</sub> )	60 – 150 seconds		
PeakTemp	erature (T <sub>P</sub> )	260 <sup>+0/-5</sup> °C		
Time with Temperatu	in 5°C of Actual Peak ure (t <sub>p</sub> )	10 – 30 seconds		
Ramp-dov	vn Rate	6°C/second max.		
Time 25°C	to Peak Temperature (T <sub>P</sub> )	8 minutes max.		
Do not exc	ceed	260°C		



# **Soldering Parameters - Wave Soldering (Thru-Hole Devices)**



# **Recommended Process Parameters:**

Wave Parameter	Lead-Free Recommendation		
Preheat:			
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)		
Temperature Minimum:	100° C		
Temperature Maximum:	150° C		
Preheat Time:	60-180 seconds		
Solder Pot Temperature:	280° C Maximum		
Solder DwellTime:	2-5 seconds		

# **Soldering Parameters - Hand Soldering**

Solder Iron Temperature: 350° C +/- 5°C


Heating Time: 5 seconds max.




#### **Packaging Dimensions**

#### For Axial Lead Items

Dimensions are in millimeters [and inches]







# For 'SM' Type Surface Mount Items (SL1411A series only)

Dimensions are in millimeters [and inches]

Dimensions are in millimeters [and inches]





For 'C' Type Core Items: Packed in plastic bag (500 pcs)



# **Part Numbering System and Ordering Information**

# For SL1011A series:


# SL1011A XXX X Voltage Pin Configuration

A = Axial Lead

C = Core

Remarks: Formed leads are available on request

# For SL1411A series:



A = Axial Lead

C = Core

SM = Surface Mount