


S1A THRU S1M

SUFACE MOUNT GENERAL PURPOSE SILICON RECTIFIER

Reverse Voltage - 50 to 1000 Volts Forward Current - 1.0 Ampere

SOD-123FL



FEATURES

- Glass passivated device
- Ideal for surface mouted applications
- Low reverse leakage
- Metallurgically bonded construction
- High temperature soldering guaranteed: 250°C/10 seconds,0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

MECHANICAL DATA

- Case : JEDEC SOD-123FL molded plastic body over passivated chip
- Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end Mounting Position: Any Weight :0.0007 ounce, 0.02 grams

Dimensions in millimeters

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.


	SYMBOLS	S1A	S1B	S1D	S1G	S1J	S1K	S1M	UNITS
	MARK	S1A	S1B	S1D	S1G	S1J	S1K	S1M	
Maximum repetitive peak reverse voltage	Vrrm	50	100	200	400	600	800	1000	VOLTS
Maximum RMS voltage	Vrms	35	70	140	280	420	560	700	VOLTS
Maximum DC blocking voltage	Vdc	50	100	200	400	600	800	1000	VOLTS
Maximum average forward rectified current at TA=65°C (NOTE 1)	l(AV)	1.0							Amp
Peak forward surge current									
8.3ms single half sine-wave superimposed on rated load (JEDEC Method) TL=25°C	Іғѕм 30.0								Amps
Maximum instantaneous forward voltage at 1.0A	Vf	1.1							Volts
Maximum DC reverse currentTa=25°Cat rated DC blocking voltageTa=125°C	lr	5.0 50.0							μΑ
Typical junction capacitance (NOTE 2)	CJ	4							pF
Typical thermal resistance (NOTE 3)	Reja	180							K/W
Operating junction and storage temperature range	Тј,Тѕтс	-55 to +150							°C

Note: 1. Averaged over any 20ms period.

2.Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3. Thermal resistance from junction to ambient at 0.375" (9.5mm)lead length, P.C.B. mounted


FIG.1 - TYPICAL FORWARD CHARACTERISTIC



INSTANTANEOUS FORWARD VOLTAGE, mV


FIG.3 - TYPICAL INSTANTANEOUS

FIG.2 - TYPICAL JUNCTION CAPACITANCE



REVERSE VOLTAGE, VOLTS

FIG.4 - FORWARD DERATING CURVE



INSTANTANEOUS REVERSE CURRENT REVERSE CHARACTERISTICS 100 T_{.1} = 150°C 10 T,₁ = 125°C ≣ T_J = 100°C μ AMPERES 1 T_J = 75°C T」= 50°C 0.1 T, = 25°C 0.01 **L** 0 500 300 400 600 700 800 100 200 900 INSTANTANEOUS REVERSE VOLTAGE,V

AMBIENT TEMPERATURE, °C