



## 2SB1198

## PNP EPITAXIAL SILICON TRANSISTOR


### LOW FREQUENCY PNP TRANSISTOR

#### DESCRIPTION

The UTC **2SB1198** is an epitaxial planar type PNP silicon transistor.

#### FEATURES

- \* High breakdown voltage :  $V_{CE0} = -80V$
- \* Low  $V_{CE(sat)}$  :  $V_{CE(sat)} = -0.2V$  (Typ)  
( $I_C/I_B = -0.5A/-50mA$ )




#### ORDERING INFORMATION

Ordering Number	Package	Pin Assignment			Packing
		1	2	3	
2SB1198G-x-AE3-R	SOT-23	E	B	C	Tape Reel

Note: Pin Assignment: E: Emitter    C: Collector    B: Base

<p>2SB1198G-x-AE3-R</p> <p>(1) Packing Type (2) Package Type (3) Rank (4) Green Package</p>	<p>(1) R: Tape Reel (2) AE3: SOT-23 (3) x: refer to Classification of <math>h_{FE}</math> (4) G: Halogen Free and Lead Free</p>
---	---

#### MARKING



■ ABSOLUTE MAXIMUM RATING ( $T_A=25^{\circ}\text{C}$ , unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Collector-Base Voltage	$V_{CBO}$	-80	V
Collector-Emitter Voltage	$V_{CEO}$	-80	V
Emitter-Base Voltage	$V_{EBO}$	-5	V
Collector Current	$I_C$	-0.5	A
Collector Power Dissipation	$P_C$	0.2	W
Junction Temperature	$T_J$	150	$^{\circ}\text{C}$
Storage Temperature	$T_{STG}$	-40 ~ +150	$^{\circ}\text{C}$

Note 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. The device is guaranteed to meet performance specification within  $0^{\circ}\text{C} \sim 70^{\circ}\text{C}$  operating temperature range and assured by design from  $-20^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .

■ ELECTRICAL CHARACTERISTICS ( $T_A=25^{\circ}\text{C}$ , unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Collector Base Breakdown Voltage	$BV_{CBO}$	$I_C = -50\mu\text{A}$	-80			V
Collector Emitter Breakdown Voltage	$BV_{CEO}$	$I_C = -2\text{mA}$	-80			V
Emitter Base Breakdown Voltage	$BV_{EBO}$	$I_E = -50\mu\text{A}$	-5			V
Collector Cut-Off Current	$I_{CBO}$	$V_{CB} = -50\text{V}$			-0.5	$\mu\text{A}$
Emitter Cut-Off Current	$I_{EBO}$	$V_{EB} = -4\text{V}$			-0.5	$\mu\text{A}$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C/I_B = -0.5\text{A}/-50\text{mA}$		-0.2	-0.5	V
DC Current Transfer Ratio	$h_{FE}$	$V_{CE} = -3\text{V}, I_C = -0.1\text{A}$	120		390	
Transition Frequency	$f_T$	$V_{CE} = -10\text{V}, I_E = 50\text{mA}, f = 100\text{MHz}$		180		MHz
Output Capacitance	$C_{ob}$	$V_{CB} = -10\text{V}, I_E = 0\text{A}, f = 1\text{MHz}$		11		pF

■ CLASSIFICATION OF  $h_{FE}$

RANK	Q	R
RANGE	120-270	180-390
MARKING	AKQ	AKR

■ TYPICAL CHARACTERISTICS

Figure 1. Grounded Emitter Propagation Characteristics




Figure 2. Grounded Emitter Output Characteristics




Figure 3. DC Current Gain vs. Collector Current




Figure 4. Collector-Emitter Saturation Voltage vs. Collector Current (I)




Figure 5. Collector-emitter Saturation Voltage vs. Collector Current (II)








Figure 6. Collector-Emitter Saturation Voltage vs. Collector Current (III)



■ TYPICAL CHARACTERISTICS(Cont.)



UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.