

Typical Application Circuit




Figure 2. Typical Application Schematic

Output Voltage Lookup Table

D+	D-	Output Voltage	Internal Switch Setting		
			SW1	SW2	SW3
3.3V	3.3V	20V	0	0	0
0.6V	0.6V	12V	0	0	1
3.3V	0.6V	9V	0	1	1
0.6V	GND	5V (Default)	1	1	1

Note: 1 represent the NMOS are OFF, 0 represent the NMOS are ON.

Functional Pin Description

Pin Name	Pin No. (SOP-8)	Pin Function
GND	1	Ground Pin.
VSEN1	2	Open Drain Output of output voltage adjustment switch. Active for 9V, 12V, 20V output setting.
VSEN2	3	Open Drain Output of output voltage adjustment switch. Active for 12V, 20V output setting.
VSEN3	4	Open Drain Output of output voltage adjustment switch. Active for 20V output setting.
D-	5	USB D- data line input
D+	6	USB D+ data line input
VREF	7	Internal Reference Voltage Output Pin. It must be with a resistor to GND
VDD	8	Power Supply Input Pin.

Block Diagram




Figure 3. Block Diagram of FP6600

Absolute Maximum Ratings

- Input Supply Voltage VDD ----- - 0.3V to + 8V
- All Other Pins Voltage ----- - 0.3V to + 8V
- Maximum Junction Temperature (T_J)----- + 150°C
- Storage Temperature (T_S)----- - 65°C to + 150°C
- Lead Temperature (Soldering, 10sec.) ----- +260°C
- Power Dissipation @T_A=25°C, (P_D)
 - SOP-8 ----- 1.39W
- Package Thermal Resistance, (θ_{JA}):
 - SOP-8----- 90°C/W
- Package Thermal Resistance, (θ_{JC}):
 - SOP-8----- 39°C/W

Note1 : Stresses beyond those listed under “Absolute Maximum Ratings” may cause permanent damage to the device.

Recommended Operating Conditions

- Input Supply Voltage (VDD)----- 4V ~ 6V
- Operation Temperature Range (T_{OPR}) ----- -40°C to +85°C

Note : Over operating free-air temperature range (unless otherwise noted)

Electrical Characteristics



(VDD=5V, T_A=25°C and the recommended supply voltage range, unless otherwise specified.)

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Input Power						
VDD Input Voltage Range	V _{DD}		4		6	V
Input UVLO Threshold	V _{UVLO(VTH)}	V _{DD} Rising	2.0		3.9	V
VDD Supply Current		VDD=5V, Measure V _{DD} , SW1 = SW2 = SW3 = Off		200		μA
VDD Shunt Voltage	V _{DD(SHUNT)}		TBD	TBD	TBD	V
Reference Voltage Output	V _R		1.18	1.23	1.28	V
High Voltage Dedicated Charging Port (HVDCP)						
20 V Output Inhibit Threshold	V _{DDH}		V _{DD-0} .6			V
Data Detect Voltage	V _{DAT(REF)}		0.25	0.325	0.4	V
Output voltage selection reference	V _{SEL_REF}		1.8	2.0	2.2	V
Data Lines Short-Circuit Delay	T _{DAT(SHORT)}	VOUT ≥ 0.8 V		10	20	ms
D+ High Glitch Filter Time	T _{GLITCH(BC)- D+_H}		1000	1250	1500	ms
D- Low Glitch Filter Time	T _{GLITCH(BC)- D-_L}		1			ms
Output Voltage Glitch Filter Time	T _{GLITCH(V) CHANGE}		20	40	60	ms
D- Pull-Down Resistance	R _{D-(DWN)}			20		KΩ
Switch SW1 on-resistance	R _{DS_ON_N1}	SW1 = 200μA			300	Ω
Switch SW2 on-resistance	R _{DS_ON_N2}	SW2 = 200μA			300	Ω
Switch SW3 on-resistance	R _{DS_ON_N3}	SW3 = 200μA			300	Ω
Switch SW5 on-resistance	R _{DS_ON_N5}	SW5 = 200μA			40	Ω
DCP 1.2V Charging Mode						
D+ _{-1.2V} /D- _{-1.2V} line output voltage			1.08	1.2	1.32	V
D+ _{-1.2V} /D- _{-1.2V} line output Impedance				58		KΩ
Apple 2.4A Mode						
D+ _{-2.7V} /D- _{-2.7V} line output voltage			2.57	2.7	2.84	V
D+ _{-2.7V} /D- _{-2.7V} line output Impedance				33.6		KΩ

Note : Not production tested.


Outline Information

SOP-8 Package (Unit: mm)





SYMBOLS UNIT	DIMENSION IN MILLIMETER	
	MIN	MAX
A	1.35	1.75
A1	0.10	0.25
A2	1.25	1.50
B	0.31	0.51
D	4.80	5.00
E	3.80	4.00
e	1.20	1.34
H	5.80	6.20
L	0.40	1.27

Note : Followed from JEDEC MO-012-E



Carrier dimensions



Tape Size (W1) mm	Pocket Pitch (P) mm	Reel Size (A)		Reel Width (W2) mm	Empty Cavity Length mm	Units per Reel
		in	mm			
12	8	13	330	12.4	400~1000	2,500

Life Support Policy

Fitipower's products are not authorized for use as critical components in life support devices or other medical systems.