
XL/ML1225 scr

MEDIUM POWER LOW VOLTAGE TRANSISTOR

DESCRIPTION


The **XL1225/ML1225** silicon controlled rectifiers are high performance planner diffused PNPN devices. These parts are intended for low cost high volume applications.




ORDERING INFORMATION

Ordering	Ordering Number		Pin Assignment			Da alain a	
Lead Free	Halogen Free	gen Free Package 1		2	3	Packing	
-	XL1225G-xx-AE3-R	SOT-23	G	K	Α	Tape Reel	
XL1225L-xx-T92-B	XL1225G-xx-T92-B	TO-92	K	G	Α	Tape Box	
XL1225L-xx-T92-K	XL1225G-xx-T92-K	TO-92	K	G	Α	Bulk	
-	ML1225G-xx-AE3-R	SOT-23	G	K	Α	Tape Reel	
ML1225L-xx-T92-B	ML1225G-xx-T92-B	TO-92	K	G	Α	Tape Box	
ML1225L-xx-T92-K	ML1225G-xx-T92-K	TO-92	K	G	Α	Bulk	

Note: Pin Assignment : G: Gate K: Cathode A: Anode



■ MARKING



<u>www.unisonic.com.tw</u> 1 of 3

■ ABSOLUATE MAXIUM RATINGS (Ta= 25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT	
Repetitive Peak Off-State Voltage	XL1225	V	400	V	
$(T_J = 40 \sim 125^{\circ}C, R_{GK} = 1k\Omega)$	ML1225	V _{DRM} 300		V	
On-State Current (Tc=40°C)		I _{T(RMS)}	0.8	Α	
Average On-State Current (Half Cycle=180,Tc=40°C)		I _{T(AV)}	0.5	Α	
Peak Reverse Gate Voltage (IGR=10μA)		V_{GRM}	1	V	
Peak Gate Current (10μs Max.)		I_{GM}	0.1	Α	
Gate Dissipation (20ms Max.)		$P_{G(AV)}$	150	mW	
Junction Temperature		T_J	+125	°C	
Storage Temperature		T _{STG}	-40 ~ +150	°C	

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

■ ELECTRICAL CHARACTERISTICS (Ta= 25°C, unless otherwise specified.)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Off State Leakage Current		$V_{DRM}(R_{GK}=1K\Omega), T_J=125^{\circ}C$			0.1	mA
Off State Leakage Current		$V_{DRM}(R_{GK}=1K\Omega), T_J=25^{\circ}C$			1.0	μA
0 - 01-1-1/-11	V _T	AT I _T =0.4A			1.4	
On State Voltage		AT I _T =0.8A			2.2	· V
On State Threshold Voltage	V _{T(TO)}	T _J =125°C			0.95	V
On State Slops Resistance	Rt	T _J =125°C			600	m
Gate Trigger Current	I_{GT}	V _D =7V			200	μA
Gate Trigger Voltage	V_{GT}	V _D =7V			0.8	V
Holding Current	Ι _Η	R _{GK} =1KΩ			5	mA
Latching Current	ΙL	R _{GK} =1KΩ			6	mA
Critical Rate of Voltage Rise	DV/DT	$V_D=0.67 \times V_{DRM}(R_{GK}=1K\Omega), T_J=125^{\circ}C$				V/µs
Critical Rate of Current Rise	DV/DT	I_G =10mA, d I_G /dt=0.1A/ μ s, T_J =125°C				A/µs
Gate Controlled Delay Time	T_GD	l _G =10mA, dl _G /dt=0.1A/μs			2.2	μs
Commutated Turn-off Time	TG	$T_J = 85^{\circ}C, V_D = 0.67^*V_{DRM}, V_R = 35V,$ $I_T = I_{T(AV)}$			200	μs

■ CLASSIFICATION OF I_{GT}

RANK	В	С	AA	AB	AC	AD
RANGE	50-100	100-200	8-15	15-20	20-25	25-50

^{2.} The device is guaranteed to meet performance specification within $0^{\circ}\text{C} \sim 70^{\circ}\text{C}$ operating temperature range and assured by design from $-20^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

■ TYPICAL CHARACTERICS







Figure 1. Typical Gate Trigger Current versus Junction Temperature

Figure 2. Typical Gate Trigger Voltage versus Junction Temperature






Figure 3. Typical Holding Current versus Junction Temperature

Figure 4. Typical Latching Current versus Junction Temperature




Figure 5. Typical On-State Characteristics

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.