EVERLIGHT ELECTRONICS CO.,LTD.

Technical Data Sheet

1206 Package Chip LED (1.1 mm Height)

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS complaint version.

Descriptions

- The 12-215 SMD Taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide


Part No.	C		
	Material	Emitted Color	Lens Color
12-215UYC/S530-XX/TR8	AlGaInP	Brilliant Yellow	Water Clear




12-215UYC/S530-XX/TR8




Package Outline Dimensions







For reflow soldering (Propose)



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

EVERLIGHT ELECTRONICS CO.,LTD.

12-215UYC/S530-XX/TR8

Absolute Maximum Ratings (Ta=25°C)

EVERLIGHT

Symbol Rating Unit Parameter V Reverse Voltage V_R 5 25 Forward Current \mathbf{I}_{F} mА °C $-40 \sim +85$ **Operating Temperature** Topr °C $-40 \sim +90$ Storage Temperature Tstg Electrostatic Discharge(HBM) ESD 2000 V **Power Dissipation** Pd 60 mW Peak Forward Current 60 IFP mA (Duty 1/10 @1KHz) Reflow Soldering : 260 $^{\circ}$ C for 10 sec. Soldering Temperature Tsol Hand Soldering : 350 °C for 3 sec.

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	*Chip Rank	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	A2	16.0	39		mcd	
		A3	36.0	57			
		A4	52.0	78			
		A5	62.0	98			
		A6	78.0	114			
Viewing Angle	201/2			130		deg	I _F =20mA
Peak Wavelength	λp			591		nm	
Dominant Wavelength	λd			589		nm	
Spectrum Radiation Bandwidth	$ riangle \lambda$			15		nm	
Forward Voltage	\mathbf{V}_{F}			2.0	2.4	V	
Reverse Current	I _R				10	μΑ	V _R =5V

*12-215UYC/S530-XX/TR8

Chip Rank

Everlight Electronics Co., Ltd. Device No:SZDSE-125-007


http://www.everlight.com Prepared date:19-Aug-2005 Rev 1 Page: 3 of 9

Prepared by:Meng Yali

EVERLIGHT ELECTRONICS CO., LTD.

Electro-Optical Characteristics (Ta=25°C)

ÆRLIGHT



Everlight Electronics Co., Ltd. Device No:SZDSE-125-007


12-215UYC/S530-XX/TR8

Label explanation

- **CAT: Luminous Intensity Rank**
- HUE: Dom. Wavelength Rank
- **REF: Forward Voltage Rank**



Reel Dimensions




Note: The tolerances unless mentioned is ± 0.1 mm ,Unit = mm

12-215UYC/S530-XX/TR8




Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm ,Unit = mm

Moisture Resistant Packaging



http://www.everlight.com Prepared date:19-Aug-2005 Rev 1Page: 6 of 9Prepared by:Meng Yali

Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below. Confidence level : 90% LTPD : 10%


No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H : +100°C 5min $\int 10 \sec$ L : -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85℃/ 85% RH	1000 Hrs.	22 PCS.	0/1

Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30° C or less and 90%RH or less.
 - 2.3 The LEDs should be used within a year.
 - 2.4 After opening the package, the LEDs should be kept at 30° C or less and 60%RH or less.
 - 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
 - 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.Baking treatment : 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD. Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C

Tel: 886-2-2267-2000, 2267-9936 *Fax:* 886-2267-6244, 2267-6189, 2267-6306 *http://www.everlight.com*

Everlight Electronics Co., Ltd. Device No:SZDSE-125-007

http://www.everlight.com Prepared date:19-Aug-2005 Rev 1 Page: 9 of 9 Prepared by:Meng Yali