EVERLIGHT EVERLIGHT ELECTRONICS CO., LTD.

# **Technical Data Sheet**

# **Chip LED with Right Angle Lens**

# Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow

solder process.

- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS complaint version.

#### Descriptions

- The 12-21 SMD taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications etc.

#### Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: Indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.
- Indoor signboard use.

# **Device Selection Guide**

Part No.		I CI	
	Material	<b>Emitted</b> Color	Lens Color
12-21UBC/C430/TR8	GaN/SiC	Purplish Blue	Water Clear





12-21UBC/C430/TR8

Everlight Electronics Co., Ltd. Device No. : SZDSE-121-021





### **Package Outline Dimensions**





For reflow soldering (propose)





**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm

Everlight Electronics Co., Ltd. Device No. : SZDSE-121-021 http://www.everlight.com Prepared date: 18-Aug-2005 Rev.1 Page: 2 of 9 Prepared by:Meng Yali EVERLIGHT ELECTRONICS CO., LTD.

# 12-21UBC/C430/TR8

#### Absolute Maximum Ratings (Ta=25°C) Symbol Rating Unit Parameter V Reverse Voltage $V_R$ 5 30 Forward Current $\mathbf{I}_{\mathbf{F}}$ mА °C -40 ~ +85 **Operating Temperature** Topr °C Storage Temperature Tstg -40 ~ +90 V Electrostatic Discharge(HBM) ESD 1000 **Power Dissipation** Pd 130 $\mathrm{mW}$ Peak Forward Current 70 I<sub>FP</sub> mА (Duty 1/10 @1KHz) Reflow Soldering : 260 $^{\circ}$ C for 10 sec. Soldering Temperature Tsol Hand Soldering : 350 $^{\circ}$ C for 3 sec.

## Electro-Optical Characteristics (Ta=25°C)

EVERLIGHT


Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition		
Luminous Intensity	Iv	17	22		mcd			
Viewing Angle	2 <del>0</del> 1/2		120		deg			
Peak Wavelength	λp		428		nm	I <sub>F</sub> =20mA		
Dominant Wavelength	λd		466		nm			
Spectrum Radiation Bandwidth	$ riangle \lambda$		65		nm			
Forward Voltage	$V_{\rm F}$		3.8	4.5	V			
Reverse Current	I <sub>R</sub>			50	$\mu$ A	V <sub>R</sub> =5V		

http://www.everlight.com Prepared date: 18-Aug-2005 Rev.1

Page: 3 of 9

EVERLIGHT ELECTRONICS CO., LTD.

# 12-21UBC/C430/TR8



**Typical Electro-Optical Characteristics Curves** 

**ÆRLIGHT** 

Everlight Electronics Co., Ltd. Device No. : SZDSE-121-021

http://www.everlight.com Prepared date: 18-Aug-2005

Page: 4 of 9 Prepared by:Meng Yali

Rev.1

# EVERLIGHT ELECTRONICS CO., LTD.

# 12-21UBC/C430/TR8

### Label explanation


**CAT: Luminous Intensity Rank** 

HUE: Dom. Wavelength Rank

**REF: Forward Voltage Rank** 




#### **Reel Dimensions**



**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm


http://www.everlight.com Prepared date: 18-Aug-2005 Rev.1 Page: 5 of 9 Prepared by:Meng Yali

# **Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel**



**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm

# **Moisture Resistant Packaging**



Everlight Electronics Co., Ltd. Device No. : SZDSE-121-021 http://www.everlight.com Prepared date: 18-Aug-2005 Rev.1 Page: 6 of 9 Prepared by:Meng Yali

# **Reliability Test Items And Conditions**

The reliability of products shall be satisfied with items listed below.

Confidence level : 90%

LTPD: 10%


No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100°C 5min $\int 10 \sec$ L: -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	<b>Temp.</b> : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	IF = 20  mA	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85℃/ 85%RH	1000 Hrs.	22 PCS.	0/1

# **Precautions For Use**

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change ( Burn out will happen ).

- 2. Storage
  - 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package, the LEDs should be kept at  $30^{\circ}$ C or less and 90% RH or less.
- 2.3 The LEDs should be used within a year.
- 2.4 After opening the package, the LEDs should be kept at  $30^{\circ}$ C or less and 60%RH or less.
- 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
- 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
  Baking treatment : 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

#### 4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $350^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

#### 5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



#### **EVERLIGHT ELECTRONICS CO., LTD.** Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C

*Tel:* 886-2-2267-2000, 2267-9936 *Fax:* 886-2267-6244, 2267-6189, 2267-6306 *http://www.everlight.com* 

Everlight Electronics Co., Ltd. Device No. : SZDSE-121-021 http://www.everlight.com Prepared date: 18-Aug-2005 Rev.1 Page: 9 of 9 Prepared by:Meng Yali