ISO9001: 2000 ISO14001: 2004

APPROVAL SPECIFICATIONS

Title. TACT SWITCH

Product Model. KAN0632

Customer's Part NO.

Customer's Model:

Customer's Approval Requested.

Please return this copy as a certification of your approval.

Checked by: Date:

Approved by: Date:

APPROVE	REVIEW	POLT
黄蜀东	关 林	曹 盖

WENZHOU GANGYUAN ELECTRONICS CO., LTD.



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0632	TACT SWITCH	Α

A. Specification & meanings

The name of the tact switch is composed by type and specification, the particular meaning of the type, specification and code is as follows.

KAN0632- □□□										
	Т	Т								
				Press	force	(ref	er to	cha	art	3)
					color					
		11/		Produ	ict heig	ght	refer	to	ch	art

1. Product height: It is denoted by three figures; For examples, "075" expresses the product which the total height is 7.5mm, as chart 1 shows:

Code	Product height	Code	Product height	Code	Product height
043	4.3				
050	5				
060	6				
070	7				

2. Stem color: It is expressed by a figure, as chart 2 shows:

Color	Black
Code	1

3. Operating force: An English letter expresses it, unite: Newton (N),as chart 3 shows:

force Code Spe	perating ec	Press force	Return force
Α	1.0	1.0±0.3	0.2min
В	1.6	1.6±0.5	0.4min
C	2.6	2.6±0.5	0.6min

Examples: "KAN0632-0501B" denotes the tact switch with 6×6 base, the height is 5mm,the stem is black , the operating force is 1.6N.

APPROVE BY 黄蜀东 09.10.25 CHECKED BY	关 林 09.10.25	PRPARE BY	曹 盖 09.10.25
------------------------------------	--------------	-----------	--------------

1)



GYUAN CO.,LTD

CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0632	TACT SWITCH	А

1、 概述

GENERAL

1.2 适用范围

APPLICATION

此规格书适用于机械式轻触开关的相关要求

This specification is applied to the requirements for TACTILE SWITCH (MECHANICAL CONTACT)

1.3 工作温度范围

Operating Temperature Range

- -20℃~70℃(在标准大气压、标准湿度条件下)
- -20°C ~70°C (Normal humidity, normal air pressure)

1.4 贮藏温度范围

Storage Temperature Range -30℃~80℃(在标准大气压、标准湿度条件下)

 -30° C \sim 80°C (Normal humidity, normal air pressure)

1.5 测试条件

Test Conditions

在没有其它特定的条件下,应该在以下的条件下进行测试和测量:

Unless otherwise specified, tests and measurement shall be made in the following standard conditions:

常温......5℃~35℃

Normal temperature......5°C~35°C

标准湿度......相对湿度 25%~85%

Normal humidity.....relative humidity 25%~85%

标准大气压......86KPa~106Kpa

Normal air pressure......86Kpa~106Kpa

在制造过程中,测试和测量应该在以下的条件下进行:

If any doubt arise from the judgment, tests shall be conducted at the following conditions:

温度......**20℃±2℃**

Temperature......20°C±2°C

相对湿度......65%±5%

Relative humidity......65%±5%

环境气压......86KPa~106Kpa

Air pressure......86KPa~106Kpa

APPROVE BY 黄蜀东 09.10.25 **CHECKED BY** 关 林 09.10.25 PRPARE BY 曹 盖 09.10.25



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION	
		KAN0632	TACT SWITCH	Α	

详细说明

Detailed specification

2.1 外观:应无影响、降低产品性能的缺陷;

Appearance: There should be no defects that affect the serviceability of product.

2.2 结构尺寸和安装尺寸:应符合装配图要求;

Style and dimension: shall conform to the assemble drawings.

2.3 操作形式:有触觉反应的操作

2. 4 开关结构: 单回路单输出(具体的触点结构在装配图中已绘出: Solution of the contact arrangement: 1 pole, 1 throw 1 1 pole, 1 throw 1 1 pole, 1 throw 1

(Details of contact arrangement are given in the assembly drawings.)

2.5 开关工作额定值: DC 12V, 50mA (有效值)

Ratings: 12V DC, 50mA (effective value)

3. 电气性能:

ELECTRICAL SPECIFICATION

项	目		Ì	试 验 条 件			要求
ITI	EΜ		TE	EST CONDITIONS		REG	QUIREMENTS
		接触电阻	在以 5V 10mA 的直流电源或不低于 1KHz 的交流电源的电路中,以一个等于 2 倍按力的静负荷施加于手柄中心Applying a static load of 2 times operating force to				
1		按應电阻 act Resistance	the center of the stem	, measurements sha	all be made by		≤ 100 m Ω
			5V DC 10mA or mo	re than 1KHZ AC	small-current		
			contact resistance met	er.			
2	ı	绝缘电阻 Insulation Resistance	在端子之间施加 DC 100V /1min 的条件下,测量端子之间底座、盖板的电阻值 Measurement shall be made following application of 100V DC potential, across terminals, and across terminals and cover, for one minute.				≥100MΩ
3	D	广质耐压 ielectric tage proof	在端子之间施加 250V AC(50HZ 或 60HZ)/1min 250V AC (50HZ or 60HZ) shall be applied across terminals, for one minute.				无击穿、无飞弧 There should be breakdown and flashover
APPROVI	L BY 黄蜀东 09.10.2		25 CHECKED BY 关 林 09.10.25 PRPARE BY			Y	曹 盖 09.10.25



С	USTOMER	CUSTOMER'S PA	N GYE'	S P/N	PRODUCT		REVISION
			KAN	0632	TACT SWITCH		A
	项目						要求
	ITEM		TEST COND			RE	QUIREMENTS
	械性能: IANICAL SPEC	IFICATION					
1	按力 Operating Force	开关垂直于操作方量开关导通所需的却 Placing the switch vertical and then center of the stem, come to a stop sha	最大力度。 such that the d gradually increa the maximum l	irection of swit asing the load load required fo	ch operation is applied to the	re	fer to chart 3
2	最大行程 Full Travel	开关垂直于操作方向放置,以一个等于 2 倍按力的静负荷施加在开关驱动件顶端中心,测量顶端移动的距离。Placing the switch such that the direction of switch operation is vertical and then applying static load of 2times operating force to the center of the stem; the travel distance for the switch to come to a stop shall be measured.					0.25±0.1mm
APP	ROVE BY	黄蜀东 09.10.25 C	HECKED BY	关 林 09.10	.25 PRPARI	E BY	曹 盖 09.10.25



l	GAN	NGYUAN	APPI	ROVAL	SPEC	IFICA	TIONS			
С	USTOMER	CUSTOMER'S	S P/N GY	E'S P/N	PROD	DUCT	REVISION			
			KA	N0632	TACT S	WITCH	А			
	项目		试 验		l		要求			
	ITEM		TEST CON	IDITIONS			REQUIREMENTS			
3	回弹力 Return Force	开关垂直于操作 后,测量顶端向 The sample sw operation is ve to the whole tra	开关垂直于操作方向放置,在开关驱动件顶端中心下降至全行程后,测量顶端向自由位置转换的力度。 The sample switch is installed such that the direction of switch operation is vertical and upon depressing the stem in its center of the whole travel distance, the force of the stem to return to its ree position shall be measured.							
4	停止强度 Stop Strengt	荷持续 1min。 Placing the swivertical, and th	表向放置,从操作 tch such that the en a static load m operation for a	ion is T	无机械和电气损坏 here shall be no sign of image mechanically and electrically.					
5	手柄拔出 强度 Stem Strength	的行程范围。 Placing the swi vertical, and the	三方向放置,反方(itch such that the en the maximum f direction of stem	ion is	20N.min.					
6	可焊性 Solderability 在以下设定条件下进行测量: Measurements shall be made following the test set forth below: (1) 焊接温度:245±5℃ Solder temperature: 245±5℃ (2) 浸入时间:2s±0.5s Immersion time: 2s±0.5s 对于其它步骤参考《GB 5095.6—86》试验 12a The other steps please refer to 《GB 5095.6-86》TEST 12a						边缘外涂层应均匀覆盖 %以上 cept for the edge, the ating should cover a nimum 90%			
APP	ROVE BY	黄蜀东 09.10.25	CHECKED BY	关 林 09.	10.25 F	PRPARE E	曹 盖 09.10.25			



С	USTOMER		CUSTOMER	'S P/N	GYE'	S P/N	PI	RODUCT		REVISION
					KAN	0632	TAC	T SWITCH		А
	项目	<u> </u>		试 验 条 件					要求	
	ITEM				TEST CON	IDITIONS			RE	QUIREMENTS
	5、极限电气性能: ENVIRONMENTAL SPECIFICATION									
1	低温测试 Resistance low tempera	to ature	标准湿度的 Following t normal ten measurem (1) 温度 Tem (2) 时间	Temperature : -30±2°C						H: ≤200mΩ resistance: Ω 4.1,4.2,4.3 4.1,4.2,4.3
2	高温测试 Heat resista	nce	标准湿度的 forth below humidity co (1) 温度 ten (2) 时间	temperature:80±2℃					Contac ≤200ms 项目 3,4	
3	温度周期性 Change temperati	of	样品应放在 试期间样品 After 5 cyc allowed to conditions	根据下面的测试要求进行 5 次循环的温度周期性测试, 实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试。测试期间样品应保持干燥. After 5 cycles of following conditions, the sample shall be allowed to stand under normal temperature and humidity conditions for 1 h. and measurements shall be made. During the test water drops shall be removed. Temperature Time 1 cycle 1 cycle 65+2℃ 2 cycles of following conditions, the sample shall be allowed to stand under normal temperature and humidity conditions for 1 h. and measurements shall be made. During the test water drops shall be removed.					Contac ≤200ms 项目 3,4	
APP	ROVE BY	黄蜀	东 09.10.25	СНЕ	ECKED BY	关 林(9.10.25	PRPARE	E BY	曹 盖 09.10.25



С	USTOMER	CUSTOMER'S F	P/N GYE	S P/N	PRODUCT		REVISION
			KAN	0632	TACT SWITCH	I A	
	项目		试 验	条件			要求
	ITEM		TEST CON	IDITIONS		REC	QUIREMENTS
4	湿温测试 Moisture resistance	标准湿度的环境 forth below the humidity condi (1) 温度: tempera (2) 相对湿	iture: 60±2℃ 度: 90%~95% humidity:90% to 96h	Contact ≤200mΩ 项目 3,4			
5	硫化试验 Sulfuration resistance	标准湿度的环境 forth below the humidity condi (1) H2S 气 H ₂ S gas (2) 时间: Time: 75 (3) 温度: 4		Contact ≤200mΩ 项目 3,4			
6	盐雾试验 Salt Mist	The switch sl (1)温度:35 tempera (2)盐溶液浓 salt solu (3)时间:8h Time:8h 实验后的盐沉和	在以下设定条件下进行测量: The switch shall be checked after following test: (1) 温度: 35℃±2℃ temperature: 35℃±2℃ (2) 盐溶液浓度: 5±1% (质量百分比) salt solution: 5±1%(solids by mass) (3) 时间: 8h±1h Time: 8h±1 hour 实验后的盐沉积物后水冲掉 After test, salt deposit shall be removed by running water.				上没有腐蚀斑点 No remarkable on shall be zed in metal part.
APP	APPROVE BY 黄蜀东 09.10.25 CF			关 林 09.	10.25 PRPAR	E BY	曹 盖 09.10.25



	UA UA	1401	UAN	/\l \	O V/ \L	OI L		110	2110
C	USTOMER		CUSTOMER'S P/N	GYE'	S P/N	P	RODUCT	REVISION	
				KAN	0632	TAC	CT SWITCH	А	
	限机械性能: NDURANCE	SPEC	IFICATION	1					
	项目			试 验	条 件				要求
	ITEM			TEST CON				DE	QUIREMENTS
		<u>></u>		TEST CON	SNOITIGI			KE	ZUIREIVIENTS
1	工作寿命 Operation		(2) 接动速率: 1 Rate of ope (3) 接力: 接力 Operating (be made foll OmA 带负载 mA resistive 次/秒 eration: 1 time 的1.5倍	load es/s erating Force	e1.5dou	接 re: 接 Or ini 项	sistan 力: peratii tial va 目 3,4	阻≤200mΩContact ce≤200mΩ 初值的±30% ng Force: nlue±30% l.1,4.2,4.3 l.1,4.2,4.3
2	振动 Vibra	根据以下给定条件进行测试: Measurement shall be made following the test set forth below: (1) 振动频率范围: 10~55~10Hz Vibration frequency range: 10 to 55 to 10Hz (2) 振幅(峰一峰): 1.5mm Amplitude: 1.5mm (3) 振动方向: 包括手柄行程方向在内的三个相互垂直的方向 Direction of vibration:Three mutually perpendicular direction including the direction of stem travel (4) 测试时间: 每次 2hours. Duration: Each 2hours.				z 項 五垂直的方 Ite		l.1,4.2,4.3 l.1,4.2,4.3	
	接条件: ERING CON	DITIO	NS:				·		
			· 请按以下约	条件进行焊接	:				
			(1) 焊锡温度: ≤350℃						
7 4	手工焊接		(2) 连续焊接时间: ≤3 s						
7.1	Hand solde	ering	, ,	actice accord		condition	ons:		
				ring temperature: 350℃ Max. nuous soldering time: 3 s Max.					
4.55	DOVE 53.4	41: mr					DDD455	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	本 * * * * * * * * * * * * * * * * * * *
│ APPROVE BY │ 黄蜀菊		东 09.10.25 CHE	CKED BY	关 林 09.	10.25	PRPARE B	Y	曹 盖 09.10.25	



CUSTOMER		CUSTOMER'S P/N	GYE'S P/N		PRODUCT	REVISION			
KA			AN0632	А					
	自动浸焊	项目 Items		条件 Condition					
	Conditions for	助焊剂附着量 Flux built-up			不附着于零部件贴装面的程度 Mounting surface should not be coated with flax				
	Auto-dip	预热温度 Preheating temper	预热温度 Preheating temperature		印刷电路板焊接面的周围温度 100℃ max. Ambient temperature of the soldered surface of PC board. 100℃ max.				
7.2		预热温度时间 Preheating tim			60s max.				
		焊接温度 Soldering tem	焊接温度 Soldering temperature		260°C max.				
	WER	上焊接浸渍时间 Continuous dipping time		5s max.					
		焊接次数		2 次以下					
	传 控说明。	Number of solds	Number of soldering		2times max.				

焊接说明:

1、开关浸焊后,注意不要用溶剂清洗。

After switches were soldered, please be careful not to clean switches with solvent.

1.1 在使用烙铁的情况下,焊锡温度应在 350℃以下、3 秒以内。

In the case of using solding iron, solding conditions shall be 380℃ max and 3 sec.max.

1.2 浸焊后,注意不要在顶部施加负荷。

Right after switches were soidered; please be careful not to load to on the knobs of switches.

- 2、设计中应注意的事项(Design instructions)
- 2.1 印刷基板的安装孔尺寸参见产品图。

Follow recommended P.W.B. piercing plan in outside drawing page.

- 3、注意点(Note):
- 3.1 注意不要施加超负荷的压力或晃动开关。

Please be cautions not to give excessive static load or shock to swiches.

3.2 开关浸焊后,印刷基板注意不要叠放。

Please be careful not to pile up P.W.B.after switches were soldered.


3.3 保管时尤其应注意避开高湿高温和有腐蚀性气体的环境。如需要长时间保存,请不要打开包装箱。

Preservation under high temperature and high high humidity or corrosive gas should be avoided Especially . When you need to preserve for a long period ,do not open the carton.

APPROVE BY 黄蛋	蜀东 09.10.25 CHECKED E	BY 关 林 09.10.25	PRPARE BY	曹 盖 09.10.25
---------------	-----------------------	-----------------	-----------	--------------



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0632	TACT SWITCH	А



General tolerance: ±0.2mm

	NO.	NAME	MATERIAL NATIONALITY		QTY.	FINIS	HING			
	1	BRACKET	SPCC-SD	(China	1	CuSn	plating		
	2 TERMINAL 3 CASE 4 CONTACT		Brass	(China		Silver	plating		
			PA66		China	1	Bla	Black		
			Phosphor bronze	i Korea I		1	Contact side	Contact side silver plating		
	5	COVER	SPCC-SD	China		1	CuSn	plating		
	6 STEM		PA66	China		1				
APPROVE BY		黄蜀东 09.10.25	CHECKED	BY	关 林 09	.10.25	PRPARE BY	曹 盖 09.10	1.25	