



## Surface Mountable PTC Resettable Fuse: FSMD Series

### 1. Summary

(a) **RoHS Compliant & Halogen Free**

(b) Applications: All high-density boards

(c) Product Features: Small surface mountable, Solid state, Faster time to trip than standard SMD devices, Lower resistance than standard SMD devices

(d) Operation Current: 0.10A~3.00A

(e) Maximum Voltage: 6V~60VDC

(f) Temperature Range : -40°C to 85°C

### 2. Agency Recognition

UL: File No. E211981

C-UL: File No. E211981

TÜV: File No. R50004084, R50090556

### 3. Electrical Characteristics (23°C)


Part Number	Hold Current	Trip Current	Rated Voltage	Max Current	Typical Power	Max Time to Trip		Resistance	
	I <sub>H</sub> , A	I <sub>T</sub> , A	V <sub>MAX</sub> , VDC	I <sub>MAX</sub> , A	P <sub>d</sub> , W	Current	Time	R <sub>MIN</sub>	R <sub>1MAX</sub>
	I <sub>H</sub> , A	I <sub>T</sub> , A	V <sub>MAX</sub> , VDC	I <sub>MAX</sub> , A	P <sub>d</sub> , W	Amp	Sec	Ohms	Ohms
FSMD010-R	0.10	0.30	60	100	0.8	8.0	0.020	1.600	15.000
FSMD014-R	0.14	0.30	60	100	0.8	8.0	0.008	1.200	6.500
FSMD020-R	0.20	0.40	30	100	0.8	8.0	0.020	0.800	5.000
FSMD020-60-R	0.20	0.40	60	100	0.8	8.0	0.020	0.800	5.000
FSMD030-R	0.30	0.60	30	100	0.8	8.0	0.100	0.200	1.750
FSMD035-R	0.35	0.70	16	100	0.8	8.0	0.100	0.320	1.500
FSMD035-30-R	0.35	0.70	30	100	0.8	8.0	0.100	0.320	1.500
FSMD050-R	0.50	1.00	16	100	0.8	8.0	0.150	0.150	1.000
FSMD050-30-R	0.50	1.00	30	100	0.8	8.0	0.150	0.150	1.000
FSMD075-R	0.75	1.50	16	100	0.8	8.0	0.200	0.110	0.450
FSMD075-24R	0.75	1.50	24	100	1.0	8.0	0.200	0.110	0.290
FSMD075-33R	0.75	1.50	33	100	1.0	8.0	0.200	0.110	0.400
FSMD110-R	1.10	2.20	8	100	0.8	8.0	0.300	0.040	0.210
FSMD110-16-R	1.10	2.20	16	100	0.8	8.0	0.500	0.060	0.180
FSMD110-24R	1.10	2.20	24	100	1.0	8.0	0.500	0.060	0.200
FSMD125-R	1.25	2.50	6	100	0.8	8.0	0.400	0.050	0.140
FSMD125-16R	1.25	2.50	16	100	0.8	8.0	0.400	0.050	0.140
FSMD150-R	1.50	3.00	8	100	0.8	8.0	0.500	0.040	0.110
FSMD150-12R	1.50	3.00	12	100	1.0	8.0	0.500	0.040	0.110
FSMD150-24R	1.50	3.00	24	100	1.0	8.0	1.500	0.040	0.120
FSMD160-R	1.60	3.20	8	100	0.8	8.0	0.500	0.030	0.100
FSMD160-12R	1.60	3.20	12	100	1.0	8.0	1.000	0.030	0.100
FSMD160-16R	1.60	3.20	16	100	1.0	8.0	1.000	0.030	0.100
FSMD200R	2.00	3.50	8	100	1.0	8.0	2.000	0.020	0.070
FSMD200-16R	2.00	3.50	16	100	1.0	8.0	5.000	0.020	0.085
FSMD260R	2.60	5.00	8	100	1.0	8.0	2.500	0.015	0.047
FSMD260-13R	2.60	5.00	13.2	100	1.3	8.0	5.000	0.015	0.050
FSMD260-16R	2.60	5.00	16	100	1.3	8.0	5.000	0.015	0.050
FSMD300R	3.00	5.00	6	100	1.0	8.0	4.000	0.012	0.040

NOTE : Specification subject to change without notice.

 <b>FUZETEC TECHNOLOGY CO., LTD.</b>	<b>NO.</b>	<b>PQ04-01ER</b>		
	<b>Product Specification and Approval Sheet</b>	<b>Version</b>	<b>A6</b>	<b>Page</b>

$I_H$ =Hold current-maximum current at which the device will not trip at 23°C still air.  
 $I_T$ =Trip current-minimum current at which the device will always trip at 23°C still air.  
 $V_{MAX}$ =Maximum voltage device can withstand without damage at it rated current.( $I_{MAX}$ )  
 $I_{MAX}$ = Maximum fault current device can withstand without damage at rated voltage ( $V_{MAX}$ ).  
 $P_d$ =Typical power dissipated-type amount of power dissipated by the device when in the tripped state in 23°C still air environment.  
 $R_{MIN}$ =Minimum device resistance at 23°C prior to tripping.  
 $R_{1MAX}$ =Maximum device resistance at 23°C measured 1 hour after tripping or reflow soldering of 260°C for 20 seconds.  
Termination pad characteristics  
Termination pad materials: Pure Tin

#### 4. FSMD Product Dimensions (Millimeters)




Part Number	A		B		C		D		E	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
FSMD010-R	4.37	4.73	3.07	3.41	0.60	0.90	0.30	0.95	0.25	0.65
FSMD014-R	4.37	4.73	3.07	3.41	0.60	0.90	0.30	0.95	0.25	0.65
FSMD020-R	4.37	4.73	3.07	3.41	0.60	0.90	0.30	0.95	0.25	0.65
FSMD020-60-R	4.37	4.73	3.07	3.41	0.60	0.90	0.30	0.95	0.25	0.65
FSMD030-R	4.37	4.73	3.07	3.41	0.40	0.70	0.30	0.95	0.25	0.65
FSMD035-R	4.37	4.73	3.07	3.41	0.40	0.70	0.30	0.95	0.25	0.65
FSMD035-30-R	4.37	4.73	3.07	3.41	0.40	0.70	0.30	0.95	0.25	0.65
FSMD050-R	4.37	4.73	3.07	3.41	0.35	0.65	0.30	0.95	0.25	0.65
FSMD050-30-R	4.37	4.73	3.07	3.41	0.45	0.75	0.30	0.95	0.25	0.65
FSMD075-R	4.37	4.73	3.07	3.41	0.35	0.65	0.30	0.95	0.25	0.65
FSMD075-24R	4.37	4.73	3.07	3.41	0.80	1.55	0.25	0.95	0.25	0.65
FSMD075-33R	4.37	4.73	3.07	3.41	0.80	1.55	0.25	0.95	0.25	0.65
FSMD110-R	4.37	4.73	3.07	3.41	0.25	0.55	0.30	0.95	0.25	0.65
FSMD110-16-R	4.37	4.73	3.07	3.41	0.25	0.90	0.30	0.95	0.25	0.65
FSMD110-24R	4.37	4.73	3.07	3.41	0.80	1.30	0.25	0.95	0.25	0.65
FSMD125-R	4.37	4.73	3.07	3.41	0.25	0.55	0.30	0.95	0.25	0.65
FSMD125-16R	4.37	4.73	3.07	3.41	0.50	1.00	0.30	0.95	0.25	0.65
FSMD150-R	4.37	4.73	3.07	3.41	0.25	0.55	0.30	0.95	0.25	0.65
FSMD150-12R	4.37	4.73	3.07	3.41	0.60	1.10	0.25	0.95	0.25	0.65
FSMD150-24R	4.37	4.73	3.07	3.41	0.60	1.55	0.25	0.95	0.25	0.65
FSMD160-R	4.37	4.73	3.07	3.41	0.25	0.90	0.30	0.95	0.25	0.65
FSMD160-12R	4.37	4.73	3.07	3.41	0.60	1.35	0.25	0.95	0.25	0.65
FSMD160-16R	4.37	4.73	3.07	3.41	0.60	1.35	0.25	0.95	0.25	0.65
FSMD200R	4.37	4.73	3.07	3.41	0.55	1.20	0.25	0.95	0.25	0.65
FSMD200-16R	4.37	4.73	3.07	3.41	0.60	1.55	0.25	0.95	0.25	0.65
FSMD260R	4.37	4.73	3.07	3.41	0.55	1.20	0.25	0.95	0.25	0.65
FSMD260-13R	4.37	4.73	3.07	3.41	0.80	1.55	0.25	0.95	0.25	0.65
FSMD260-16R	4.37	4.73	3.07	3.41	0.80	1.55	0.25	0.95	0.25	0.65
FSMD300R	4.37	4.73	3.07	3.41	0.80	1.55	0.25	0.95	0.25	0.65

NOTE : Specification subject to change without notice.




### 5. Thermal Derating Curve



- A=** FSMD075-R, 075-24R, 075-33R, 110-R, 110-16-R, 110-24R, 125-R, 125-16R, 150-R, 150-12R, 150-24R, 160-R, 160-12R, 160-16R, 200R, 200-16R, 260R, 260-13R, 260-16R, 300R
- B=** FSMD010-R, 014-R, 020-R, 020-60-R, 030-R, 035-R, 035-30-R, 050-R, 050-30-R

### 6. Typical Time-To-Trip at 23°C

- A =** FSMD010-R
- B =** FSMD014-R
- C =** FSMD020-R / 020-60-R
- D =** FSMD030-R
- E =** FSMD035-R / 035-30-R
- F =** FSMD050-R / 050-30-R
- G =** FSMD075-R / 075-24R / 075-33R
- H =** FSMD110-R / 110-16-R / 110-24R
- I =** FSMD125-R / 125-16R
- J =** FSMD150-R / 150-12R / 150-24R
- K =** FSMD160-R / 160-12R / 160-16R
- L =** FSMD200R / 200-16R
- M =** FSMD260R / 260-13R / 260-16R
- N =** FSMD300R



NOTE : Specification subject to change without notice.



### 7. Material Specification



Terminal pad material: Pure Tin

Soldering characteristics: Meets EIA specification RS 186-9E, ANSI/J-std-002 Category 3

### 8. Part Numbering and Marking System

#### Part Numbering System

F S M D □ □ □ - R




F110

Example



#### Part Marking System

F □ □ □



OR


F S M D □ □ □ - □ □ - R



F 110  
16

Example

F □ □ □  
□ □



**Warning:** -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.




-PPTC device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.

-Avoid contact of PPTC device with chemical solvent. Prolonged contact will damage the device performance.



### 9. Pad Layouts 、 Solder Reflow and Rework Recommendations

The dimension in the table below provide the recommended pad layout for each FSMD1812 device



Pad dimensions (millimeters)			
Device	A Nominal	B Nominal	C Nominal
All 1812 Series	3.45	1.78	3.50

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (T <sub>smax</sub> to T <sub>p</sub> )	3 °C/second max.
Preheat :	
Temperature Min (T <sub>smin</sub> )	150 °C
Temperature Max (T <sub>smax</sub> )	200 °C
Time (t <sub>smin</sub> to t <sub>smax</sub> )	60-180 seconds
Time maintained above:	
Temperature(T <sub>L</sub> )	217 °C
Time (t <sub>L</sub> )	60-150 seconds
Peak/Classification Temperature(T <sub>p</sub> ) :	260 °C
Time within 5°C of actual Peak :	
Temperature (t <sub>p</sub> )	20-40 seconds
Ramp-Down Rate :	6 °C/second max.
Time 25 °C to Peak Temperature :	8 minutes max.

#### Solder reflow


- ※ Due to “Lead Free” nature, Temperature and Dwelling time for the soldering zone is higher than those for Regular. This may cause damage to other components.
- 1. Recommended max past thickness > 0.25mm.
- 2. Devices can be cleaned using standard methods and aqueous solvent.
- 3. Rework use standard industry practices.
- 4. Storage Environment : < 30°C / 60%RH

#### Caution:

1. If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
2. Devices are not designed to be wave soldered to the bottom side of the board.

Note 1: All temperatures refer to of the package, measured on the package body surface.

#### Reflow Profile



NOTE : Specification subject to change without notice.