

Is Now Part of



# **ON Semiconductor**®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor dates sheds, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor dates sheds and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use on similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor and its officers, employees, subsidiaries, affliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any lay bed ON Semiconductor and its officers, employees, ween if such claim alleges that ON Semiconductor was negligent regarding the d




#### November 2013

# FGA15N120ANTDTU 1200 V, 15 A NPT Trench IGBT

### **Features**

- NPT Trench Technology, Positive temperature coefficient
- Low Saturation Voltage: V<sub>CE(sat), typ</sub> = 1.9 V @  $I_C = 15$  A and  $T_C = 25^{\circ}C$
- + Low Switching Loss:  $E_{off, \ typ}$  = 0.6 mJ @ I\_C = 15 A and T\_C = 25°C
- Extremely Enhanced Avalanche Capability





cation such as induction heating, microwave oven.

Description

easy parallel operation.

## **Absolute Maximum Ratings**

Symbol	Description		Ratings	Unit	
V <sub>CES</sub>	Collector-Emitter Voltage		1200	V	
V <sub>GES</sub>	Gate-Emitter Voltage		± 20	V	
I <sub>C</sub>	Collector Current	@ $T_{C} = 25^{\circ}C$	30	A	
	Collector Current	@ T <sub>C</sub> = 100°C	15	A	
I <sub>CM</sub>	Pulsed Collector Current (Note 1)		45	A	
I <sub>F</sub>	Diode Continuous Forward Current	@ T <sub>C</sub> = 25°C	30	A	
	Diode Continuous Forward Current	@ T <sub>C</sub> = 100°C	15	A	
I <sub>FM</sub>	Diode Maximum Forward Current		45	A	
P <sub>D</sub>	Maximum Power Dissipation	@ $T_{C} = 25^{\circ}C$	186	W	
	Maximum Power Dissipation	@ T <sub>C</sub> = 100°C	74	W	
TJ	Operating Junction Temperature		-55 to +150	°C	
T <sub>stg</sub>	Storage Temperature Range		-55 to +150	°C	
TL	Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds		300	°C	

#### **Thermal Characteristics**

Symbol	ymbol Parameter		Max.	Unit
$R_{ ext{ heta}JC}$	Thermal Resistance, Junction-to-Case for IGBT		0.67	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case for Diode		2.88	°C/W
$R_{\thetaJA}$	P <sub>0JA</sub> Thermal Resistance, Junction-to-Ambient		40	°C/W

Notes:

(1) Repetitive rating: Pulse width limited by max. junction temperature

FGA15N120ANTDTU — 1200 V, 15 A NPT Trench IGBT

Part Number         Top Mark           FGA15N120ANTDTU_F109         FGA15N120ANTDTU		Top Mark	Package Packing Method		Reel Size	Tape Width		Quantity
		FGA15N120ANTDTU	TO-3P	Tube	N/A	N/A		30
Electric	al Characte	eristics of the I		<sup>2</sup> C unless otherwise note	d	1		
Symbol	1	arameter		t Conditions	Min.	Тур.	Max	Unit
Off Charac	teristics							
ICES	Collector Cut-Of	f Current	$V_{CE} = V_{CES}, V_{GE} = 0 V$				3	mA
I <sub>GES</sub>	G-E Leakage Current		$V_{GE} = V_{GES}, V_{CE} = 0 V$				± 250	nA
							•	
On Charac		· · ·				0.7		
V <sub>GE(th)</sub>	G-E Threshold \			$V_{CE} = V_{GE}$	4.5	6.5	8.5	V
V <sub>CE(sat)</sub>	Collector to Emitter Saturation Voltage		I <sub>C</sub> = 15 A, V <sub>GE</sub> = 15 V			1.9	2.4	V
			$I_{C} = 15 \text{ A},  V_{GE} = 15 \text{ V},$ $T_{C} = 125^{\circ}\text{C}$			2.2		V
			I <sub>C</sub> = 30 A,	V <sub>GE</sub> = 15 V		2.3		V
Dvnamic C	haracteristics							
C <sub>ies</sub>		nput Capacitance $V_{CE} = 30 \text{ V}, \text{ V}_{GE} = 0 \text{ V},$			2650		pF	
C <sub>oes</sub>	Output Capacita	nce	f = 1 MHz			143		pF
C <sub>res</sub>	Reverse Transfe		-			96		pF
_	g Characteristics Turn-On Delay Time		V - 600	V <sub>CC</sub> = 600 V, I <sub>C</sub> = 15 A,		15		
t <sub>d(on)</sub>	Rise Time	inte	$R_{G} = 10 \Omega, V_{GE} = 15 V,$ Inductive Load, $T_{C} = 25^{\circ}C$			-		ns
t <sub>r</sub>		imo				20 160		ns
t <sub>d(off)</sub>	Turn-Off Delay T Fall Time	Inte				100	180	ns
t <sub>f</sub>	Turn-On Switchi		_			3		ns
E <sub>on</sub>			_			0.6	4.5 0.9	mJ mJ
E <sub>off</sub>	Turn-Off Switchi	5						
E <sub>ts</sub>	Total Switching I Turn-On Delay 1		$V_{CC} = 600 \text{ V}, \text{ I}_{C} = 15 \text{ A},$ $R_{G} = 10 \Omega, \text{ V}_{GE} = 15 \text{ V},$ Inductive Load, T <sub>C</sub> = 125°C			3.6 15	5.4	mJ
t <sub>d(on)</sub>	Rise Time					20		ns
t <sub>r</sub>	Turn-Off Delay T	ïme				170		ns
t <sub>d(off)</sub>	Fall Time	inte				150		ns
t <sub>f</sub> E <sub>on</sub>	Turn-On Switchi	naloss				3.2	4.8	mJ
	Turn-Off Switchi	-				0.8	1.2	mJ
E <sub>off</sub> E <sub>ts</sub>	Total Switching I	•				4.0	6.0	mJ
	Total Gate Charg		Ve= = 600	V = 15		4.0	180	nC
Qg			$V_{CE} = 600 \text{ V}, \text{ I}_{C} = 15 \text{ A},$ $V_{GE} = 15 \text{ V}$					
Q <sub>ge</sub>	Gate-Emitter Ch	orao	$V_{GF} = 10$ V			16	22	nC

Symbol V <sub>FM</sub>	Parameter	Test Conditions		Min.	Тур.	Max.	Unit
	Diode Forward Voltage	I <sub>F</sub> = 15 A	$T_{C} = 25^{\circ}C$		1.7	2.7	V
			T <sub>C</sub> = 125°C		1.8		
rr Diode Reverse	Diode Reverse Recovery Time	I <sub>F</sub> = 15 A di <sub>F</sub> /dt = 200 A/μs	$T_{C} = 25^{\circ}C$		210	330	ns
			T <sub>C</sub> = 125°C		280		
I <sub>rr</sub> Diode Peak Reverse Recovery rent	Diode Peak Reverse Recovery Cur-		$T_{C} = 25^{\circ}C$		27	40	А
	rent		T <sub>C</sub> = 125°C		31		
Q <sub>rr</sub>	Diode Reverse Recovery Charge		$T_{\rm C} = 25^{\circ}{\rm C}$		2835	6600	nC
			T <sub>C</sub> = 125°C		4340		

FGA15N120ANTDTU — 1200 V, 15 A NPT Trench IGBT

## **Typical Performance Characteristics**

#### Figure 1. Typical Output Characteristics




Figure 2. Typical Saturation Voltage Characteristics




Figure 3. Saturation Voltage vs. Case Temperature at Variant Current Level




Figure 5. Saturation Voltage vs. V<sub>GE</sub>






Figure 4. Saturation Voltage vs. V<sub>GE</sub>




**Figure 6. Capacitance Characteristics** 



FGA15N120ANTDTU — 1200 V, 15 A NPT Trench IGBT

### Typical Performance Characteristics (Continued)

Figure 7. Turn-On Characteristics vs. Gate Resistance



# Figure 8. Turn-Off Characteristics vs. Gate Resistance






Figure 9. Switching Loss vs. Gate Resistance








Figure 10. Turn-On Characteristics vs. Collector Current








Figure 12. Switching Loss vs. Collector Current



FGA15N120ANTDTU — 1200 V, 15 A NPT Trench IGBT









SEMICONDUCTOR

#### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

®

AccuPower™ AX-CAF BitSiC™ Build it Now™ CorePLUS™ CorePOWER™ CROSSVOLT™ CTL™ Current Transfer Logic™ DEUXPEED® Dual Cool™ EcoSPARK<sup>®</sup> EfficentMax™ ESBC™

R Fairchild® Fairchild Semiconductor® FACT Quiet Series™ FACT® FAST® FastvCore™ FETBench™ FPS™

FRFET® Global Power Resource<sup>SM</sup> GreenBridge™ Green FPS™ Green FPS™ e-Series™ G*max*™ GTO™ IntelliMAX™ **ISOPLANAR™** Marking Small Speakers Sound Louder and Better™ MegaBuck™ MICROCOUPLER™ MicroFET<sup>™</sup> MicroPak™ MicroPak2™ MillerDrive™ MotionMax<sup>™</sup> mWSaver<sup>®</sup> OptoHiT™ **OPTOLOGIC<sup>®</sup> OPTOPLANAR<sup>®</sup>** 

F-PFS™

PowerTrench<sup>®</sup> PowerXS™ Programmable Active Droop™ **QFĔT**® QS™ Quiet Series™ RapidConfigure™ тм Saving our world, 1mW/W/kW at a time™ SignalWise™ SmartMax™ SMART START Solutions for Your Success™ SPM<sup>®</sup> STEALTH™ SuperFET<sup>®</sup> SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS® SyncFET™

Sync-Lock™ **GENERAL** <sup>®'</sup> TinyBoost TinyBuck<sup>®</sup> TinyCalc™ TinyLogic® TINYOPTO™ TinyPower™ TinyPWM™ TinyWire™ TranSiC™ TriFault Detect™ TRUECURRENT®\* µSerDes™  $\mu_{_{
m Ser}}$ UHC®

FGA15N120ANTDTU — 1200 V, 15 A NPT Trench IGBT

Ultra FRFET™ UniFET™ VCX™ VisualMax™ VoltagePlus™ XS™

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

- Life support devices or systems are devices or systems which, (a) are 1. intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support. Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their

parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

### PRODUCT STATUS DEFINITIONS Definition of Terms

Datasheet Identification	Product Status	Definition		
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.		
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		