ON Semiconductor

Is Now

To learn more about onsemi™, please visit our website at
www.onsemi.com

NGTG30N60FWG

IGBT

This Insulated Gate Bipolar Transistor (IGBT) features a robust and cost effective Trench construction, and provides superior performance in demanding switching applications, offering both low on state voltage and minimal switching loss.

Features

- Optimized for Very Low V_{CEsat}
- Low Switching Loss Reduces System Power Dissipation
- 5 μs Short−Circuit Capability
- These are Pb−Free Devices

Typical Applications

- Power Factor Correction

ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector−emitter voltage	V_{CES}	600	V
Collector current @ T_C = 25°C @ T_C = 100°C	I_C	 60 30	A
Pulsed collector current, T_{pulse} limited by T_{Jmax}	I_{CM}	120	A
Short−circuit withstand time V_{GE} = 15 V, V_{CE} = 300 V, $T_J \leq$ +150°C	t_{SC}	5	μs
Gate−emitter voltage Transient Gate Emitter Voltage (t_p = 5 μs, D < 0.010)	V_{GE}	±20 ±30	V
Power Dissipation @ T_C = 25°C @ T_C = 100°C	P_D	 167 67	W
Operating junction temperature range	T_J	−55 to +150	°C
Storage temperature range	T_{stg}	−55 to +150	°C
Lead temperature for soldering, 1/8” from case for 5 seconds	T_{SLD}	260	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

ON Semiconductor®

http://onsemi.com

30 A, 600 V
V_{CEsat} = 1.5 V





TO−247
CASE 340L
STYLE 4

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

ORDERING INFORMATION

Device	Package	Shipping
NGTG30N60FWG	TO−247 (Pb−Free)	30 Units / Rail

THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal resistance junction−to−case, for IGBT	$R_{\theta JC}$	0.75	°C/W
Thermal resistance junction−to−ambient	$R_{\theta JA}$	40	°C/W

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
STATIC CHARACTERISTIC						
Collector−emitter breakdown voltage, gate−emitter short−circuited	V_{GE} = 0 V, I_C = 500 μA	$V_{(BR)CES}$	600	−	−	V
Collector−emitter saturation voltage	V_{GE} = 15 V, I_C = 30 A V_{GE} = 15 V, I_C = 30 A, T_J = 150°C	V_{CEsat}	1.25 −	1.45 1.75	1.70 −	V
Gate−emitter threshold voltage	V_{GE} = V_{CE}, I_C = 200 μA	$V_{GE(th)}$	4.5	5.5	6.5	V
Collector−emitter cut−off current, gate−emitter short−circuited	V_{GE} = 0 V, V_{CE} = 600 V V_{GE} = 0 V, V_{CE} = 600 V, T_J = 150°C	I_{CES}	− −	− −	0.2 2	mA
Gate leakage current, collector−emitter short−circuited	V_{GE} = 20 V , V_{CE} = 0 V	I_{GES}	−	−	100	nA
DYNAMIC CHARACTERISTIC						
Input capacitance	V_{CE} = 20 V, V_{GE} = 0 V, f = 1 MHz	C_{ies}	−	4100	−	pF
Output capacitance		C_{oes}	−	115	−	
Reverse transfer capacitance		C_{res}	−	95	−	
Gate charge total	V_{CE} = 480 V, I_C = 30 A, V_{GE} = 15 V	Q_g		170		nC
Gate to emitter charge		Q_{ge}		34		
Gate to collector charge		Q_{gc}		83		
SWITCHING CHARACTERISTIC, INDUCTIVE LOAD						
Turn−on delay time	T_J = 25°C V_{CC} = 400 V, I_C = 30 A R_g = 10 Ω V_{GE} = 0 V/ 15 V*	$t_{d(on)}$		81		ns
Rise time		t_r		31		
Turn−off delay time		$t_{d(off)}$		190		
Fall time		t_f		110		
Turn−on switching loss		E_{on}		0.65		mJ
Turn−off switching loss		E_{off}		0.65		
Total switching loss		E_{ts}		1.30		
Turn−on delay time	T_J = 150°C V_{CC} = 400 V, I_C = 30 A R_g = 10 Ω V_{GE} = 0 V/ 15 V*	$t_{d(on)}$		80		ns
Rise time		t_r		32		
Turn−off delay time		$t_{d(off)}$		200		
Fall time		t_f		230		
Turn−on switching loss		E_{on}		0.80		mJ
Turn−off switching loss		E_{off}		1.1		
Total switching loss		E_{ts}		1.90		

*Includes diode reverse recovery loss using NGTB30N60FWG.

TYPICAL CHARACTERISTICS



Figure 1. Output Characteristics



Figure 2. Output Characteristics



Figure 3. Output Characteristics



Figure 4. Typical Transfer Characteristics



Figure 5. $V_{CE(sat)}$ vs. T_J



Figure 6. Typical Capacitance

TYPICAL CHARACTERISTICS



Figure 7. Typical Gate Charge



Figure 8. Switching Loss vs. Temperature



Figure 9. Switching Time vs. Temperature



Figure 10. Switching Loss vs. I_C



Figure 11. Switching Time vs. I_C

TYPICAL CHARACTERISTICS



Figure 12. Switching Loss vs. Rg



Figure 13. Switching Time vs. Rg



Figure 14. Switching Loss vs. V_{CE}



Figure 15. Switching Time vs. V_{CE}



Figure 16. Safe Operating Area



Figure 17. Reverse Bias Safe Operating Area

TYPICAL CHARACTERISTICS



R_i (°C/W)	τ_i (sec)
0.03276	1.0E−4
0.07477	6.84E−5
0.12790	0.002
0.17518	0.03
0.22911	0.1
0.11135	2.0

Figure 18. IGBT Transient Thermal Impedance



Figure 19. Test Circuit for Switching Characteristics



Figure 20. Definition of Turn On Waveform



Figure 21. Definition of Turn Off Waveform

PACKAGE DIMENSIONS

TO−247
CASE 340L−02
ISSUE F



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.

	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
A	20.32	21.08	0.800	8.30
B	15.75	16.26	0.620	0.640
C	4.70	5.30	0.185	0.209
D	1.00	1.40	0.040	0.055
E	1.90	2.60	0.075	0.102
F	1.65	2.13	0.065	0.084
G	5.45 BSC		0.215 BSC	
H	1.50	2.49	0.059	0.098
J	0.40	0.80	0.016	0.031
K	19.81	20.83	0.780	0.820
L	5.40	6.20	0.212	0.244
N	4.32	5.49	0.170	0.216
P	---	4.50	---	0.177
Q	3.55	3.65	0.140	0.144
U	6.15 BSC		0.242 BSC	
W	2.87	3.12	0.113	0.123

STYLE 4:
PIN 1. GATE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative