


1.4(H)mm, 1.5/2.0mm-travel Surface Mount Type SSSS8 Series

Part number			SSSS820501
Travel			1.5mm
Actuator directions			Vertical
Actuator thickness			0.8mm
Poles			2
Positions			3
Operating force			Refer to the dimensions
Changeover timing			Not specified
Ground terminal			With
Soldering			Reflow
Operating temperature range			-40℃ to +85℃
Rating (max.)/(min.) (Resistive load)			0.3A 5V DC/50µA 3V DC
Electrical performance	Contact resistance (Initial performance	/After lifetime)	70mΩ max./130mΩ max.
	Insulation resistance	2	100MΩ min. 100V DC
	Voltage proof		100V AC for 1 minute
Mechanical performance	Terminal strength		3N for 1 minute
	Actuator strength	Operating direction	10N
		Pulling direction	10N
Durability	Operating life without load		10,000 cycles 100mΩ max.
	Operating life with le (at max. rated load		10,000 cycles 130m Ω max.


SSSS8 Series - Basic information

Environmental performance	Cold		-40℃ 500h
	Dry heat		85℃ 500h
	Damp he	eat	60℃, 90 to 95%RH 500h
Minimum order unit (pcs.)		Japan	1,800
		Export	7,200


Photo



Dimensions




Land Dimensions




Viewed from direction A in the dimensions.

Circuit Diagram



Packing Specifications

Taping



Number of packages (pcs.)	1 reel	1,800
	1 case / Japan	3,600
	1 case / export packing	7,200

2017/6/19	SSSS8 Series - Basic information
Reel width W(mm)	25.4
Tape width (mm)	24
Export package measurements (mm)	406×406×190

Soldering Conditions

Example of Reflow Soldering Condition


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2 Φ CA (K) or CC (T) at soldering portion (copper foil surface). A heat resisting tape should be used for fixed measurement.

3. Temperature profile



(1) The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.

(2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Reference for Hand Soldering

Soldering temperature	330±5℃
Soldering time	3s max.

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).
- 3. Products other than those listed in the above chart are also available. Please contact us for details.
- 4. Please contact us for automotive use products.