



# $2.8 \times 2.4 \text{mm}$ Compact Type with Projection (Surface Mount) SKSF Series

Туре		Surface mount
Operating force		1.6N
Operating direction		Top push
Travel		0.1mm
Operating life (5mA 5V DC)		100,000 cycles
Initial contact resistance		100m $\Omega$ max.
Series type		Sharp feeling type
Operating temperature range		-30℃ to +85℃
Rating (max.)		50mA 12V DC
Rating (min.)		10μA 1V DC
Electrical performance	Insulation resistance	100M $\Omega$ min. 100V DC for 1min.
	Voltage proof	100V AC for 1 min.
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively
Environmental performance	Cold	-30±2℃ for 96h
	Dry heat	80±2℃ for 96h
	Damp heat	60±2℃, 90 to 95%RH for 96h
Minimum order unit (pcs.)	Japan	20,000
	Export	20,000


## **Dimensions**



## Land Dimensions




Circuit Diagram



# **Packing Specifications**

## **Taping**



Number of packages (pcs.)	s 1 reel	20,000
	1 case / Japan	200,000
	1 case / export packing	200,000
Tape width (mm)		12
Export package measurements (mm)		395×395×205

# **Soldering Conditions**

## **Condition for Reflow**


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2  $\Phi$  CA(K) or CC(T) at solder joints (copper foil surface). A heat resisting tape should be used for fix measurement.

3. Temperature profile



- (1) The above temperature shall be measured of the top of switch. There are cases where PC board's temperature greatly differs from that of the switch, depending on the material, size, thickness of PC board's and others. Care, should be taken to prevent the switch's surface temperature from exceeding  $260^{\circ}$ C.
- (2) Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

#### **Manual Soldering**

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

- 1. Consult with us for availability of TACT switch™ washing.
- 2. Prevent flux penetration from the top side of the TACT switch™.
- 3. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 4. The second soldering should be done after the switch returns to normal temperature.

#### Notes are common to this series/models.

- 1. Please place purchase orders for taping products per minimum order unit (1 reel or a case).
- 2. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 3. For  $\phi$ 330mm diameter reel requirements, please contact us.
- 4. Please contact us for automotive use products.