

#### **Features**

- Low Power Consumption
- Wide Common-Mode and Differential Voltage Ranges
- Low Input Bias and Offset Currents
- **Output Short-Circuit Protection**
- Low Total Harmonic Distortion...0.003% Typ
- Low Noise Vn=  $18nV/\sqrt{HZ}$  Typ at f=1kHz
- High Input Impedance...JFET-Input Stage
- Internal Frequency Compensation
- Latch-Up-Free Operation
- High Slew Rate...13V/µs Typ
- Common-Mode Input Voltage Range Includes Vcc+
- SOP-8L: Available in "Green" Molding Compound
- Lead Free Finish/ RoHS Compliant (Note 1)


### **General Description**

The JFET-input operational amplifiers in the TL072 are similar to the TL082, with low input bias and offset currents and fast slew rate. The low harmonic distortion and low noise make the TL072 ideally suited for high-fidelity and audio preamplifier applications. Each amplifier features JFET inputs (for high input impedance) coupled with bipolar output stages integrated on a single monolithic chip.

### **Applications**

- Active filters
- Audio pre-amps

#### **Ordering Information**



	Device	Package	Packaging	13" Tape and Reel			
		Code	(Note 2)	Quantity	Part Number Suffix		
Pb,	TL072SG-13	S	SOP-8L	2500/Tape & Reel	-13		


Notes:

- 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied. Please visit our website at
- http://www.diodes.com/products/lead\_free.html
  2. Pad layout as shown on Diodes Inc. suggested pad layout document AP02001, which can be found on our website at http://www.diodes.com/datasheets/ap02001.pdf.



### **Pin Assignments**


#### (1) Dual channel SOP-8L



### **Pin Descriptions**

Pin Name	Pin No.	Description	
OUTPUT1	1	Channel 1 Output	
INVERTING INPUT1	2	Channel 1 Inverting Input	
NON-INVERTING INPUT1	3	Channel 1 Non-inverting Input	
V <sub>CC</sub> -	4	Supply Voltage	
NON-INVERTING INPUT2	5	Channel 2 Non-inverting Input	
INVERTING INPUT2	6	Channel 2 Inverting Input	
OUTPUT2	7	Channel 2 Ouput	
V <sub>CC</sub> +	8	Supply Voltage	

## **Block Diagram**





#### **Absolute Maximum Ratings** (Note 8)

Symbol	Parameter	Rating	Unit
ESD HBM	Human Body Model ESD Protection	1	KV
ESD MM	SD MM Machine Model ESD Protection		V
V <sub>CC</sub> +	V <sub>CC</sub> + Supply Voltage + (Note 3)		V
V <sub>cc</sub> -	V <sub>CC</sub> - Supply Voltage - (Note 3)		V
Vı	Input voltage (Notes 3 and 5)	±15	V
$V_{ID}$	Differential input Voltage, V <sub>ID</sub> (Note 4)	±30	V
	Duration of output short circuit (Note 6)	Unlimited	
$P_{D}$	Power Dissipation (Note 7)	860	mW
$T_J$	T <sub>J</sub> Operating Junction Temperature Range		°C
T <sub>ST</sub>	Storage Temperature Range	-65 to +150	°C

Notes:

- 3. ALL voltage values, except differential voltages, are with respect to the midpoint between V<sub>CC</sub>+ and V<sub>CC</sub>-.
- 4. Differential voltage are at the non-inverting input terminal with respect to the inverting input terminal.
- 5. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15V, whichever is less.

  6. The output may be shorted to ground or either supply. Temperature and/or supply voltage must be limited to ensure that the dissipation rating is not exceeded.
- 7. Maximum power dissipation is a function of T<sub>J</sub>(max),  $\theta_{JA}$ , and T<sub>A</sub>. The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_J(max) - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of 150°C can affect reliability

#### **Recommended Operating Conditions** (Note 8)

Symbol	Description	Rating	Unit
V <sub>CC</sub> ±	Supply Voltage	±15	V
T <sub>A</sub>	Operating Ambient Temperature Range	-40 to +85	°C

Notes: 8. Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Recommended Operating Conditions indicate conditions for which the device is intended to be functional, but specific performance is not guaranteed. For guaranteed specifications and the test conditions, see the Electrical Characteristics.




## Electrical Characteristics (V<sub>CC±</sub> = ±15V, T<sub>A</sub> = 25 °C; unless otherwise noted)


Symbol	Parameter	Test Conditions		Min	Тур.	Max	Unit	
W	Input Offset Voltage	V <sub>O</sub> =0,	T <sub>A</sub> =25 °C		3	6	m\/	
V <sub>IO</sub>	Input Offset Voltage	$R_s=50\Omega$	T <sub>A</sub> = full range			8	mV	
$^{\alpha}V_{IO}$	Temperature Coefficient of Input Offset Voltage	$V_O=0$ , $R_S=50\Omega$ , $T_A=$ full range			18		μV/°C	
I <sub>IO</sub>	Input Offset Current	V <sub>O</sub> =0	T <sub>A</sub> =25 °C		5	100	pА	
IO	input onset ourrent	V <sub>0</sub> =0	T <sub>A</sub> = full range			2	nA	
I <sub>IB</sub>	Input Bias Current	V <sub>O</sub> =0	T <sub>A</sub> =25 °C		65	200	pА	
·ID		*0=0	T <sub>A</sub> = full range			20	nA	
$V_{ICR}$	Common Mode Input Voltage Range			±11	-12~+15		V	
	Maximum Peak	$R_L=10k\Omega$ , $T_A=25$ °C		±12	±13.5			
$V_{OM}$		$R_L \ge 10 k\Omega$ ,	T full rooms	±12			V	
	Output Voltage Swing	$R_L \ge 2k\Omega$	T <sub>A</sub> = full range	±10				
	Large Signal Differential	V <sub>O</sub> =±10V,	T <sub>A</sub> =25 °C	50	200		\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	
$A_{VD}$	Voltage Amplification	$R_L {\geqq} 2k\Omega$	T <sub>A</sub> = full range	25			V/mV	
B <sub>1</sub>	Unity Gain Bandwidth				3		MHz	
r <sub>i</sub>	Input Resistance	T <sub>A</sub> =25 °C			10 <sup>12</sup>		Ω	
CMRR	Common Mode Rejection Ratio	$V_{IC}=V_{ICRmin}, V_O=0$ $R_S=50\Omega, T_A=25$ °C		75	100		dB	
<b>k</b> <sub>SVR</sub>	Supply Voltage Rejection Ratio (ΔV <sub>CC</sub> ±/ΔV <sub>IO</sub> )	$V_{CC}$ =±9 to ±15V $V_{O}$ =0 $R_{S}$ =50 $\Omega$ , $T_{A}$ =25 °C		80	100		dB	
I <sub>CC</sub>	Supply Current (each amplifier)	V <sub>O</sub> =0, T <sub>A</sub> =25 °C No load			1.4	2.5	mA	
V <sub>O1</sub> /V <sub>O2</sub>	Crosstalk Attenuation	A <sub>VD</sub> =100, T <sub>A</sub> =25 °C			120		dB	
SR	Slew Rate at Unity Gain	V <sub>I</sub> =10V, C <sub>L</sub> = (See Figure	100pF, R <sub>L</sub> =2kΩ 1)	8	13		V/µs	
tr	Rise Time	V <sub>I</sub> =20mV, R <sub>L</sub>	=2kΩ, C <sub>L</sub> =100pF		0.1		μs	
	Overshoot Factor	(See Figure 1)			20		%	
Vn	voltage	R <sub>S</sub> =20Ω	f=1kHz		18		$nV/\sqrt{HZ}$	
			f=10 Hz to 10kHz		4	1	μV	
In	Equivalent Input Noise Current	$R_S=20\Omega$ , f=1kHz			0.01		pA/√HZ	
THD	Total Harmonic Distortion	$\label{eq:V_Irms} \begin{split} V_{Irms} = & 6V, \ A_{VD} = 1, \\ R_L & \geq & 2k\Omega, \ R_S \leq 1k\Omega, \\ f = & 1kHz \end{split}$			0.003		%	
$\theta_{JA}$	Thermal Resistance Junction-to-Ambient	SOP-8L (Note 9)			145		°C/W	
$\theta_{JC}$	Thermal Resistance Junction-to-Case	SOP-8L (Note 9)			35		°C/W	


Notes: 9. Test condition for SOP-8L: Devices mounted on FR-4 substrate PC board, with minimum recommended pad layout.




## **Typical Performance Characteristics**















### Typical Performance Characteristics (Continued)















### Typical Performance Characteristics (Continued)















### Typical Performance Characteristics (Continued)











### **Test Circuit**





Figure 1. Unity-Gain Amplifier

Figure 2. Gain-of-10 Inverting Amplifier

### **Marking Information**


#### (1) SOP-8L





## Package Information (All Dimensions in mm)

#### (1) Package type: SOP-8L





#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2009, Diodes Incorporated

www.diodes.com