

March 2015

FDD8444

N-Channel PowerTrench $^{\circledR}$ MOSFET 40V, 50A, 5.2m Ω


Features


- Typ $r_{DS(on)}$ = 4m Ω at V_{GS} = 10V, I_D = 50A
- Typ $Q_{g(10)}$ = 89nC at V_{GS} = 10V
- Low Miller Charge
- Low Q_{rr} Body Diode
- UIS Capability (Single Pulse/ Repetitive Pulse)
- Qualified to AEC Q101
- RoHS Compliant



Applications

- Automotive Engine Control
- Powertrain Management
- Solenoid and Motor Drivers
- Electronic Transmission
- Distributed Power Architecture and VRMs
- Primary Switch for 12V Systems





MOSFET Maximum Ratings $T_C = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Ratings	Units
V_{DSS}	Drain to Source Voltage	40	V
V_{GS}	Gate to Source Voltage	±20	V
	Drain Current Continuous (V _{GS} = 10V) (Note 1)	145	
I_D	Continuous ($V_{GS} = 10V$, with $R_{\theta JA} = 52^{\circ}C/W$)	20	Α
	Pulsed	Figure 4	
E _{AS}	Single Pulse Avalanche Energy (Note 2)	535	mJ
В	Power Dissipation	153	W
P_{D}	Derate above 25°C	1.02	W/°C
T _J , T _{STG}	Operating and Storage Temperature	-55 to +175	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	0.98	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient TO-252, 1in ² copper pad area	52	°C/W

Package Marking and Ordering Information

Parameter

Gate to Source Leakage Current

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDD8444	FDD8444	TO-252AA	13"	16mm	2500 units

Electrical Characteristics $T_J = 25$ °C unless otherwise noted

Off Characteristics							
B _{VDSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$		40	-	-	V
	Zero Gate Voltage Drain Current	V _{DS} = 32V		-	-	1	^
I _{DSS} Zero Gate voltage Drain Current	V= 0V	. = 150°C	_	_	250	μΑ	

 $V_{GS} = \pm 20V$

Test Conditions

Min

Тур

Max

±100

Units

nΑ

On Characteristics

Symbol

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu A$	2	2.5	4	V
		$I_D = 50A, V_{GS} = 10V$	-	4	5.2	
r _{DS(on)}		$I_D = 50A$, $V_{GS} = 10V$, $T_J = 175$ °C	-	7.2	9.4	mΩ

Dynamic Characteristics

C _{iss}	Input Capacitance	V 05V V	V 05)/ V/ 0)/		6195	-	pF
C _{oss}	Output Capacitance	V _{DS} = 25V, V _{GS} = (- f = 1MHz	JV,	-	585	-	pF
C _{rss}	Reverse Transfer Capacitance	1 - 11/11/12		-	332	-	pF
R_G	Gate Resistance	f = 1MHz		-	1.9	-	Ω
$Q_{g(TOT)}$	Total Gate Charge at 10V	V _{GS} = 0 to 10V		-	89	116	nC
$Q_{g(5)}$	Total Gate Charge at 5V	$V_{GS} = 0 \text{ to } 5V$	1		43	56	nC
$Q_{g(TH)}$	Threshold Gate Charge	$V_{GS} = 0 \text{ to } 2V$	$V_{DD} = 20V$ $I_{D} = 50A$	-	11	14.3	nC
Q_{gs}	Gate to Source Gate Charge		$I_0 = 30A$ $I_0 = 1.0mA$	-	23	-	nC
Q _{gs2}	Gate Charge Threshold to Plateau		.g	-	11	-	nC
Q_{gd}	Gate to Drain "Miller" Charge			-	20	-	nC

Electrical Characteristics T_J = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units

Switching Characteristics

t _{on}	Turn-On Time		-	-	135	ns
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 20V, I_D = 50A$ $V_{GS} = 10V, R_{GS} = 2\Omega$	-	12	-	ns
t _r	Turn-On Rise Time		-	78	-	ns
t _{d(off)}	Turn-Off Delay Time		-	48	-	ns
t _f	Turn-Off Fall Time		-	15	-	ns
t _{off}	Turn-Off Time		-	-	95	ns

Drain-Source Diode Characteristics

V	V _{SD} Source to Drain Diode Voltage	I _{SD} = 50A	-	0.9	1.25	1/	
V SD		I _{SD} = 25A	1	0.8	1.0	V	
t _{rr}	Reverse Recovery Time	$I_{\rm F} = 50$ A, $dI_{\rm F}/dt = 100$ A/ μ s	-	39	51	ns	
Q _{rr}	Reverse Recovery Charge	- 1 _F = 50A, d1 _F /dt = 100A/μs	-	45	59	nC	

Package current limitation is 50A.
 Starting T_J = 25°C, L = 0.67mH, I_{AS} = 40A

This product has been designed to meet the extreme test conditions and environment demanded by the automotive industry. For a copy of the requirements, see AEC Q101 at: http://www.aecouncil.com/
All Fairchild Semiconductor products are manufactured, assembled and tested under ISO9000 and QS9000 quality systems certification.




Figure 1. Normalized Power Dissipation vs Case Temperature

Figure 2. Maximum Continuous Drain Current vs Case Temperature




Figure 3. Normalized Maximum Transient Thermal Impedance





Figure 4. Peak Current Capability

Typical Characteristics




 $\begin{array}{c} \textbf{500} \\ \textbf{(i)} \\ \textbf{If R = 0} \\ \textbf{100} \\ \textbf{If R = 0} \\ \textbf{14} \\ \textbf{V} = (L/R) \text{In} [(I_{AS})'(1.3 \text{*RATED BV}_{DSS} - V_{DD}) + 1] \\ \textbf{If R = 0} \\ \textbf{14} \\ \textbf{V} = (L/R) \text{In} [(I_{AS} \text{*R})'(1.3 \text{*RATED BV}_{DSS} - V_{DD}) + 1] \\ \textbf{STARTING T}_{J} = 25 \text{°C} \\ \textbf{STARTING T}_{J} = 25 \text{°C} \\ \textbf{1001} \\ \textbf{0.01} \\ \textbf{0.1} \\ \textbf{1} \\ \textbf{1} \\ \textbf{10} \\ \textbf{100} \\ \textbf{1000} \\ \textbf{100$

Figure 5. Forward Bias Safe Operating Area

NOTE: Refer to Fairchild Application Notes AN7514 and AN7515

Figure 6. Unclamped Inductive Switching

Capability







Figure 7. Transfer Characteristics

Figure 8. Saturation Characteristics






Figure 9. Drain to Source On-Resistance Variation vs Gate to Source Voltage

Figure 10. Normalized Drain to Source On Resistance vs Junction Temperature

Typical Characteristics




Figure 11. Normalized Gate Threshold Voltage vs Junction Temperature




Figure 12. Normalized Drain to Source Breakdown Voltage vs Junction Temperature




Figure 13. Capacitance vs Drain to Source Voltage







Figure 14. Gate Charge vs Gate to Source Voltage






LAND PATTERN RECOMMENDATION




NON-DIODE PRODUCTS VERSION






DIODE PRODUCTS VERSION



NOTES: UNLESS OTHERWISE SPECIFIED

- A) THIS PACKAGE CONFORMS TO JEDEC, TO-252,
- ISSUE C, VARIATION AA.

 B) ALL DIMENSIONS ARE IN MILLIMETERS.
 C) DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.
- D) SUPPLIER DEPENDENT MOLD LOCKING HOLES OR CHAMFERED CORNERS OR EDGE PROTRUSION.
- E) TRIMMED CENTER LEAD IS PRESENT ONLY FOR DIODE PRODUCTS F) DIMENSIONS ARE EXCLUSSIVE OF BURSS,
 - MOLD FLASH AND TIE BAR EXTRUSIONS.
- G) LAND PATTERN RECOMENDATION IS BASED ON IPC7351A STD TO228P991X239-3N.
- H) DRAWING NUMBER AND REVISION: MKT-TO252A03REV10



(ROTATED -90°) SCALE: 12X







TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

 $\begin{array}{lll} \mathsf{AccuPower^{\mathsf{TM}}} & \mathsf{F-PFS^{\mathsf{TM}}} \\ \mathsf{AttitudeEngine^{\mathsf{TM}}} & \mathsf{FRFET}^{\mathsf{B}} \end{array}$

Awinda® Global Power Resource SM AX-CAP®* GreenBridge™

BitSiC™ Green FPS™
Build it Now™ Green FPS™ e-Series™

Current Transfer Logic™ Making Small Speakers Sound Louder

DEUXPEED® and Better™
Dual Cool™ MegaBuck™
EcoSPARK® MICROCOUPLER™
EfficientMax™ MicroFET™

ESBC™ MicroPak™ MicroPak™ MicroPak2™ MicroPak2™ MillerDrive™ MillerDrive™ MotionMax™ Mo

Farchild Semiconductor

FACT Quiet Series™
FACT®

FastvCore™
FETBench™
FPS™

MotionGrid®
MTI®
MTX®
MVN®
FETBench™
MVN®
FPS™

OptoHiT™
OPTOLOGIC®

OPTOPLANAR®

Power Supply WebDesigner™ PowerTrench®

PowerXS™

Programmable Active Droop™

QFET[®]
QS™
Quiet Series™
RapidConfigure™

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

SPM®
STEALTH™
SuperFET®
SuperSOT™-3
SuperSOT™-6
SuperSOTTM-8
SupreMOS®
SyncFET™
Sync-Lock™

ESYSTEM
GENERAL®*

TinyBoost®
TinyBuck®
TinyCalc™
TinyLogic®
TINYOPTO™
TinyPower™
TinyPWM™
TinyWire™
TranSiC™

TriFault Detect™ TRUECURRENT®* μSerDes™

SerDes*
UHC®
Ultra FRFET™
UniFET™
VCX™

UniFET™ VCX™ VisualMax™ VoltagePlus™ XS™ Xsens™ 仙童™

* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE AT http://www.fairchildsemi.com, FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

AUTHORIZED USE

Unless otherwise specified in this data sheet, this product is a standard commercial product and is not intended for use in applications that require extraordinary levels of quality and reliability. This product may not be used in the following applications, unless specifically approved in writing by a Fairchild officer: (1) automotive or other transportation, (2) military/aerospace, (3) any safety critical application – including life critical medical equipment – where the failure of the Fairchild product reasonably would be expected to result in personal injury, death or property damage. Customer's use of this product is subject to agreement of this Authorized Use policy. In the event of an unauthorized use of Fairchild's product, Fairchild accepts no liability in the event of product failure. In other respects, this product shall be subject to Fairchild's Worldwide Terms and Conditions of Sale, unless a separate agreement has been signed by both Parties.

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Terms of Use

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Deminion of Terms	Similar of Terms					
Datasheet Identification	Product Status	Definition				
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.				
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.				
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.				
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.				

Rev. 176