

Schottky Barrier rectifiers

Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. proprietary barrier technology allows for reliable operation up to 150° C junction temperature. Typical application are in switching Mode Power Supplies such as adaptors, DC/DC converters free- wheeling and polarity protection diodes.

- *Low Forward Voltage.
- *Low Switching noise.
- * High Current Capacity
- * Guarantee Reverse Avalanche.
- * Guard-Ring for Stress Protection.
- *Low Power Loss & High efficiency.
- *150°C Operating Junction Temperature
- *Low Stored Charge Majority Carrier Conduction.
- * Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O



* In compliance with EU RoHs 2002/95/EC directives

The marking is indicated by part no. with. "M". ex:SR2100LM

MAXIMUM RATINGS


Characteristic	Symbol	SR2100L	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	100	V
RMS Reverse Voltage	V _{R(RMS)}	70	V
Average Rectifier Forward Current	Io	2.0	Α
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfware, single phase, 60Hz)	I _{FSM}	50	Α
Operating and Storage Junction Temperature Range	T_J , T_{STG}	-65 to +150	$^{\circ}\!$


ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	SR2100L		Unit			
$\label{eq:maximum Instantaneous Forward Voltage} \begin{tabular}{l} $(I_F=0.1 \ Amp \ T_C=25^\circ\mathbb{C})$ \\ $(I_F=1.0 \ Amp \ T_C=25^\circ\mathbb{C})$ \\ $(I_F=2.0 \ Amp \ T_C=25^\circ\mathbb{C})$ \\ \end{tabular}$	VF	Min. 	Typ. 0.36 0.65 0.79	Max. 0.38 0.70 0.82	V		
Maximum Instantaneous Reverse Current (Rated DC Voltage, $T_C = 25^{\circ}C$) (Rated DC Voltage, $T_C = 125^{\circ}C$)	I _R		0.01 10		mA		
Maximum Thermal Resistance Junction to case	R _{eJC}		55		°C/W		
Typical Junction Capacitance (Reverse Voltage of 4 volts & f=1 MHz)	C_P		80		₽F		

SCHOTTKY BARRIER RECTIFIERS

2.0 AMPERES 100 VOLTS






DIM	MILLIMETERS		
DIIVI	MIN	MAX	
Α	5.00	5.60	
В	25.40		
С	8.50	9.50	
D	1.20	1.30	

CASE---Transfer molded plastic

OLARITY---Cathode indicated polarity band 0.4

0.0

25




CASE TEMPERATURE ($^{\circ}$ C)

100

125


150

FIG-2 TYPICAL FORWARD CHARACTERISITICS




FORWARD VOLTAGE (Volts)

FIG-3 TYPICAL REVERSE CHARACTERISTICS




REVERSE VOLTAGE (Volts)

FIG-4 TYPICAL JUNCTION CAPACITANCE



REVERSE VOLTAGE (Volts)

FIG-5 PEAK FORWARD SURGE CURRENT



NUMBER OF CYCLES AT 60 Hz