

#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Resistive or inductive load, 60Hz.

PARAMETER	SYMBOL	UF200	UF201	UF202	UF204	UF206	UF208	UF2010	UNITS
Maximum Recurrent Peak Reverse Voltage	V <sub>rrm</sub>	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V <sub>rms</sub>	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V
Maximum Average Forward Current at T <sub>A</sub> =55°C	I <sub>F(AV)</sub>	2					A		
Peak Forward Surge Current : 8.3ms single half sine-wave superimposed on rated load	I <sub>fsm</sub>	60					А		
laximum Forward Voltage at 2A		1 1.3 1.7				V			
Maximum DC Reverse Current at Rated DC Blocking T <sub>j</sub> =25°C Voltage T <sub>j</sub> =100°C		10 500					μA		
Typical Junction Capacitance (Note 1)	C	35					рF		
Typical Thermal Resistance (Note 2)	R <sub>eja</sub>	40			°C / W				
Maximum Reverse Recovery Time (Note 3)	t <sub>rr</sub>	50 75				ns			
Operating Junction and Storage Temperature Range	T_,T <sub>stg</sub>	-55 to +150			°C				

#### NOTES:


1. Measured at 1 MHz and applied reverse voltage of 4 VDC.

2. Thermal Resistance from Junction to Ambient and from Junction to lead length 0.375"(9.5mm) P.C.B. mounted.

3. Reverse Recovery Time  $I_F{=}0.5A$  ,  $I_R{=}1A$  ,  $I_{rr}{=}0.25A$ 



#### RATING AND CHARACTERISTIC CURVES







#### Part No\_packing code\_Version

UF200_AY_00001
UF200_AY_10001
UF200_B0_00001
UF200_B0_10001
UF200_R2_00001
UF200_R2_10001

### For example :

### RB500V-40\_R2\_00001



• Serial number

• Version code means HF

- Packing size code means 13"
- -• Packing type means T/R

Packing Code XX			Version Code XXXXX				
Packing type	1 <sup>st</sup> Code	Packing size code	2 <sup>nd</sup> Code	HF or RoHS	1 <sup>st</sup> Code	2 <sup>nd</sup> ~5 <sup>th</sup> Code	
Tape and Ammunition Box (T/B)	A	N/A	0	HF	0	serial number	
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number	
Bulk Packing (B/P)	В	13"	2				
Tube Packing (T/P)	т	26mm	X				
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y				
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U				
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D				





# Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.