

# **Schottky Barrier Rectifiers**

Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. The proprietary barrier technology allows for reliable operation up to 175°C junction temperature. Typical application are in switching Mode Power Supplies such as adaptors, DC/DC converters, freewheeling and polarity protection diodes.

#### **Features**

- \*Low Forward Voltage.
- \*Low Switching noise.
- \*High Current Capacity
- \* Guarantee Reverse Avalanche.
- \* Guard-Ring for Stress Protection.
- \*Low Power Loss & High efficiency.
- \*175℃ Operating Junction Temperature
- \*Low Stored Charge Majority Carrier Conduction.
- \*Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O



\* In compliance with EU RoHs 2002/95/EC directives

### **MAXIMUM RATINGS**

| Characteristic   | Symbol   | MBR10100CT  | Unit                   |
|--|--|-------------|------------------------|
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                 | $egin{array}{c} V_{RRM} \ V_{RWM} \ V_{R} \end{array}$ | 100         | V                      |
| RMS Reverse Voltage  | $V_{R(RMS)}$   | 70          | V                      |
| Average Rectifier Forward Current ( Per diode ) Total Device (Rated $V_R$ ), $T_C$ =125 $^{\circ}$ C   | I <sub>F(AV)</sub>                                     | 5.0<br>10   | А                      |
| Peak Repetitive Forward Current<br>(Rate V <sub>R</sub> , Square Wave, 20kHz)                          | I <sub>FM</sub>  | 10          | Α                      |
| Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfware, single phase, 60Hz) | I <sub>FSM</sub>                                       | 125         | Α                      |
| Operating and Storage Junction Temperature Range   | $T_J$ , $T_stg$  | -65 to +175 | $^{\circ}\!\mathbb{C}$ |

# THERMAL RESISTANCES


| Typical Thermal Resistance junction to case | $R_{\theta jc}$ | 3.8 | °C/w |
|---|-----------------|-----|------|
|---|-----------------|-----|------|


## **ELECTRIAL CHARACTERISTICS**

| LELOTRIAL OFFICIALIST CONTROL OF THE |                |              |      |
|--|----------------|--------------|------|
| Characteristic   | Symbol         | MBR10100CT   | Unit |
| Maximum Instantaneous Forward Voltage<br>( $I_F = 5.0 \text{ Amp } T_C = 25^{\circ}C$ )<br>( $I_F = 5.0 \text{ Amp } T_C = 125^{\circ}C$ )   | V <sub>F</sub> | 0.85<br>0.78 | V    |
| Maximum Instantaneous Reverse Current (Rated DC Voltage, T <sub>C</sub> = 25°C)  | IR             | 0.78         | mA   |
| ( Rated DC Voltage, T <sub>C</sub> = 125°C)  |                | 10           |      |

### SCHOTTKY BARRIER RECTIFIERS

10 AMPERES 100 VOLTS





| DIM   | MILLIMETERS |       |  |
|-------|-------------|-------|--|
| DIIVI | MIN         | MAX   |  |
| Α     | 14.68       | 15.32 |  |
| В     | 9.78        | 10.42 |  |
| С     | 5.02        | 6.52  |  |
| D     | 13.06       | 14.62 |  |
| E     | 3.57        | 4.07  |  |
| F     | 2.42        | 2.66  |  |
| G     | 1.12        | 1.36  |  |
| Н     | 0.72        | 0.96  |  |
| - 1   | 4.22        | 4.98  |  |
| J     | 1.14        | 1.38  |  |
| K     | 2.20        | 2.98  |  |
| L     | 0.33        | 0.55  |  |
| M     | 2.48        | 2.98  |  |
| 0     | 3.70        | 3.90  |  |

