ESD Protection Diode

Dual Line CAN Bus Protector

The SZ/NUP2125 has been designed to protect the CAN transceiver from ESD and other harmful transient voltage events. This device provides bidirectional protection for each data line with a single compact SC-70 (SOT-323) package, giving the system designer a low cost option for improving system reliability and meeting stringent EMI requirements.

Features

- 200 W Peak Power Dissipation per Line (8/20 µs Waveform)
- Diode Capacitance Matching
- Low Reverse Leakage Current (< 100 nA)
- IEC Compatibility: IEC 61000-4-2 (ESD): Level 4
 - IEC 61000–4–4 (EFT): 50 A 5/50 ns
 - IEC 61000-4-5 (Lighting) 3.0 A (8/20 μs)
- ISO 7637–1, Nonrepetitive EMI Surge Pulse 2, 8.0 A (1/50 μs)
- ISO 7637–3, Repetitive Electrical Fast Transient (EFT) EMI Surge Pulses, 50 A (5/50 ns)
- Flammability Rating UL 94 V-0
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These are Pb–Free Devices


Applications

- Automotive Networks
 - CAN / CAN-FD
 - Low and High-Speed CAN
 - Fault Tolerant CAN



ON Semiconductor®


www.onsemi.com




25 = Specific Device Code M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)





ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

MAXIMUM RATINGS ($T_J = 25^{\circ}C$, unless otherwise specified)

| Symbol | Rating | Value | Unit |
|----------------|---|------------------------------------|----------------------------|
| PPK | Peak Power Dissipation, 8 x 20 μs Double Exponential Waveform (Note 1) | 200 | W |
| T _J | Operating Junction Temperature Range | -55 to 150 | °C |
| TJ | Storage Temperature Range | -55 to 150 | °C |
| T _L | Lead Solder Temperature (10 s) | 260 | °C |
| ESD | Human Body Model (HBM) Machine Model (MM) IEC 61000–4–2 Contact IEC 61000–4–2 Air ISO 10605 150 pF / 2 kΩ Contact ISO 10605 330 pF / 2 kΩ Contact | 8.0 1.6 30 30 30 30 | kV kV kV kV kV |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS (T_J = 25°C, unless otherwise specified)

| Symbol | Parameter | Test Conditions | Min | Тур | Max | Unit |
|------------------|----------------------------|--|------|------|------|------|
| V _{RWM} | Reverse Working Voltage | (Note 2) | 24 | - | - | V |
| V _{BR} | Breakdown Voltage | I _T = 1 mA (Note 3) | 26.2 | 28.5 | 32 | V |
| I _R | Reverse Leakage Current | V _{RWM} = 24 V | - | 15 | 100 | nA |
| V _C | Clamping Voltage | I _{PP} = 1 A (8/20 μs Waveform) (Note 4) | - | 33.4 | 36.6 | V |
| V _C | Clamping Voltage | I _{PP} = 3 A (8/20 μs Waveform) (Note 4) | - | 44 | 50 | V |
| I _{PP} | Maximum Peak Pulse Current | 8/20 μs Waveform (Note 4) | - | - | 3.0 | Α |
| CJ | Capacitance | V _R = 0 V, f = 1 MHz (Line to GND) | - | 7.0 | 10 | pF |
| | | V _R = 5 V, f = 1 MHz (Line to GND) | - | 4.5 | 6.0 | pF |
| | | $V_R = 5 \text{ V, f} = 1 \text{ MHz}$ (Line to GND), $T_A = +150^{\circ}\text{C}$ | - | 5.0 | - | pF |
| ΔC | Diode Capacitance Matching | V _R = 0 V, 5 MHz (Note 5) | - | 0.26 | 2 | % |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse waveform per Figure 1.

ORDERING INFORMATION

| Device | Package | Shipping [†] | |
|-----------------|-----------|-----------------------|--|
| NUP2125WTT1G | | 2000 / Tong & Book | |
| SZNUP2125WTT1G* | SC-70 | 3000 / Tape & Reel | |
| NUP2125WTT3G | (Pb-Free) | 10000 / Tone % Deel | |
| SZNUP2125WTT3G* | | 10000 / Tape & Reel | |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

^{1.} Non-repetitive current pulse per Figure 1.

^{2.} Surge protection devices are normally selected according to the working peak reverse voltage (V_{RWM}), which should be equal or greater than the DC or continuous peak operating voltage level.

^{3.} V_{BR} is measured at pulse test current I_T.

ΔC is the percentage difference between C_J of lines 1 and 2 measured according to the test conditions given in the electrical characteristics table.

^{*}SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.


TYPICAL PERFORMANCE CURVES

(T_J = 25°C unless otherwise noted)

3.5

3.0

2.5




IPP, PEAK PULSE CURRENT (A) 2.0 1.5 1.0 0.5 0.0 35 40 30 45

Figure 1. Pulse Waveform, $8 \times 20~\mu s$

Figure 2. Clamping Voltage vs Peak Pulse Current

V_C, CLAMPING VOLTAGE (V)

50







Figure 3. Typical Junction Capacitance vs **Reverse Voltage**

Figure 4. V_{BR} versus I_T Characteristics






Figure 5. I_R versus Temperature Characteristics

Figure 6. Temperature Power Dissipation Derating

Surge Protection Diode Circuit

Surge protection diodes provide protection to a transceiver by clamping a surge voltage to a safe level. Surge protection diodes have high impedance below and low impedance above their breakdown voltage. A surge protection Zener diode has its junction optimized to absorb the high peak energy of a transient event, while a standard Zener diode is designed and specified to clamp a steady state voltage.

Figure 7 provides an example of a dual bidirectional surge protection diode array that can be used for protection with the high–speed CAN network. The bidirectional array is created from four identical Zener TVS diodes. The clamping voltage of the composite device is equal to the

breakdown voltage of the diode that is reversed biased, plus the diode drop of the second diode that is forwarded biased.





Figure 7. High-Speed and Fault Tolerant CAN Surge Protection Circuit

PACKAGE DIMENSIONS

SC-70 (SOT-323) CASE 419-04




ISSUE N

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- CONTROLLING DIMENSION: INCH.

| | MILLIMETERS | | | INCHES | | |
|-----|-------------|------|-----------|--------|-------|-------|
| DIM | MIN | NOM | MAX | MIN | NOM | MAX |
| Α | 0.80 | 0.90 | 1.00 | 0.032 | 0.035 | 0.040 |
| A1 | 0.00 | 0.05 | 0.10 | 0.000 | 0.002 | 0.004 |
| A2 | 0.70 REF | | 0.028 REF | | | |
| b | 0.30 | 0.35 | 0.40 | 0.012 | 0.014 | 0.016 |
| С | 0.10 | 0.18 | 0.25 | 0.004 | 0.007 | 0.010 |
| D | 1.80 | 2.10 | 2.20 | 0.071 | 0.083 | 0.087 |
| Е | 1.15 | 1.24 | 1.35 | 0.045 | 0.049 | 0.053 |
| е | 1.20 | 1.30 | 1.40 | 0.047 | 0.051 | 0.055 |
| e1 | 0.65 BSC | | 0.026 BSC | | | |
| L | 0.20 | 0.38 | 0.56 | 0.008 | 0.015 | 0.022 |
| HE | 2.00 | 2.10 | 2.40 | 0.079 | 0.083 | 0.095 |

STYLE 11: PIN 1. CATHODE 2. CATHODE 3. CATHODE

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Honeywell and SDS are registered trademarks of Honeywell International Inc. DeviceNet is a trademark of Rockwell Automation.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative