
ES1A THRU ES1M

Surface Mount Superfast Recovery Rectifier Reverse Voltage - 50 to 1000 V Forward Current - 1 A

Features

- · Glass passivated junction
- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- Easy pick and place
- For surface mounted applications
- Low profile package
- Built-in strain relief
- · Superfast recovery times for high efficiency



Dimensions in inches and (millimeters)

Mechanical Data

- · Case: SMA (DO-214AC), molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026 guaranteed
- · Polarity: Color band denotes cathode end

Absolute Maximum Ratings and Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Parameter	Symbols	ES1A	ES1B	ES1C	ES1D	ES1E	ES1G	ES1J	ES1K	ES1M	Units
	Marking	ES1A	ES1B	ES1C	ES1D	ES1E	ES1G	ES1J	ES1K	ES1M	-
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	150	200	300	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	25	70	105	140	210	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	150	200	300	400	600	800	1000	V
Maximum Average Forward Rectified Current	I _{F(AV)}	1									А
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	I _{FSM}	30								A	
Maximum Forward Voltage at 1 A	V _F	1				1.3		1.7		V	
Maximum Reverse Current $T_J = 25^{\circ}C$ at Rated DC Blocking Voltage $T_J = 125^{\circ}C$	I _R	5 50								μA	
Typical Junction Capacitance at V_R = 4 V, f = 1 MH _z	CJ	10								pF	
Typical Reverse Recovery Time at I_F = 0.5 A, I_R = 1 A, I_{rr} = 0.25 A	trr	35								ns	
Typical Thermal Resistance	$R_{ extsf{ heta}JL}$ $R_{ extsf{ heta}JA}$	35 85							°C/W		
Operating Junction and Storage Temperature Range	T_{j} , T_{stg}	- 55 to + 150									°C



SEMTECH ELECTRONICS LTD.



Dated : 10/03/2016 JG Rev:01

ES1A THRU ES1M





FIG. 5 TYPICAL JUNCTION CAPACITANCE





SEMTECH ELECTRONICS LTD.



Dated : 10/03/2016 JG Rev:01