https://www.murata.com/en-us/products/productdetail?partno=NXFT15XH103FA1B\_

# NXFT15XH103FA1B\_












## Appearance & Shape








### **Features**

- 1. High accuracy and high sensibility temperature sensing is available by the small size and high accuracy NTC Thermistor.
- 2. Narrow space temperature sensing is available by the small sensing head and the thin lead wire.
- 3. Flexibility and wide variety length (25 mm to 150mm) enables designing flexible temperature sensing architectures.
- 4. This product is compatible with our 0402 (EIA) size chip Thermistor.
- 5. Excellent long time aging stability
- 6. This is halogen free product (CI= max.900ppm\ Br=max.900ppm and CI+Br=max.1500ppm).
- 7. Lead is not contained in the product.
- 8. NXF series are recognized by UL/cUL (UL1434, File No.E137188).







## Packaging Information

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	1000

1 of 3

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before or ordering.

2. This detablet has apply third people in the popular base in an arrange for tehelited people for income.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/03/09



Note: This datasheet may be out of date. Please download the latest datasheet of NXFT15XH103FA1B from the official website of Murata Manufacturing Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=NXFT15XH103FA1B\_\_\_

# NXFT15XH103FA1B\_\_\_\_



Resistance (25°C)	10kΩ
Resistance Value Tolerance (at 25°C)	±1%
B-Constant (25/50°C)	3380K
B-Constant (25/50°C) Tolerance	±1%
B-Constant(25/80°C)(Reference Value)	3428K
B-Constant(25/85°C)(Reference Value)	3434K
B-Constant(25/100°C)(Reference Value)	3455K
Operating Current for Sensor(25°C)	0.12mA
Rated Electric Power (25°C)	7.5mW
Typical Dissipation Constant (25°C)	1.5mW/°C
Thermal Time Constant	4s
Operating Temperature Range	-40°C to 125°C
Lead Shape	Lead Wire type
Shape	Lead
Mass	0.03g to 0.15g

2 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




URL: https://www.murata.com/

Note: This datasheet may be out of date. Please download the latest datasheet of NXFT15XH103FA1B from the official website of Murata

Manufacturing Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=NXFT15XH103FA1B\_\_

# NXFT15XH103FA1B\_\_\_\_





Resistance-Temperature Characteristics

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2018/03/09