

# 441A Series - 0603 High I<sup>2</sup>t Fuse



Agency A	pprovals	
AGENCY	AGENCY FILE NUMBER	AMPERE RANGE
<b>A</b>	E10480	2A - 6A
۲.	29862	2A - 6A

Electrical Ch	aracteristics	
% of Ampere Rating	Ampere Rating	Opening Time at 25°C
100%	2A - 6A	4 Hours Minimum
350%	2A - 6A	5 Seconds Maximum

## **Electrical Specifications by Item**

### Description

The 441A series AECQ-Compliant fuses are specifically tested to cater to secondary circuit protection needs of compact auto-electronics application.

The general design ensures excellent temperature stability and performance reliability.

This high I<sup>2</sup>t fuse series is designed to have ultra high inrush current withstand capability to avoid nuisance fuse open.

#### Features

 Operating Temperature from -55°C to 150°C

• 100% Lead-free, Halogen-

automotive qualifications\*

 Suitable for both leaded and lead-free reflow/wave soldering

Rohs 🕫 HF 5 👀

Free and RoHS compliant • Ultra high I<sup>2</sup>t values

\* - Largely based on Littelfuse internal AEC-Q200 test plan.

#### Applications

- Li-ion Battery
- LED Head Lights

• Meets Littelfuse's

- Automotive Navigation System
- TFT Display
- Battery Management System (BMS)
- Clusters

Ampere	•		1.1	Nominal	Nominal	Nominal Voltage	Nominal Power	Agency A	pprovals
Rating (A)	Amp Code	Rating (V)	Rating <sup>1</sup>	Resistance (Ohms) <sup>2</sup>	Melting I <sup>2</sup> t (A <sup>2</sup> Sec.) <sup>3</sup>	Drop At Rated Current (V) <sup>4</sup>	Dissipation At Rated Current (W)	77	<b>(</b> )
2	002.	32		0.0302	0.3103	0.0551	0.110	Х	Х
2.5	02.5	32		0.0200	0.5520	0.0534	0.134	Х	Х
3	003.	32		0.0158	0.8165	0.0531	0.159	Х	Х
3.5	03.5	32	50 A @ 32 VDC	0.0117	0.9438	0.0468	0.164	Х	Х
4	004.	32		0.0097	1.2659	0.0475	0.190	Х	Х
5	005.	32		0.0073	1.6287	0.0472	0.236	Х	Х
6	006.	32		0.0056	2.6049	0.0464	0.278	Х	Х

Notes:

1. DC Interrupting Rating tested at rated voltage with time constant < 0.8 msecs.

- 2. Nominal Resistance measured with < 10% rated current.
- 3. Nominal Melting I<sup>2</sup>t measured at 1 msec. opening time.

4. Nominal Voltage Drop measured at rated current after temperature has stabilized.

### **Additional Information**



Datasheet





Samples

Devices designed to carry out rated current for 4 hours minimum. It is recommended that devices be operated continuously at no more than 80% rated current. See "Temperature Re-rating Curve" for additional re-rating information

Devices designed to be mounted with marking code facing up.

© 2017 Littelfuse, Inc. Specifications are subject to change without notice. Application testing is strongly recommended. Revised: 06/08/17

# **Surface Mount Fuses**

Ceramic Fuse > 441A Series





Note:

1. Re-rating depicted in this curve is in addition to the standard re-rating of 20% for continuous operation.

For continuous operation at 75 degrees celsius, the fuse should be rerated as follows: I = (0.80)(0.85)I\_{RAT} = (0.68)I\_{RAT}

### Average Time Current Curves



## **Soldering Parameters**

Reflow Co	ndition	Pb – free assembly
	-Temperature Min (T <sub>s(min)</sub> )	150°C
Pre Heat	-Temperature Max (T <sub>s(max)</sub> )	200°C
	-Time (Min to Max) (t <sub>s</sub> )	60 – 180 seconds
Average R (T <sub>L</sub> ) to pea	amp-up Rate (LiquidusTemp k)	3°C/second max.
$T_{S(max)}$ to $T_{I}$	- Ramp-up Rate	5°C/second max.
Poflow	-Temperature (T <sub>L</sub> ) (Liquidus)	217°C
nellow	-Temperature (t <sub>L</sub> )	60 – 150 seconds
PeakTemp	erature (T <sub>P</sub> )	260 <sup>+0/-5</sup> °C
Time with Temperatu	in 5°C of actual peak ıre (t <sub>p</sub> )	10 – 30 seconds
Ramp-dov	vn Rate	6°C/second max.
Time 25°C	to peakTemperature (T <sub>P</sub> )	8 minutes max.
Do not exc	ceed	260°C

Wave Soldering	260°C, 10 seconds max.





### **Product Characteristics**

Materials	Body: Advanced Ceramic Terminations: Ag / Ni / Sn (100% Lead-free) Element Cover Coating: Lead-free Glass
Moisture Sensitivity Level	IPC/JEDEC J-STD-020, Level 1
Solderability	IPC/ECA/JEDEC J-STD-002, Condition C
Humidity Test	MIL-STD-202, Method 103, Conditions D
Resistance to Solder Heat	MIL-STD-202, Method 210, Condition B
Moisture Resistance	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B
Mechanical Shock	MIL-STD-202, Method 213, Condition A
Vibration	MIL-STD-202, Method 201
Vibration, High Frequency	MIL-STD-202, Method 204, Condition D
Dissolution of Metallization	IPC/ECA/JEDEC J-STD-002, Condition D
Terminal Strength	IEC 60127-4

Dimen	sions



High Temperature Storage	MIL-STD-202, Method 108 with exemptions
Thermal Shock Test	JESD22 Method JA-104, Test Conditions B and N
Biased Humidity	MIL-STD-202, Method 103, 85C/85% RH with 10% operating power for 1000 hrs
<b>Operational Life</b>	MIL-STD-202, Method 108, Test Condition D
Resistance to Solvents	MIL-STD-202, Method 215
Mechanical Shock	MIL-STD-202, Method 213, Test Condition C
High Frequency Vibration	MIL-STD-202, Method 204
Resistance to Soldering Heat	MIL-STD-202, Method 210, Test Condition B
Solderability	JESD22-B102E Method 1
Terminal Strength for SMD	AEC Q200-006
Board Flex	AEC Q200-005
Electrical Characterization	3 Temperature Electrical

## Part Marking System

Amp Code	Marking Code
002.	N
02.5	0
003.	Р
03.5	R
004.	S
005.	т
006.	U



Packaging			
Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
8mm Tape and Reel	EIA-481, IEC 60286, Part 3	3000	WRA