


MMBT2222 / MMBT2222A

NPN Silicon Epitaxial Planar Transistor


for switching and amplifier applications



1. Base 2. Emitter 3. Collector
TO-236 Plastic Package

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Collector Base Voltage MMBT2222 MMBT2222A	V_{CBO}	60 75	V
Collector Emitter Voltage MMBT2222 MMBT2222A	V_{CEO}	30 40	V
Emitter Base Voltage MMBT2222 MMBT2222A	V_{EBO}	5 6	V
Collector Current	I_C	600	mA
Power Dissipation	P_{tot}	350	mW
Junction Temperature	T_j	150	°C
Storage Temperature Range	T_{stg}	- 55 to + 150	°C



SEMTECH ELECTRONICS LTD.




Dated: 16/03/2015 Rev: 03

MMBT2222 / MMBT2222A

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
DC Current Gain at $V_{CE} = 10 \text{ V}$, $I_C = 0.1 \text{ mA}$ at $V_{CE} = 10 \text{ V}$, $I_C = 1 \text{ mA}$ at $V_{CE} = 10 \text{ V}$, $I_C = 10 \text{ mA}$ at $V_{CE} = 1 \text{ V}$, $I_C = 150 \text{ mA}$ at $V_{CE} = 10 \text{ V}$, $I_C = 150 \text{ mA}$ at $V_{CE} = 10 \text{ V}$, $I_C = 500 \text{ mA}$	h_{FE}	35	-	-
	h_{FE}	50	-	-
	h_{FE}	75	-	-
	h_{FE}	50	-	-
	h_{FE}	100	300	-
	h_{FE}	30	-	-
	h_{FE}	40	-	-
Collector Base Cutoff Current at $V_{CB} = 50 \text{ V}$ at $V_{CB} = 60 \text{ V}$	I_{CBO}	-	10	nA
Emitter Base Cutoff Current at $V_{EB} = 3 \text{ V}$	I_{EBO}	-	100	nA
Collector Base Breakdown Voltage at $I_C = 10 \mu\text{A}$	$V_{(BR)CBO}$	60 75	-	V
Collector Emitter Breakdown Voltage at $I_C = 10 \text{ mA}$	$V_{(BR)CEO}$	30 40	-	V
Emitter Base Breakdown Voltage at $I_E = 10 \mu\text{A}$	$V_{(BR)EBO}$	5 6	-	V
Collector Emitter Saturation Voltage at $I_C = 150 \text{ mA}$, $I_B = 15 \text{ mA}$ at $I_C = 500 \text{ mA}$, $I_B = 50 \text{ mA}$	$V_{CE(sat)}$	-	0.4	V
		-	0.3	
		-	1.6	
		-	1	
Base Emitter Saturation Voltage at $I_C = 150 \text{ mA}$, $I_B = 15 \text{ mA}$ at $I_C = 500 \text{ mA}$, $I_B = 50 \text{ mA}$	$V_{BE(sat)}$	- 0.6 -	1.3 1.2 2.6	V
		-	2	
Transition Frequency at $V_{CE} = 20 \text{ V}$, $-I_E = 20 \text{ mA}$, $f = 100 \text{ MHz}$	f_T	300	-	MHz
Collector Output Capacitance at $V_{CB} = 10 \text{ V}$, $f = 100 \text{ KHz}$	C_{ob}	-	8	pF
Delay Time at $V_{CC} = 30 \text{ V}$, $V_{BE(OFF)} = 0.5 \text{ V}$, $I_C = 150 \text{ mA}$, $I_{B1} = 15 \text{ mA}$	t_d	-	10	ns
Rise Time at $V_{CC} = 30 \text{ V}$, $V_{BE(OFF)} = 0.5 \text{ V}$, $I_C = 150 \text{ mA}$, $I_{B1} = 15 \text{ mA}$	t_r	-	25	ns
Storage Time at $V_{CC} = 30 \text{ V}$, $I_C = 150 \text{ mA}$, $I_{B1} = -I_{B2} = 15 \text{ mA}$	t_{stg}	-	225	ns
Fall Time at $V_{CC} = 30 \text{ V}$, $I_C = 150 \text{ mA}$, $I_{B1} = -I_{B2} = 15 \text{ mA}$	t_f	-	60	ns



SEMTECH ELECTRONICS LTD.



ISO/TS 16949 : 2009 Certificate No. 160719000 ISO 14001 : 2004 Certificate No. 7116 ISO 9001 : 2008 Certificate No. 60713410 BS-OHSAS 18001 : 2007 Certificate No. 7116 IECQ QC 080000 Certificate No. PRC-HSPM-1403-1 Intertek UKAS Quality Management System Certified DEKRA Quality Management System Certified Intertek UKAS Environmental Management System Certified DEKRA Quality Management System Certified Intertek UKAS Occupational Health and Safety Management System Certified BS-OHSAS 18001 : 2007 Certificate No. 7116 IECQ QC 080000 Certificate No. PRCHSPM-1403-1 SGS Quality Management System Certified Intertek UKAS Environmental Management System Certified DEKRA Quality Management System Certified Intertek UKAS Occupational Health and Safety Management System Certified BS-OHSAS 18001 : 2007 Certificate No. 7116 IECQ QC 080000 Certificate No. PRCHSPM-1403-1

Dated: 16/03/2015 Rev: 03

MMBT2222 / MMBT2222A




Fig.1 Grounded emitter output characteristics




Fig.3 DC current gain vs. collector current(I)




Fig.2 Collector-emitter saturation voltage vs. collector current




Fig.4 DC current gain vs. collector current(II)




Fig.5 P_c - T_a





Fig.6 Base-emitter saturation voltage vs. collector current



SEMTECH ELECTRONICS LTD.



Dated: 16/03/2015 Rev: 03