UNISONIC TECHNOLOGIES CO., LTD

MBR0540


SCHOTTKY RECTIFIER

■ FEATURES

- * For surface mounted applications
- * Low forward voltage drop (V_F=0.50V Typ. at 0.5A)
- * Guard ring for transient and ESD protection

■ SYMBOL







■ ORDERING INFORMATION

Order Number		Dealtess	Pin Assignment		Deaking	
Lead Free	Halogen Free	Package	1	2	Packing	
MBR0540L-CA2-R	MBR0540G-CA2-R	SOD-123	Α	K	Tape Reel	
MBR0540L-CB2-R	MBR0540G-CB2-R	SOD-323	Α	K	Tape Reel	

Note: Pin assignment: A: Anode K: Cathode



MARKING



<u>www.unisonic.com.tw</u> 1 of 3

MBR0540 DIODE

■ **ABSOLUTE MAXIMUM RATINGS** (Single Diode @T_A=25°C, unless otherwise specified)

PARAMETER		SYMBOL	RATINGS	UNIT	
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	40	V	
Maximum DC Blocking Voltage		V_R	40	V	
Working Peak Reverse Voltage		V_{RWM}	40	V	
Maximum RMS Reverse Voltage		$V_{R(RMS)}$	28	V	
Maximum Voltage Rate of Change (Rated V _R)		dv/dt	1000	V/µs	
Average Rectified Forward Current		I _{OUT}	500	mA	
Non-Repetitive Peak Forward Surge Current		I _{FSM}	5.5	Α	
Power Dissipation	SOD-123	- P _D	410	mW	
	SOD-323		200	mW	
Storage Temperature		T _{STG}	-65 ~ +150	°C	

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

■ THERMAL DATA


PARAMETER		SYMBOL	RATINGS	UNIT	
hunstian to Ambient	SOD-123	θја	244	°C/W	
Junction to Ambient	SOD-323		500	°C/W	


■ **ELECTRICAL CHARACTERISTICS** (T_A=25°C, unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Reverse Breakdown Voltage	BV_R	I _R =20μA	40			V
Famuurd Valtaga Duan	V_{F1}	I _F =0.5A			0.51	V
Forward Voltage Drop	V_{F2}	I _F =1A			0.62	V
Developed Landson Comment	I _{R1}	V _R =20V			10	μΑ
Reverse Leakage Current	I _{R2}	V _R =40V			20	μΑ
Total Capacitance	Ст	V _R =1V, f=1MHz			170	pF
Tymical Daylarea Dagaylary Time	l too	$I_F=I_R=10$ mA, $R_L=100$ Ω			4	ns
Typical Reverse Recovery Time		recover to 0.1 x I _R				

MBR0540 DIODE

TYPICAL CHARACTERISTICS







UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.