Surface Mount Schottky Power Rectifier

SMB Power Surface Mount Package

... employing the Schottky Barrier principle in a metal-to-silicon power rectifier. Features epitaxial construction with oxide passivation and metal overlay contact. Ideally suited for low voltage, high frequency switching power supplies; free wheeling diodes and polarity protection diodes.

- Compact Package with J-Bend Leads Ideal for Automated Handling
- Highly Stable Oxide Passivated Junction
- Guardring for Overvoltage Protection
- Low Forward Voltage Drop
- Pb-Free Package is Available

Mechanical Characteristics:

- Case: Molded Epoxy
- Epoxy Meets UL 94, V-0 at 0.125 in
- Weight: 95 mg (approximately)
- Cathode Polarity Band
- Maximum Temperature of 260°C/10 Seconds for Soldering
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	40	V
Average Rectified Forward Current (At Rated V _R , T _C = 100°C)	I _O	2.0	Α
Peak Repetitive Forward Current (At Rated V_R , Square Wave, 20 kHz, $T_C = 105^{\circ}C$)	I _{FRM}	4.0	A
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I _{FSM}	25	А
Storage/Operating Case Temperature	T _{stg} , T _C	T _{stg} , T _C -55 to +150	
Operating Junction Temperature	TJ	-55 to +125	°C
Voltage Rate of Change (Rated V _R , T _J = 25°C)	dv/dt	10,000	V/μs

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.



ON Semiconductor®

http://onsemi.com

SCHOTTKY BARRIER RECTIFIER 2.0 AMPERES 40 VOLTS



SMB CASE 403A PLASTIC

MARKING DIAGRAM



2BL4 = Specific Device Code A = Assembly Location

Y = Year W = Work Week

ORDERING INFORMATION

Device	Package	Shipping [†]
MBRS240LT3	SMB	2500/Tape & Reel
MBRS240LT3G	SMB (Pb-Free)	2500/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

THERMAL CHARACTERISTICS


Characteristic	Symbol	Value	Unit
Thermal Resistance — Junction-to-Lead (Note 1)	$R_{ heta JL}$	18	°C/W
Thermal Resistance — Junction-to-Ambient (Note 3)	$R_{\theta JA}$	78	

ELECTRICAL CHARACTERISTICS

Maximum Instantaneous Forward Voltage (Note 2)	V _F	T _J = 25°C	T _J = 125°C	Volts
(I _F :	= 2.0 A) = 4.0 A)	0.43 0.54	0.375 0.55	
Maximum Instantaneous Reverse Current (Note 2)	I _R	T _J = 25°C	T _J = 100°C	mA
` ,	= 40 V)	2.0	60	
see Figure 4 (V _R	= 20 V)	0.5	40	

- 1. Mounted with minimum recommended pad size, PC Board FR4.
- 2. Pulse Test: Pulse Width \leq 250 μ s, Duty Cycle \leq 2.0%. 3. 1 inch square pad size (1 x 0.5 inch for each lead) on FR4 board.

TYPICAL CHARACTERISTICS



I_F, INSTANTANEOUS FORWARD CURRENT (AMPS) 1.0 T_J = 125°C 85°C 0.1 0.6 8.0 0.0 0.3 0.4 0.5 0.7 V_F, MAXIMUM INSTANTANEOUS FORWARD VOLTAGE (VOLTS)

Figure 1. Typical Forward Voltage

Figure 2. Maximum Forward Voltage





Figure 3. Typical Reverse Current

Figure 4. Maximum Reverse Current

TYPICAL CHARACTERISTICS







Figure 5. Current Derating

Figure 6. Forward Power Dissipation






Figure 7. Capacitance

Figure 8. Maximum Non-Repetitive Forward Surge Current







Figure 9. Thermal Response

PACKAGE DIMENSIONS

SMB PLASTIC PACKAGE CASE 403A-03 ISSUE D








NOTES

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
- D DIMENSION SHALL BE MEASURED WITHIN DIMENSION P

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	0.160	0.180	4.06	4.57
В	0.130	0.150	3.30	3.81
С	0.075	0.095	1.90	2.41
D	0.077	0.083	1.96	2.11
Н	0.0020	0.0060	0.051	0.152
J	0.006	0.012	0.15	0.30
K	0.030	0.050	0.76	1.27
Р	0.020 REF		0.51 REF	
S	0.205	0.220	5.21	5.59

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082-1312 USA Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Japan: ON Semiconductor, Japan Customer Focus Center 2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051 Phone: 81-3-5773-3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.

This datasheet has been download from:

www.datasheetcatalog.com

Datasheets for electronics components.