

XL6006

Features

- Wide 5V to 32V Input Voltage Range
- Maximum Boost Output Up to 60V
- 0.22V FB adjustable LED drive current
- Directly drive 16 Series 1W/3W LED at VIN=24V
- Fixed 180KHz Switching Frequency
- Max. 5A Switching Current Capability
- Up to 94% efficiency
- Excellent line and load regulation
- EN PIN TTL shutdown capability
- Internal Optimize Power MOSFET
- Built in Soft-Start Function
- Built in Frequency Compensation
- Built in Thermal Shutdown Function
- Built in Current Limit Function
- Available in TO263-5L package

Applications

- LED Lighting
- Boost constant current driver
- TFT LED Backlighting

General Description

The XL6006 regulator is fixed frequency PWM Boost (step-up) LED constant current driver, capable of driving Series 1W/3W/5W LED units with excellent line and load regulation. The regulator is simple to use because it includes internal frequency compensation and a fixed-frequency oscillator so that it requires a minimum number of external components to work.

The XL6006 could directly drive 16 Series 1W/3W LED units at VIN=24V.

The PWM control circuit is able to adjust the duty ratio linearly from 0 to 90%. An enable function, an over current protection function is built inside. An internal compensation block is built in to minimize external component count.



Figure 1. Package Type of XL6006



XL6006

Pin Configurations




Figure 2. Pin Configuration of XL6006 (Top View)

Table 1 Pin Description

Pin Number	Pin Name	Description
1	GND	Ground Pin.
2	EN	Enable Pin. Drive EN pin low to turn off the device, drive it high to turn it on. Floating is default high.
3	SW	Power Switch Output Pin (SW).
4	VIN	Supply Voltage Input Pin. XL6006 operates from a 5V to 32V DC voltage. Bypass Vin to GND with a suitably large capacitor to eliminate noise on the input.
5	FB	Feedback Pin (FB). The feedback threshold voltage is 0.22V.



XL6006

Function Block




Figure 3. Function Block Diagram of XL6006

Typical Application Circuit




Figure 4. XL6006 Typical Application Circuit



XL6006

Ordering Information

Order Information	Marking ID	Package Type	Packing Type Supplied As
XL6006E1	XL6006E1	TO263-5L	800 Units on Tape & Reel

XLSEMI Pb-free products, as designated with "E1" suffix in the par number, are RoHS compliant.

Absolute Maximum Ratings (Note1)

Parameter	Symbol	Value	Unit
Input Voltage	Vin	-0.3 to 36	V
Feedback Pin Voltage	V_{FB}	-0.3 to Vin	V
EN Pin Voltage	V_{EN}	-0.3 to Vin	V
Output Switch Pin Voltage	V_{Output}	-0.3 to 60	V
Power Dissipation	P_{D}	Internally limited	mW
Thermal Resistance (TO263-5L) (Junction to Ambient, No Heatsink, Free Air)	R_{JA}	30	°C/W
Operating Junction Temperature	T_{J}	-40 to 125	°C
Storage Temperature	T _{STG}	-65 to 150	°C
Lead Temperature (Soldering, 10 sec)	T_{LEAD}	260	°C
ESD (HBM)		2000	V

Note1: Stresses greater than those listed under Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.



XL6006

XL6006 Electrical Characteristics

 $T_a = 25$ °C; unless otherwise specified.

Symbol	Parameter	Test Condition	Min.	Тур.	Max.	Unit	
System parameters test circuit figure4							
VFB	Feedback	Vin = 5V to 12V, Vout=24V	209	220	231	mV	
	Voltage	Iload=100mA	209				
ŋ	Efficiency	Vin=12V ,Vout=51.2V		92	-	%	
		Iout=350mA	-			/0	

Electrical Characteristics (DC Parameters)

Vin = 12V, GND=0V, Vin & GND parallel connect a 100uf/50V capacitor; Iout=100mA, T_a = 25 °C; the others floating unless otherwise specified.

Parameters	Symbol	Test Condition	Min.	Тур.	Max.	Unit
Input operation voltage	Vin		5		32	V
Shutdown Supply Current	I_{STBY}	$V_{EN}=0V$		70	100	uA
Quiescent Supply Current	I_q	$V_{EN} = 2V,$ $V_{FB} = V_{in}$		2.5	5	mA
Oscillator Frequency	Fosc		144	180	216	KHz
Switch Current Limit	I_{L}	$V_{FB} = 0$		5		A
Output Power NMOS	Rdson	Vin=12V, I _{SW} =5A		35	40	mohm
EN Pin Threshold	V_{EN}	High (Regulator ON) Low (Regulator OFF)		1.4 0.8		V
EN Pin Input Leakage	I_{H}	$V_{EN} = 2V (ON)$		3	10	uA
Current	I_L	$V_{EN} = 0V (OFF)$		3	10	uA
Max. Duty Cycle	D_{MAX}	$V_{FB}=0V$		90		%



XL6006

Typical System Application for VIN=12V to driver 16 x 1W series LED units




Figure 5. XL6006 System Parameters Test Circuit (12V ~16 x 1W LED)

Typical System Application for VIN=12V to driver 8 x 3W series LED units




Figure 6. XL6006 System Parameters Test Circuit (12V ~ 8 x 3W LED)



XL6006

Typical System Application for VIN=24V to driver 16 x 3W series LED units




Figure 7. XL6006 System Parameters Test Circuit (24V ~ 16 x 3W LED)

Typical System Application for VIN>=12V to driver 16 series x 40 parallel White LED Array




Figure 8. XL6006 System Parameters Test Circuit (VIN>=12V ~ 16 x 40 White LED)



XL6006

Typical System Application for SEPIC Buck-Boost LED Driver




Figure 9. XL6006 System Parameters Test Circuit (Buck-Boost LED Driver)

Typical System Application for VIN=12V to driver 16 x 1W series LED units With Dimming Function




Figure 10. XL6006 System Test Circuit (12V ~16 x 1W LED with Dimming Function)



XL6006

Typical System Application (LED OVP)

LED OVP function can be used in typical system application with external components. The output voltage can be limited in a suitable value by choose different zener diode when the output LED open. the zener diode voltage choosed by output led voltage's 1.3 times.






Figure 11. XL6006 System Test Circuit (LED OVP)




XL6006

Package Information TO263-5L







Symbol	Dimensions I	n Millimeters	Dimensions In Inches		
	Min	Max	Min	Max	
A	4.06	4.83	0.160	0.190	
В	0.71	1.02	0.030	0.040	
С	0.36	0.64	0.014	0.025	
C2	1.14	1.40	0.045	0.055	
D	8.39	9.65	0.330	0.380	
Е	9.78	10.54	0.385	0.415	
e	1.55	1.85	0.061	0.073	
F	6.36	7.36	0.250	0.290	
L	13.95	15.37	0.549	0.605	
L2	1.12	1.42	0.044	0.056	



XL6006

Important Notice

XLSEMI reserve the right to make modifications, enhancements, improvements, corrections or other changes without notice at any time. XLSEMI does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. XLSEMI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using XLSEMI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards. XLSEMI warrants performance of its products to the specifications applicable at the time of sale, in accordance with the warranty in XLSEMI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent XLSEMI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

For the latest product information, go to www.xlsemi.com.