




MB2S THRU MB10S

SINGLE PHASE GLASS PASSIVATED BRIDGE RECTIFIERS
Voltage Range - 200 to 1000 Volts Current - 0.5/0.8 Ampere

MBS



Dimensions in inches and (millimeters)

FEATURES

- ◆ Ideal for printed circuit board
- ◆ Reliable low cost construction utilizing molded plastic technique
- ◆ High temperature soldering guaranteed: 260°C/10 seconds at 5 lbs., (2.3kg) tension
- ◆ Small size, simple installation
- ◆ High surge current capability

MECHANICAL DATA

Case: Molded plastic body
Terminals: Plated leads solderable per MIL-STD-750, Method 2026
Polarity: Polarity symbols marked on case
Mounting Position: Any
Weight: 0.008 ounce, 0.22 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
 Single phase half-wave 60Hz, resistive or inductive load, for capacitive load derate current by 20%.

MDD Catalog Number	SYMBOLS	MDD MB2S	MDD MB4S	MDD MB6S	MDD MB8S	MDD MB10S	UNITS
Maximum repetitive peak reverse voltage	V_{RRM}	200	400	600	800	1000	VOLTS
Maximum RMS voltage	V_{RMS}	140	280	420	560	700	VOLTS
Maximum DC blocking voltage	V_{DC}	200	400	600	800	1000	VOLTS
Maximum average forward rectified current at $T_c=30^\circ C$ On glass-epoxy P.C.B. On aluminum substrate	$I_{F(AV)}$	0.5 0.8					Amps
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	30					Amps
Maximum instantaneous forward voltage drop per leg at 0.4A	V_F	1.0					Volts
Maximum DC reverse current at rated DC blocking voltage $T_A=25^\circ C$ $T_A=125^\circ C$	I_R	5.0 500					μA μA
Typical junction capacitance per leg (Note3)	C_J	13					pF
Typical thermal resistance per leg	$R_{\theta JA}$	70					$^\circ C/W$
Operating temperature range	T_J	-55 to +150					$^\circ C$
storage temperature range	T_{STG}	-55 to +150					$^\circ C$

NOTES: 1. On glass epoxy P.C.B. mounted on 0.05x0.05" (1.3x1.3mm) pads
 2. On aluminum substrate P.C.B. with on area of 0.8"x0.8" (20x20mm) mounted on 0.05x0.05" (1.3x1.3mm) solder pad
 3. Measured at 1.0MHz and applied reverse voltage of 4.0 volts.



RATINGS AND CHARACTERISTIC CURVES MB2S THRU MB10S

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT FOR




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS PER LEG




FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS PER LEG





FIG. 5-TYPICAL JUNCTION CAPACITANCE PER LEG



The cruve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!

