

# BAS70WS

## List

List..... 1

Package outline..... 2

Features..... 2

Mechanical data..... 2

Maximum ratings ..... 2

Rating and characteristic curves..... 3

Pinning information..... 4

Marking..... 4

Suggested solder pad layout..... 4

Packing information..... 5

Reel packing..... 6

Suggested thermal profiles for soldering processes..... 6

High reliability test capabilities..... 7

# BAS70WS

## 70mA Surface Mount Small Signal Schottky Diodes-70V


### Features

- Low current rectification and high speed switching.
- Small surface mount type.
- Up to 70mA current capability.
- Low forward voltage drop ( $V_F = 1.00V$  typ. @15mA)
- Silicon epitaxial planar chip, metal silicon junction.
- Lead-free parts for green partner, exceeds environmental standards of MIL-STD-19500 /228
- High speed (  $t_{rr} < 5$  ns )
- Suffix "-H" indicates Halogen-free parts, ex. BAS70WS-H.

### Mechanical data

- Epoxy:UL94-V0 rated flame retardant
- Case : Molded plastic, SOD-323F
- Terminals : Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity : Indicated by cathode band
- Mounting Position : Any
- Weight : Approximated 0.005 gram

### Package outline



### Maximum ratings and Electrical Characteristics (AT $T_A=25^\circ\text{C}$ unless otherwise noted)

| PARAMETER                       | CONDITIONS  | Symbol          | MIN. | TYP. | MAX. | UNIT                      |
|---------------------------------|---|-----------------|------|------|------|---------------------------|
| Repetitive peak reverse voltage |   | $V_{RRM}$       |      |      | 70   | V                         |
| Reverse voltage                 |   | $V_R$           |      |      | 70   | V                         |
| Repetitive peak forward current | @ $t < 1.0s$  | $I_{FSM}$       |      |      | 100  | mA                        |
| Forward current                 |   | $I_F$           |      |      | 70   | mA                        |
| Power Dissipation               |   | $P_D$           |      |      | 200  | mW                        |
| Thermal Resistance              | Junction to Ambient   | $R_{\theta JA}$ |      |      | 625  | $^\circ\text{C}/\text{W}$ |
| Junction temperature            |   | $T_J$           | -55  |      | +125 | $^\circ\text{C}$          |
| Storage temperature             |   | $T_{STG}$       | -65  |      | +125 | $^\circ\text{C}$          |
| Forward voltage                 | $I_F = 1.0$ mA  | $V_F$           |      |      | 0.41 | V                         |
|                                 | $I_F = 15$ mA   | $V_F$           |      |      | 1.00 | V                         |
| Reverse current                 | $V_R = 50$ V  | $I_R$           |      |      | 100  | nA                        |
| Diode capacitance               | $V_R = 0$ V, $f = 1$ MHz  | $C_D$           |      |      | 2    | pF                        |
| Reverse recovery time           | $I_F = 10$ mA, $V_R = 10$ mA, $I_{RR} = 0.1 \times I_{R1}$ , $RL=100\Omega$ | $t_{rr}$        |      |      | 5    | ns                        |

## Rating and characteristic curves for each diode (BAS70WS)




Fig.1 Forward current as a function of forward voltage; typical values.




Fig.2 Reverse current as a function of reverse voltage; typical values.




Fig.3 Differential forward resistance as a function of forward current.






Fig.4 Diode capacitance as a function of reverse voltage.

# BAS70WS


## Pinning information

| Pin                        | Simplified outline  | Symbol  |
|----------------------------|---|---|
| Pin1 cathode<br>Pin2 anode |  |  |

## Marking

| Type number | Marking code |
|-------------|--------------|
| BAS70WS     | K73          |

## Suggested solder pad layout




Dimensions in inches and (millimeters)

| PACKAGE  | A            | B            | C            |
|----------|--------------|--------------|--------------|
| SOD-323F | 0.033 (0.83) | 0.025 (0.63) | 0.063 (1.60) |

# BAS70WS

## Packing information



unit:mm

| Item                      | Symbol | Tolerance | SOD-323F |
|---------------------------|--------|-----------|----------|
| Carrier width             | A      | 0.1       | 1.46     |
| Carrier length            | B      | 0.1       | 2.95     |
| Carrier depth             | C      | 0.1       | 1.25     |
| Sprocket hole             | d      | 0.1       | 1.50     |
| 13" Reel outside diameter | D      | 2.0       | -        |
| 13" Reel inner diameter   | D1     | min       | -        |
| 7" Reel outside diameter  | D      | 2.0       | 178.00   |
| 7" Reel inner diameter    | D1     | min       | 62.00    |
| Feed hole diameter        | D2     | 0.5       | 13.00    |
| Sprocket hole position    | E      | 0.1       | 1.75     |
| Punch hole position       | F      | 0.1       | 3.50     |
| Punch hole pitch          | P      | 0.1       | 4.00     |
| Sprocket hole pitch       | P0     | 0.1       | 4.00     |
| Embossment center         | P1     | 0.1       | 2.00     |
| Overall tape thickness    | T      | 0.1       | 0.23     |
| Tape width                | W      | 0.3       | 8.00     |
| Reel width                | W1     | 1.0       | 11.40    |

Note: Devices are packed in accordance with EIA standard RS-481-A and specifications listed above.


# BAS70WS

## Reel packing

| PACKAGE  | REEL SIZE | REEL (pcs) | COMPONENT SPACING (m/m) | BOX (pcs) | INNER BOX (m/m) | REEL DIA, (m/m) | CARTON SIZE (m/m) | CARTON (pcs) | APPROX. GROSS WEIGHT (kg) |
|----------|-----------|------------|-------------------------|-----------|-----------------|-----------------|-------------------|--------------|---------------------------|
| SOD-323F | 7"        | 3,000      | 4.0                     | 30,000    | 183*183*123     | 178             | 382*262*387       | 240,000      | 8.0                       |

## Suggested thermal profiles for soldering processes

- 1.Storage environment: Temperature=5°C~40°C Humidity=55%±25%
- 2.Reflow soldering of surface-mount devices



### 3.Reflow soldering

| Profile Feature   | Soldering Condition         |
|---|-----------------------------|
| Average ramp-up rate(T <sub>L</sub> to T <sub>P</sub> )   | <3°C/sec                    |
| Preheat<br>-Temperature Min(T <sub>smmin</sub> )<br>-Temperature Max(T <sub>smmax</sub> )<br>-Time(min to max)(t <sub>s</sub> ) | 150°C<br>200°C<br>60~120sec |
| T <sub>smmax</sub> to T <sub>L</sub><br>-Ramp-upRate  | <3°C/sec                    |
| Time maintained above:<br>-Temperature(T <sub>L</sub> )<br>-Time(t <sub>L</sub> )   | 217°C<br>60~260sec          |
| Peak Temperature(T <sub>P</sub> )   | 255°C-0/+5°C                |
| Time within 5°C of actual Peak Temperature(t <sub>P</sub> )   | 10~30sec                    |
| Ramp-down Rate  | <6°C/sec                    |
| Time 25°C to Peak Temperature   | <6minutes                   |

**BAS70WS****High reliability test capabilities**

| Item Test                         | Conditions   | Reference                     |
|-----------------------------------|--|-------------------------------|
| 1. Solder Resistance              | at $260\pm 5^{\circ}\text{C}$ for $10\pm 2\text{sec.}$<br>immerse body into solder $1/16''\pm 1/32''$                                      | MIL-STD-750D<br>METHOD-2031   |
| 2. Solderability                  | at $245\pm 5^{\circ}\text{C}$ for 5 sec.   | MIL-STD-202F<br>METHOD-208    |
| 3. High Temperature Reverse Bias  | $V_R=80\%$ rate at $T_J=125^{\circ}\text{C}$ for 168 hrs.  | MIL-STD-750D<br>METHOD-1038   |
| 4. Forward Operation Life         | Rated average rectifier current at $T_A=25^{\circ}\text{C}$ for 500hrs.  | MIL-STD-750D<br>METHOD-1027   |
| 5. Intermittent Operation Life    | $T_A = 25^{\circ}\text{C}$ , $I_F = I_o$<br>On state: power on for 5 min.<br>off state: power off for 5 min.<br>on and off for 500 cycles. | MIL-STD-750D<br>METHOD-1036   |
| 6. Pressure Cooker                | $15P_{SIG}$ at $T_A=121^{\circ}\text{C}$ for 4 hrs.  | JESD22-A102                   |
| 7. Temperature Cycling            | $-55^{\circ}\text{C}$ to $+125^{\circ}\text{C}$ dwelled for 30 min.<br>and transferred for 5min. total 10 cycles.                          | MIL-STD-750D<br>METHOD-1051   |
| 8. Thermal Shock                  | $0^{\circ}\text{C}$ for 5 min. rise to $100^{\circ}\text{C}$ for 5 min. total 10 cycles.   | MIL-STD-750D<br>METHOD-1056   |
| 9. Forward Surge                  | Peak forward surge current @ $t < 1.0\text{s}$   | MIL-STD-750D<br>METHOD-4066-2 |
| 10. Humidity                      | at $T_A=85^{\circ}\text{C}$ , RH=85% for 1000hrs.  | MIL-STD-750D<br>METHOD-1021   |
| 11. High Temperature Storage Life | at $175^{\circ}\text{C}$ for 1000 hrs.   | MIL-STD-750D<br>METHOD-1031   |