

RoHS

HALOGEN FREE

GREEN

# **IR Receiver Modules for Remote Control Systems**



## **MECHANICAL DATA**

Pinning:

1, 4 = GND,  $2 = V_S$ , 3 = OUT

#### **ORDERING CODE**

Taping:

TSOP77...TT - top view taped TSOP77...TR - side view taped

#### **FEATURES**

- · Improved immunity against HF and RF noise
- · Low supply current
- · Photo detector and preamplifier in one package
- Internal filter for PCM frequency
- Supply voltage: 2.5 V to 5.5 V
- Improved immunity against optical noise
- Capable of side or top view
- Insensitive to supply voltage ripple and noise
- Two lenses for high sensitivity and wide receiving angle
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



The TSOP77... series are miniaturized SMD IR receiver modules for infrared remote control systems. Two PIN diodes and a preamplifier are assembled on a leadframe, the epoxy package contains an IR filter. The demodulated output signal can be directly connected to a microprocessor for decoding.

The TSOP774.. series devices are optimized to suppress almost all spurious pulses from Wi-Fi and CFL sources. They may suppress some data signals if continuously transmitted.

The TSOP772.. series devices are provided primarily for compatibility with old AGC2 designs. New designs should prefer the TSOP774.. series containing the newer AGC4.

These components have not been qualified according to automotive specifications.


PARTS T	ABLE		
AGC		LEGACY, FOR LONG BURST REMOTE CONTROLS (AGC2)	RECOMMENDED FOR LONG BURST CODES (AGC4)
	30 kHz	TSOP77230	TSOP77430
	33 kHz	TSOP77233	TSOP77433
Carrier frequency	36 kHz	TSOP77236	TSOP77436 (1)(2)(3)
	38 kHz	TSOP77238	TSOP77438 <sup>(4)(5)</sup>
	40 kHz	TSOP77240	TSOP77440
	56 kHz	TSOP77256	TSOP77456 (6)(7)
Package		Heir	ndall
Pinning		1, 4 = GND, 2	= V <sub>S</sub> , 3 = OUT
Dimensions	s (mm)	6.8 W x 3.0	O H x 3.2 D
Mounting		SM	MD
Application	ı	Remote	control
Best choice	for	(1) RC-5 (2) RC-6 (3) Panasonic (4) NEO	C (5) Sharp (6) r-step (7) Thomson RCA



## **BLOCK DIAGRAM**

# 2 Vs 30 kΩ Vs 3 OUT Demodulator PIN Control circuit GND

## **APPLICATION CIRCUIT**



 $R_1$  and  $C_1$  recommended to reduce supply ripple for  $V_S < 2.8 \text{ V}$ 


ABSOLUTE MAXIMUM RA	TINGS				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Supply voltage		Vs	-0.3 to +6	V	
Supply current		I <sub>S</sub>	5	mA	
Output voltage		Vo	-0.3 to (V <sub>S</sub> + 0.3)	V	
Output current		I <sub>O</sub>	5	mA	
Junction temperature		Tj	100	°C	
Storage temperature range		T <sub>stg</sub>	-25 to +85	°C	
Operating temperature range		T <sub>amb</sub>	-25 to +85	°C	
Power consumption	T <sub>amb</sub> ≤ 85 °C	P <sub>tot</sub>	10	mW	

#### Note

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only
and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification
is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability

ELECTRICAL AND	OPTICAL CHARACTERISTICS (T <sub>amb</sub> = 25	°C, unles	s otherwi	se specif	ied)	
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply voltage		Vs	2.5	-	5.5	V
Cupply ourrent	$V_S = 5 \text{ V}, E_v = 0$	I <sub>SD</sub>	0.55	0.7	0.9	mA
Supply current	$E_v = 40 \text{ klx, sunlight}$	I <sub>SH</sub>	-	0.8	-	mA
Transmission distance	$E_V = 0$ , IR diode TSAL6200, $I_F = 250$ mA, test signal see Fig. 1	d	-	40	-	m
Output voltage low	$I_{OSL} = 0.5 \text{ mA}, E_e = 0.7 \text{ mW/m}^2$ , test signal see Fig. 1	V <sub>OSL</sub>	=	-	100	mV
Minimum irradiance	Pulse width tolerance: $t_{pi}$ - 5/ $f_o$ < $t_{po}$ < $t_{pi}$ + 6/ $f_o$ , test signal see Fig. 1	E <sub>e min.</sub>	-	0.2	0.4	mW/m <sup>2</sup>
Maximum irradiance	$t_{pi}$ - $5/f_0 < t_{po} < t_{pi} + 6/f_0$ , test signal see Fig. 1	E <sub>e max.</sub>	50	-	-	W/m <sup>2</sup>
Directivity	Angle of half transmission distance	Φ1/2	1	± 50	-	deg

# TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)






Fig. 2 - Pulse Length and Sensitivity in Dark Ambient






Fig. 3 - Output Function




Fig. 4 - Output Pulse Diagram




Fig. 5 - Frequency Dependence of Responsivity




Fig. 6 - Sensitivity in Bright Ambient




Fig. 7 - Sensitivity vs. Supply Voltage Disturbances




Fig. 8 - Max. Envelope Duty Cycle vs. Burst Length






Fig. 9 - Sensitivity vs. Ambient Temperature




Fig. 10 - Relative Spectral Sensitivity vs. Wavelength




Fig. 11 - Horizontal Directivity




Fig. 12 - Vertical Directivity




Fig. 1 Sensitivity vs. Supply Voltage



## **SUITABLE DATA FORMAT**

This series is designed to suppress spurious output pulses due to noise or disturbance signals. The devices can distinguish data signals from noise due to differences in frequency, burst length, and envelope duty cycle. The data signal should be close to the device's band-pass center frequency (e.g. 38 kHz) and fulfill the conditions in the table below.

When a data signal is applied to the product in the presence of a disturbance, the sensitivity of the receiver is automatically reduced by the AGC to insure that no spurious pulses are present at the receiver's output.

Some examples which are suppressed are:

- DC light (e.g. from tungsten bulbs sunlight)
- · Continuous signals at any frequency
- Strongly or weakly modulated noise from fluorescent lamps with electronic ballasts (see Fig. 13 or Fig. 14)
- 2.4 GHz and 5 GHz Wi-Fi




Fig. 13 - IR Disturbance from Fluorescent Lamp with Low Modulation




Fig. 14 - IR Disturbance from Fluorescent Lamp with High Modulation


	TSOP772	TSOP774
Minimum burst length	10 cycles/burst	10 cycles/burst
After each burst of length a minimum gap time is required of	10 to 70 cycles ≥ 12 cycles	10 to 35 cycles ≥ 12 cycles
For bursts greater than a minimum gap time in the data stream is needed of	70 cycles > 4 x burst length	35 cycles > 10 x burst length
Maximum number of continuous short bursts/second	800	1300
NEC code	Yes	Preferred
RC5 / RC6 code	Yes	Preferred
Thomson 56 kHz code	Yes	Preferred
Sharp code	Yes	Preferred
Suppression of interference from fluorescent lamps	Mild disturbance patterns are suppressed (example: signal pattern of Fig. 13)	Complex and critical disturbance patterns are suppressed (example: signal pattern of Fig. 14 or highly dimmed LCDs)

## Note

• For data formats with short bursts please see the datasheet of TSOP773.. and TSOP775..



## **PACKAGE DIMENSIONS** in millimeters



#### **ASSEMBLY INSTRUCTIONS**


#### **Reflow Soldering**

- Reflow soldering must be done within 72 h while stored under a max. temperature of 30 °C, 60 % RH after opening the dry pack envelope
- Set the furnace temperatures for pre-heating and heating in accordance with the reflow temperature profile as shown in the diagram. Exercise extreme care to keep the maximum temperature below 260 °C. The temperature shown in the profile means the temperature at the device surface. Since there is a temperature difference between the component and the circuit board, it should be verified that the temperature of the device is accurately being measured
- Handling after reflow should be done only after the work surface has been cooled off


#### **Manual Soldering**


- Use a soldering iron of 25 W or less. Adjust the temperature of the soldering iron below 300 °C
- Finish soldering within 3 s
- · Handle products only after the temperature has cooled off

# **VISHAY LEAD (Pb)-FREE REFLOW SOLDER PROFILE**



## **TAPING VERSION TSOP..TR DIMENSIONS** in millimeters







Drawing-No.: 9.700-5337.01-4 Issue: 2; 06.10.15

technical drawings according to DIN specifications

## TAPING VERSION TSOP..TT DIMENSIONS in millimeters






technical drawings according to DIN specifications

Drawing-No.: 9.700-5338.01-4 Issue: 4; 12.06.13


## **REEL DIMENSIONS** in millimeters



Drawing-No.: 9.800-5052.V2-4

Issue: 1; 07.05.02

16734



Form of the leave open of the wheel is supplier specific.


Dimension acc. to IEC EN 60 286-3

Tape width 16



technical drawings according to DIN specifications

# **LEADER AND TRAILER DIMENSIONS** in millimeters



## **COVER TAPE PEEL STRENGTH**

According to DIN EN 60286-3 0.1 N to 1.3 N  $300 \pm 10$  mm/min.  $165^{\circ}$  to  $180^{\circ}$  peel angle

## **LABEL**

## Standard bar code labels for finished goods


The standard bar code labels are product labels and used for identification of goods. The finished goods are packed in final packing area. The standard packing units are labeled with standard bar code labels before transported as finished goods to warehouses. The labels are on each packing unit and contain Vishay Semiconductor GmbH specific data.



PLAIN WRITING	ABBREVIATION	LENGTH
Item-description	-	18
Item-number	INO	8
Selection-code	SEL	3
LOT-/serial-number	BATCH	10
Data-code	COD	3 (YWW)
Plant-code	PTC	2
Quantity	QTY	8
Accepted by	ACC	-
Packed by	PCK	-
Mixed code indicator	MIXED CODE	-
Origin	xxxxxx+	Company logo
Long bar code top	Туре	Length
Item-number	N	8
Plant-code	N	2
Sequence-number	X	3
Quantity	N	8
Total length	-	21
Short bar code bottom	Туре	Length
Selection-code	X	3
Data-code	N	3
Batch-number	X	10
Filter	-	1
Total length	-	17

## **DRY PACKING**

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



## **FINAL PACKING**

The sealed reel is packed into a cardboard box.

## RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity  $\leq$  60 % RH max.

After more than 72 h under these conditions moisture content will be too high for reflow soldering.


In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 h at 40 °C + 5 °C / - 0 °C and < 5 % RH (dry air / nitrogen) or


96 h at 60 °C + 5 °C and < 5 % RH for all device containers or

24 h at 125 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC $^{\circledR}$  standard J-STD-020 level 4 label is included on all dry bags.



EIA JEDEC standard J-STD-020 level 4 label is included on all dry bags





## **ESD PRECAUTION**

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electrostatic sensitive devices warning labels are on the packaging.

# VISHAY SEMICONDUCTORS STANDARD BAR CODE LABELS (example)

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



22178



# **Legal Disclaimer Notice**

Vishay

# **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.