

RoHS Device  
Halogen Free




### Features

- Bi-directional ESD protection.
- IEC61000-4-2 Level 4 ESD protection.
- Working Voltage: 5V
- Typical capacitance: 0.4pF

### Mechanical data

- Case: DFN1006-2L/0402 small outline plastic package. molded plastic.
- Terminals: Gold plated, solderable per MIL-STD-750, method 2026.
- Mounting position: Any.
- High temperature soldering guaranteed: 260°C/10 second.
- Weight: 0.001 grams(approx.).

### Circuit diagram



### Maximum Rating ( at TA=25°C unless otherwise noted )

Parameter	Symbol	Value	Unit
Peak pulse power ( tp = 8/20μs waveform)	PPP	50	W
ESD per IEC 61000-4-2(Air) ESD per IEC 61000-4-2(Contact)	VESD <sup>(1)</sup>	±15 ±8	kV
Operating temperature rang	TJ	-55 to +150	°C
Storage temperature rang	TSTG	-55 to +150	°C

### Electrical Characteristics ( at TA=25°C unless otherwise noted )

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Reverse stand-off voltage		VRWM	-	-	5	V
Reverse leakage current	VR = 5 V	IR	-	-	100	nA
Reverse breakdown voltage	IR = 1 mA	V(BR)	6	-	10	V
Clamping voltage	I <sub>PP</sub> = 1 A	VC	-	13	15	V
	I <sub>PP</sub> = 3 A	VC <sup>(2)</sup>	-	19	21	V
Junction capacitance	VR = 0V , F=1MHz	CJ	-	0.4	0.55	pF

**Notes:** 1. Device stressed with ten non-repetitive ESD pulses.

2. Non-Repetitive current pulse 8/20us exponential decay waveform according to IEC61000-4-5

**RATING AND CHARACTERISTIC CURVES (PESD5V0F1BL)**

Fig.1 - 8/20us Peak Pulse Current Wave  
Form Acc. IEC 61000-4-5




Fig.2 - Typical Capacitance Between  
Terminals Characteristics




Fig.3 - Clamping Voltage Vs.  
Peak Pulse Current






Fig.4 - Power Rating Derating Curve



## Reel Taping Specification




SOD-882	SYMBOL	A	B	C	d	D	D <sub>1</sub>	D <sub>2</sub>
	(mm)	0.75 ± 0.05	1.17 ± 0.05	0.65 ± 0.05	1.50 + 0.10 - 0	178.00 ± 1.00	60.00 ± 0.50	13.50 ± 0.20
	(inch)	0.030 ± 0.002	0.046 ± 0.002	0.026 ± 0.002	0.059 + 0.004 - 0	7.008 ± 0.039	2.362 ± 0.020	0.531 ± 0.008

SOD-882	SYMBOL	E	F	P	P <sub>0</sub>	P <sub>1</sub>	T	W	W <sub>1</sub>
	(mm)	1.75 ± 0.10	3.50 ± 0.10	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	0.20 + 0.02 - 0.05	8.00 ± 0.20	12.00 + 0.50 - 0
	(inch)	0.069 ± 0.004	0.138 ± 0.004	0.157 ± 0.004	0.157 ± 0.004	0.079 ± 0.004	0.008 + 0.001 - 0.002	0.315 ± 0.008	0.472 + 0.020 - 0

### Suggested PAD Layout

SIZE	SOD-882	
	(mm)	(inch)
<b>A</b>	0.70	0.028
<b>B</b>	0.40	0.016
<b>C</b>	0.60	0.024
<b>D</b>	1.10	0.043
<b>E</b>	0.30	0.012



### Standard Packaging

Case Type	REEL PACK	
	REEL ( pcs )	Reel Size (inch)
<b>SOD-882</b>	10,000	7