



Silicon N-Channel Power MOSFET



CS1N60 A3H

General Description:


CS1N60 A3H, the silicon N-channel Enhanced VDMOSFETs, is obtained by the self-aligned planar Technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. The transistor can be used in various power switching circuit for system miniaturization and higher efficiency. The package form is TO-251, which accords with the RoHS standard.

Features:


- | Fast Switching
- | Low ON Resistance($R_{DS(on)} \leq 15\Omega$)
- | Low Gate Charge (Typical Data:4nC)
- | Low Reverse transfer capacitances(Typical:2.6pF)
- | 100% Single Pulse avalanche energy Test

V_{DSS}	600	V
I_D	0.8	A
P_D ($T_C=25^\circ C$)	25	W
$R_{DS(ON)Typ}$	11	Ω

TO-251



Inner Equivalent Principium Chart



Applications:

Power switch circuit of adaptor and charger.

Absolute ($T_c = 25^\circ C$ unless otherwise specified):

Symbol	Parameter	Rating	Units
V_{DSS}	Drain-to-Source Voltage	600	V
I_D	Continuous Drain Current	0.8	A
	Continuous Drain Current $T_c = 100^\circ C$	0.6	A
I_{DM}^{a1}	Pulsed Drain Current	3.2	A
V_{GS}	Gate-to-Source Voltage	± 30	V
E_{AS}^{a2}	Single Pulse Avalanche Energy	20	mJ
E_{AR}^{a1}	Avalanche Energy ,Repetitive	6	mJ
I_{AR}^{a1}	Avalanche Current	1.1	A
dv/dt^{a3}	Peak Diode Recovery dv/dt	5	V/ns
P_D	Power Dissipation	25	W
	Derating Factor above $25^\circ C$	0.2	W/ $^\circ C$
T_J, T_{stg}	Operating Junction and Storage Temperature Range	150, -55 to 150	$^\circ C$
T_L	Maximum Temperature for Soldering	300	$^\circ C$

**Electrical Characteristics** (T_c= 25°C unless otherwise specified):

OFF Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
V _{DSS}	Drain to Source Breakdown Voltage	V _{GS} =0V, I _D =250μA	600	--	--	V
ΔBV _{DSS} /ΔT _J	Bvdss Temperature Coefficient	ID=250uA, Reference 25°C	--	0.55	--	V/°C
I _{DSS}	Drain to Source Leakage Current	V _{DS} = 600V, V _{GS} = 0V, T _a = 25°C	--	--	1	μA
		V _{DS} = 480V, V _{GS} = 0V, T _a = 125°C	--	--	100	
I _{GSS(F)}	Gate to Source Forward Leakage	V _{GS} = +30V	--	--	100	nA
I _{GSS(R)}	Gate to Source Reverse Leakage	V _{GS} = -30V	--	--	-100	nA

ON Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
R _{DS(ON)}	Drain-to-Source On-Resistance	V _{GS} =10V, I _D =0.4A	--	11	15	Ω
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	2.0		4.0	V
Pulse width t _p ≤300μs, δ≤2%						

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
g _f	Forward Trans conductance	V _{DS} =15V, I _D = 0.8A	--	0.9	--	S
C _{iss}	Input Capacitance		--	92	--	pF
C _{oss}	Output Capacitance	V _{GS} = 0V V _{DS} = 25V f = 1.0MHz	--	10.7	--	
C _{rss}	Reverse Transfer Capacitance		--	2.6	--	






Resistive Switching Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
t _{d(ON)}	Turn-on Delay Time	I _D = 0.8A V _{DD} = 300V V _{GS} = 10V R _G = 25Ω	--	6.3	--	ns
t _r	Rise Time		--	6.3	--	
t _{d(OFF)}	Turn-Off Delay Time		--	21	--	
t _f	Fall Time		--	15	--	
Q _g	Total Gate Charge	I _D = 0.8A V _{DD} = 300V V _{GS} = 10V	--	4		nC
Q _{gs}	Gate to Source Charge		--	0.7		
Q _{gd}	Gate to Drain ("Miller") Charge		--	2.1		

**Source-Drain Diode Characteristics**

Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
I _S	Continuous Source Current (Body Diode)		--	--	0.8	A
I _{SM}	Maximum Pulsed Current (Body Diode)		--	--	3.2	A
V _{SD}	Diode Forward Voltage	I _S =0.8A,V _{GS} =0V	--	--	1.5	V
t _{rr}	Reverse Recovery Time	I _S =0.8A,T _j =25°C	--	400		ns
Q _{rr}	Reverse Recovery Charge	dI _P /dt=100A/us, V _{GS} =0V	--	739		nC
Pulse width tp≤300μs,δ≤2%						

Symbol	Parameter	Typ.	Units
R _{θJC}	Junction-to-Case	5.0	°C/W
R _{θJA}	Junction-to-Ambient	62	°C/W

^{a1}: Repetitive rating; pulse width limited by maximum junction temperature^{a2}: L=10.0mH, I_D=2A, Start T_J=25°C^{a3}: I_{SD}=0.8A,di/dt≤100A/us,V_{DD}≤BV_{DS}, Start T_J=25°C

**Characteristics Curve:**



CS1N60 A3H




Figure 6 Maximum Peak Current Capability




Figure 7 Typical Transfer Characteristics




Figure 8 Typical Drain to Source ON Resistance vs Gate Voltage and Drain Current




Figure 9 Typical Drain to Source ON Resistance vs Drain Current










Figure 10 Typical Drian to Source on Resistance vs Junction Temperature



CS1N60 A3H





Test Circuit and Waveform




Figure 17. Gate Charge Test Circuit




Figure 18. Gate Charge Waveform




Figure 19. Resistive Switching Test Circuit




Figure 20. Resistive Switching Waveforms




Figure 21. Diode Reverse Recovery Test Circuit




Figure 22. Diode Reverse Recovery Waveform





Figure 23. Unclamped Inductive Switching Test Circuit

Figure 24. Unclamped Inductive Switching Waveforms

**Package Information:**

Items	Values(mm)	
	MIN	MAX
A	6.30	6.90
B	5.70	6.30
C	2.10	2.50
D	0.30	0.60
E	0.50	0.70
F	0.30	0.60
G	0.70	1.00
H	1.60	2.40
L	7.70	9.80
	6.00	6.30
	4.50	5.80
	2.10	3.70
M	5.10	5.50
N	2.09	2.49

TO-251 Package



The name and content of poisonous and harmful material in products

Part's Name	Hazardous Substance					
	Pb	Hg	Cd	Cr(VI)	PBB	PBDE
Limit	≤0.1%	≤0.1%	≤0.01%	≤0.1%	≤0.1%	≤0.1%
Lead Frame	○	○	○	○	○	○
Molding Compound	○	○	○	○	○	○
Chip	○	○	○	○	○	○
Wire Bonding	○	○	○	○	○	○
Solder	×	○	○	○	○	○
Note	○: means the hazardous material is under the criterion of SJ/T11363-2006. ×: means the hazardous material exceeds the criterion of SJ/T11363-2006. The plumbum element of solder exist in products presently, but within the allowed range of Eurogroup's RoHS.					

Warnings

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. It is suggested to be used under 80 percent of the maximum ratings of the device.
 2. When installing the heatsink, please pay attention to the torsional moment and the smoothness of the heatsink.
 3. VDMOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
 4. This publication is made by Huajing Microelectronics and subject to regular change without notice.

WUXI CHINA RESOURCES HUAJING MICROELECTRONICS CO., LTD.

Add: No.14 Liangxi RD. Wuxi, Jiangsu, China Mail:214061 <http://www.crhj.com.cn>
Tel: +86 0510-85807228 Fax: +86-0510-85800864

Marketing Part: Post: 214061 Tel: +86 0510-81805277/81805336
Fax: +86 0510-85800360/85803016
E-mail: sales@hj.crmicro.com

Application and Service: Post: 214061 Tel / Fax: +86-0510-81805243/81805110